

## HORIZONTAL SPLIT CASE / ELECTRIC, 50Hz

PUMP	FLOW GPM (L/s)	SPEED RPM	PRESSURE RANGE PSI (kPa)	
			UL	FM
5 x 4 x 10F	500 (32)	2945	44 (303) - 120 (827)	44 (303) - 120 (827)
	750 (47)		80 (552) - 112 (772)	80 (552) - 112 (772)
6 x 5 x 10 F	750 (47)	2945	71 (490) - 117 (807)	71 (490) - 117 (807)
	1000 (63)		88 (607) - 112 (772)	88 (607) - 112 (772)
6 x 5 x 12 MF	750 (47)	2945	95 (655) - 186 (1282)	95 (655) - 186 (1282)
	1000 (63)		104 (717) - 177 (1220)	104 (717) - 177 (1220)
6 x 5 x 9.5 F	750 (47)	2945	63 (434) - 90 (620)	63 (434) - 90 (620)
	1000 (63)	2945	73 (503) - 81 (558)	73 (503) - 81 (558)
6 x 5 x 15 F	1000 (63)	2960		162 (1117) - 236 (1627)
	1250 (79)		155 (1069) - 229 (1579)	155 (1069) - 229 (1579)
	1500 (95)		146 (1007) - 223 (1538)	146 (1007) - 223 (1538)
8 x 6 x 10 LF	1000 (63)	2945	63 (434) - 125 (862)	63 (434) - 125 (862)
	1250 (79)		75 (517) - 120 (827)	74 (510) - 120 (827)
	1500 (95)		95 (655) - 115 (793)	95 (655) - 114 (786)
8 x 6 x 12.5 LF	1250 (79)	2945	121 (834) - 190 (1310)	121 (834) - 188 (1296)
8 x 6 x 12.5 MF	1500 (95)	2945	111 (765) - 167 (1151)	111 (765) - 167 (1151)
8 x 6 x 15 HF	1500 (95)	1450	47 (324) - 72 (496)	47 (324) - 72 (496)
8 x 6 x 16 F	750 (47)	1450	40 (276) - 75 (517)	40 (276) - 75 (517)
	1000 (63)		50 (345) - 72.5 (500)	52 (359) - 73 (503)
	1250 (79)		46 (317) - 68 (489)	48 (331) - 70 (483)
10 x 8 x 11 MF	2000 (126)	2945	100 (690) - 146 (1007)	100 (690) - 146 (1007)
10 x 8 x 11 HF	2000 (126)	2945	128 (883) - 165 (1138)	128 (883) - 165 (1138)
10 x 8 x 14 LF	2000 (126)	2945	140 (965) - 217 (1496)	140 (965) - 202 (1393)
	2500 (158)		140 (965) - 212 (1462)	140 (965) - 197 (1358)
10 x 8 x 14 HF	2000 (126)	1450	54 (372) - 57 (393)	54 (372) - 57 (393)
12 x 8 x 18 F	2000 (126)	1450	59 (407) - 94 (648)	59 (407) - 94 (648)
	2500 (158)		54.5 (376) - 91 (627)	54.5 (376) - 91 (627)

S. A. Armstrong Limited  
23 Bertrand Avenue  
Toronto, Ontario  
Canada, M1L 2P3  
T: 416 755 2291  
F: 416 759 9101

Armstrong Integrated Limited  
Wenlock Way  
Manchester  
United Kingdom, M12 5JL  
T: +44 (0) 8444 145 145  
F: +44 (0) 8444 145 146

Armstrong Design Private Limited  
(Unit 1- Armstrong Manufacturing Center)  
490-L, 4<sup>th</sup> Phase, Peenya Industrial  
Area, Bangalore, India 560 058  
T: +91 (80) 4906 3555  
F: +91 (80) 2334 3535

© S.A. Armstrong Limited 2011