


415V/3ph/50Hz

PUMP	kW	FLC(A)	SC(A)	Dimn.H	WT(kg)	PUMP	kW	FLC(A)	SC(A)	Dimn.H	WT(kg)
AM2/6	0.75	1.9	10.8	400	613					415	
AM2/7					615	AM4/7	1.10	2.6	16.3		615
AM2/8	1.10	2.6	16.3		616	AM4/8	1.50	3.5	21.9		628
AM2/9					617	AM4/9					629
AM2/11	1.50	3.5	21.9		631	AM4/11	2.20	4.4	28.8		633

SYSTEM CONNECTION : 2"BSP(F)
 WATER INLET : 3/4"BSP(M)



LAST MODIFICATION DETAILS		
AHBP	BORDER	ADDED
ISSUE	DATE	BY
F	11/02/2006	CHK BSD
		APP BSD

ALL DIMENSIONS IN mm
 DRAWN TO BS308
 WELDING SYMBOLS TO BS499
 SURFACE FINISH SHOWN IN
 MICROMETERS
 MACHINE WHERE SHOWN ✓
 TO TOLERANCE ± 0.3MM
 UNLESS OTHERWISE STATED

JOB No.	PART No.	WEIGHT KG	FILE NAME
-	-	-	-
DESIGN No.	PATTERN No.	MATERIAL	MAT'L SPEC.
-	-	-	-

THIS DRAWING IS THE PRIVATE AND CONFIDENTIAL PROPERTY OF ARMSTRONG HOLDEN BROOKE PULLEN LTD. ALL COPYRIGHT, MANUFACTURING AND SALES RIGHTS RESERVED.

TITLE
 ARMEX UNIT
 AM with 1500Ltr SAFE

DRG No.	
UKD03727-5xx	
DATE	DRN
24/09/1998	DCA
CHK	APP
SCALE	SHEET
1:1	1 OF 1

ARMSTRONG
 HOLDEN BROOKE PULLEN

WENLOCK WAY, MANCHESTER. M12 5JL
 TEL: +44 (0) 161 223 2223