


415V/3ph/50Hz

PUMP	kW	FLC(A)	SC(A)	Dimn.H	WT(kg)	PUMP	kW	FLC(A)	SC(A)	Dimn.H	WT(kg)
AM2/6	0.75	1.9	10.8	400	488					415	
AM2/7					490	AM4/7	1.10	2.6	16.3		490
AM2/8	1.10	2.6	16.3		491	AM4/8	1.50	3.5	21.9		503
AM2/9					492	AM4/9					504
AM2/11	1.50	3.5	21.9		506	AM4/11	2.20	4.4	28.8		508

SYSTEM CONNECTION : 2"BSP(F)  
WATER INLET : 3/4"BSP(M)



<p><b>LAST MODIFICATION DETAILS</b></p> <p>AHBP BORDER ADDED</p>	<p>ALL DIMENSIONS IN mm DRAWN TO BS308 WELDING SYMBOLS TO BS499 SURFACE FINISH SHOWN IN MICROMETERS MACHINE WHERE SHOWN ✓ TO TOLERANCE ± 0.3MM UNLESS OTHERWISE STATED</p>	<p>JOB No. - DESIGN No. -</p>	<p>PART No. - PATTERN No. -</p>	<p>WEIGHT KG - MATERIAL -</p>	<p>FILE NAME - MAT'L SPEC. -</p>	<p>TITLE</p> <p style="text-align: center;">ARMEX UNIT AM with 750Ltr SAFE</p>	<p>DRG No. UKD03727-3xx</p>	<p><b>ARMSTRONG</b> <b>HOLDEN BROOKE PULLEN</b></p>
		<p>THIS DRAWING IS THE PRIVATE AND CONFIDENTIAL PROPERTY OF ARMSTRONG HOLDEN BROOKE PULLEN LTD. ALL COPYRIGHT, MANUFACTURING AND SALES RIGHTS RESERVED.</p>		<p>DATE 22/09/1998 DRN DCA</p> <p>CHK APP</p> <p>SCALE 1:1 SHEET 1 OF 1</p>		<p>WENLOCK WAY, MANCHESTER. M12 5JL TEL: +44 (0) 161 223 2223</p>		