


415V/3ph/50Hz																	
PUMP	kW	FLC(A)	SC(A)	Dimn.H	WT(kg)	PUMP	kW	FLC(A)	SC(A)	Dimn.H	WT(kg)	PUMP	kW	FLC(A)	SC(A)	Dimn.H	WT(kg)
HMS202	0.55	1.6	9.6	320	271	HMS402	0.55	1.6	9.6	320	271	HMS802	0.75	1.8	10.8	340	274
HMS203						HMS403						HMS803	1.10	2.6	15.6		
HMS204						HMS404	0.75	1.8	10.8			HMS804	1.50	3.5	21.0		
HMS205	0.75	1.8	10.8		276	HMS405	1.10	2.6	15.6		279	HMS805	1.85	4.6	27.6		287



SYSTEM CONNECTION : 2" BSP(F)
 WATER INLET : 3/4" BSP(M)

LAST MODIFICATION DETAILS	ALL DIMENSIONS IN mm DRAWN TO BS308 WELDING SYMBOLS TO BS499 SURFACE FINISH SHOWN IN MICROMETERS MACHINE WHERE SHOWN ✓ TO TOLERANCE ± 0.3MM UNLESS OTHERWISE STATED	JOB No. -	PART No. -	WEIGHT KG -	FILE NAME -	TITLE ARMEX UNIT HMS with SAFE 300Ltr	DRG No. UKD03725-1xx	ARMSTRONG HOLDEN BROOKE PULLEN
AHBP BOREDER ADDED	DESIGN No. -	PATTERN No. -	MATERIAL -	MAT'L SPEC. -	DATE 16/03/1998	DRN DCA	WENLOCK WAY, MANCHESTER. M12 5JL TEL: +44 (0) 161 223 2223	
ISSUE DATE 11/07/2006	DRN BSD	CHK	APP	SCALE 1:1	SHEET 1 OF 1			
K	CHK BSD	APP BSD	THIS DRAWING IS THE PRIVATE AND CONFIDENTIAL PROPERTY OF ARMSTRONG HOLDEN BROOKE PULLEN LTD. ALL COPYRIGHT, MANUFACTURING AND SALES RIGHTS RESERVED.					