

PUMP SIZE	MOTOR KW	FLC AMPS 3x415V	PUMP WEIGHT KGS	SET WEIGHT KGS
802T11T	1.10	2.61	25.5	371
803T15T	1.50	3.45	32.0	397
804T22T	2.20	5.03	34.0	405
805T32T	2.20	5.03	35.0	409
806T30T	3.00	6.22	42.0	437
808T40T	4.00	8.14	58.5	503
809T40T	4.00	8.14	59.5	507

UNCONTROLLED

ALL FLANGES TO BS4504
 MAX WORKING PRESSURE
 TEST PRESSURE

16BAR
 15BAR
 22.5BAR


SUCTION MANIFOLD STANDARD POSITION 1

DELIVERY MANIFOLD STANDARD POSITION 2


SUCTION MANIFOLD OPTIONAL POSITION 3

DELIVERY MANIFOLD OPTIONAL POSITION 4

ANTI-VIBRATION MOUNTINGS
 OPTIONAL ONLY SUPPLIER WHEN ORDERED
 (4-PER SET K2092/1)




FLEXIBLE CONNECTORS OPTIONAL ONLY SUPPLIED WHEN ORDERED (2-PER SET)



NOTE :-

- 1) MAIN POWER SUPPLY TO PANEL MUST BE SIZED TO COVER ALL PUMP RUNNING AT SAME TIME
- 2) LARGE STORAGE VESSELS IF ORDERED, WILL BE SUPPLIED LOOSE FOR POSITIONING BY CLIENT TO SUIT THE AVAILABLE FLOOR SPACE. CLIENT IS TO PROVIDE A CONNECTION FROM THE VESSEL TO THE DELIVERY PIPEWORK ADJACENT TO THE SET ISOLATING AND DRAIN VALVES SHOULD BE FITTED IN THIS CONNECTION



LAST MODIFICATION DETAILS

DRAWING BORDER CHANGED

ISSUE	DATE	BY	APP	CHK
4	02/2006	DRN PJB	APP PJB	

ALL DIMENSIONS IN mm
 DRAWN TO BS308
 WELDING SYMBOLS TO BS499
 SURFACE FINISH SHOWN IN MICRO METERS
 MACHINE WHERE SHOWN TO TOLERANCE ± 0.3MM UNLESS OTHERWISE STATED

JOB No.	PART No.	WEIGHT KG	FILE NAME
-	-	-	PX10282-4

DESIGN No.	PATTERN No.	MATERIAL	MAT'L SPEC.
-	-	-	-

THIS DRAWING IS THE PRIVATE AND CONFIDENTIAL PROPERTY OF ARMSTRONG HOLDEN BROOKE PULLEN LTD. ALL COPYRIGHT, MANUFACTURING AND SALES RIGHTS RESERVED.

TITLE
 GENERAL ARRANGEMENT
 HYDRPAK HML4 SET
 8-PUMP MODELS

DRG No.
PX10282-4

DATE	BY	APP	CHK
02/10/2002	DRN BSD	APP EGU	CHK EGU

SCALE NTS SHEET 1 OF 1

ARMSTRONG HOLDEN BROOKE PULLEN

VENLOCK WAY, MANCHESTER, M12 5JL
 TEL: +44 (0) 161 223 2223