


| PUMP SIZE | MOTOR KW | FLC AMPS 3x415V | PUMP WEIGHT KGS | SET WEIGHT KGS | VESSEL SIZE LITRES | WORKING PRESSURE BAR | TEST PRESSURE BAR |
|-----------|----------|-----------------|-----------------|----------------|--------------------|----------------------|-------------------|
| 402T05T   | 0.55     | 1.43            | 1.75            | 263            | 60                 | 10                   | 15.0              |
| 403T05T   | 0.55     | 1.43            | 18.5            | 266            | 60                 | 10                   | 15.0              |
| 404T07T   | 0.75     | 2.02            | 21.0            | 273            | 60                 | 10                   | 15.0              |
| 405T11T   | 1.10     | 2.61            | 22.0            | 276            | 60                 | 10                   | 15.0              |
| 406T11T   | 1.10     | 2.61            | 22.5            | 278            | 60                 | 10                   | 15.0              |
| 407T11T   | 1.10     | 2.61            | 23.0            | 279            | 60                 | 10                   | 15.0              |
| 408T15T   | 1.50     | 3.45            | 29.5            | 289            | 60                 | 10                   | 15.0              |
| 409T15T   | 1.50     | 3.45            | 30.0            | 290            | 60                 | 10                   | 15.0              |
| 411T2T    | 2.20     | 5.03            | 32.0            | 306            | 20                 | 15                   | 22.5              |
| 413T2T    | 2.20     | 5.03            | 33.0            | 309            | 20                 | 15                   | 22.5              |
| 414T30T   | 3.00     | 6.22            | 39.0            | 327            | 20                 | 15                   | 22.5              |

ALL FLANGES TO BS4504 16BAR

# UNCONTROLLED



ANTI-VIBRATION MOUNTINGS OPTIONAL ONLY SUPPLIER WHEN ORDERED (4-PER SET K2092/1)

FLEXIBLE CONNECTORS OPTIONAL ONLY SUPPLIED WHEN ORDERED (2-PER SET)

NOTE :-

- 1) MAIN POWER SUPPLY TO PANEL MUST BE SIZED TO COVER ALL PUMP RUNNING AT SAME TIME
- 2) LARGE STORAGE VESSELS IF ORDERED WILL BE SUPPLIED LOOSE FOR POSITIONING BY CLIENT TO SUIT THE AVAILABLE FLOOR SPACE. CLIENT IS TO PROVIDE A CONNECTION FROM THE VESSEL TO THE DELIVERY PIPEWORK ADJACENT TO THE SET ISOLATING AND DRAIN VALVES SHOULD BE FITTED IN THIS CONNECTION

LAST MODIFICATION DETAILS DRAWING BORDER CHANGED

|         |                 |         |         |
|---------|-----------------|---------|---------|
| ISSUE 1 | DATE 15/02/2006 | DRN PJB | APP PJB |
| CHK PJB |                 |         |         |

ALL DIMENSIONS IN mm DRAWN TO BS308 WELDING SYMBOLS TO BS499 SURFACE FINISH SHOWN IN MICROMETERS MACHINE WHERE SHOWN TO TOLERANCE ± 0.3MM UNLESS OTHERWISE STATED

|            |             |           |            |
|------------|-------------|-----------|------------|
| JOB No.    | PART No.    | WEIGHT KG | FILE NAME  |
| -          | -           | -         | Px10466-1  |
| DESIGN No. | PATTERN No. | MATERIAL  | MATL SPEC. |
| -          | -           | -         | -          |

TITLE GENERAL ARRANGEMENT HYDROPAK IVSLS3 SET 4-PUMP MODELS C/W VLT8000 AQUA CONTROL

|                 |              |
|-----------------|--------------|
| DRG No.         | PX10466-1    |
| DATE 19/08/2004 | DRN BSD      |
| CHK EGU         | APP EGU      |
| SCALE NTS       | SHEET 1 OF 1 |

**ARMSTRONG HOLDEN BROOKE PULLEN**  
 VENLOCK WAY, MANCHESTER, M12 5JL  
 TEL: +44 (0) 161 223 2223