



1 X 230V	POWER	FLC
50Hz IEC38	WATT	Amps
AUTO MIN.	30	0.25
AUTO MAX.	250	1.30
SPEED 1-4	180-340	1.2-2.10
NPSH (bar)	80°C-0.5	95°C-1.5

NOTE :-
 1) PUMP SHAFT MUST BE MOUNTED HORIZONTALLY
 2) FOR CORRECT ORIENTATION REFER TO D & M INSTRUCTIONS

LAST MODIFICATION DETAILS

ISSUE	DATE	DRN	APP
A	CHK -	APP -	

ALL DIMENSIONS IN mm
 DRAWN TO BS308
 WELDING SYMBOLS TO BS499
 SURFACE FINISH SHOWN IN MICROMETERS
 MACHINE WHERE SHOWN TO TOLERANCE ± 0.3MM UNLESS OTHERWISE STATED

JOB No.	PART No.	WEIGHT KG	FILE NAME
-	-	15.2	-
DESIGN No.	PATTERN No.	MATERIAL	MAT'L SPEC.
-	-	-	-

THIS DRAWING IS THE PRIVATE AND CONFIDENTIAL PROPERTY OF ARMSTRONG HOLDEN BROOKE PULLEN LTD. ALL COPYRIGHT, MANUFACTURING AND SALES RIGHTS RESERVED.

TITLE
 GENERAL ARRANGEMENT
 AGET+30-120-1
 TWIN PUMP

DRG No. AGET301201

DATE 02/03/2011	DRN BSD
CHK BSD	APP PK
SCALE 1:1	SHEET 1 OF 1

ARMSTRONG

VENLDOCK WAY, MANCHESTER, M12 5JL
 TEL: +44 (0) 161 223 2223