



CAPACITY LTRS.	GROUP No.	∅D	H	P	APPROX. WEIGHT kg
300	-031	570	1780	690	130
500	-051	690	1890	810	170
750	-071	850	2080	960	270
1000	-101	930	2130	1040	300
1500	-151	1140	2140	1250	360



NOTES
SAFE CONNECTION 1" BSP(F)



<p>LAST MODIFICATION DETAILS</p> <p>AHBP BORDER ADDED</p>	<p>ALL DIMENSIONS IN mm DRAWN TO BS308 WELDING SYMBOLS TO BS499 SURFACE FINISH SHOWN IN MICROMETERS MACHINE WHERE SHOWN ✓ TO TOLERANCE ± 0.3MM UNLESS OTHERWISE STATED</p>	<p>JOB No. -</p> <p>DESIGN No. -</p>	<p>PART No. -</p> <p>PATTERN No. -</p>	<p>WEIGHT KG -</p> <p>MATERIAL -</p>	<p>FILE NAME -</p> <p>MAT'L SPEC. -</p>	<p>TITLE</p> <p style="text-align:center; font-size: 1.2em;">ARMEX SAFES</p>	<p>DRG No. UKD03922 Sht1</p> <p>DATE 30/03/1999 DRN DCA</p> <p>CHK APP</p> <p>SCALE 1:1 SHEET 1 OF 2</p>	<p>ARMSTRONG HOLDEN BROOKE PULLEN</p> <p>WENLOCK WAY, MANCHESTER. M12 5JL TEL: +44 (0) 161 223 2223</p>
<p>ISSUE DATE 1/07/2006 DRN BSD</p> <p>C CHK BSD APP BSD</p>		<p>THIS DRAWING IS THE PRIVATE AND CONFIDENTIAL PROPERTY OF ARMSTRONG HOLDEN BROOKE PULLEN LTD. ALL COPYRIGHT, MANUFACTURING AND SALES RIGHTS RESERVED.</p>						