


EXHAUST SYSTEM | SUBMITTAL DRAWING


File No: F43.456IN
 Date: DEC. 16, 2014
 Supersedes: NEW
 Date: MAY 30, 2014

Job: _____ Representative: _____
 _____ Ordered by: _____ Date: _____
 Engineer: _____ Submitted by: _____ Date: _____
 Contractor: _____ Approved by: _____ Date: _____

**TYPE 1
 NPT MALE**



**TYPE 2
 ANSI 150# FLANGES**



NOTE:
 If pipe length between engine exhaust and silencer is more than 15 feet, silencer may need to be larger than indicated sizes. Refer to factory.

SILENCERS


ENGINE MANUFACTURER	TYPE	CONNECTION SIZE	ENGINE MODEL	A	B	C	D
Clarke	1	3" NPT	JU4H-UF10, 12, 14, 20, 22, 24	76 (3.00)	203 (8.00)	508 (20.00)	660 (26.00)
	2	4" flanged (150#)	JU4H-UF34, H0, H2, 40, 42, 50, 52, 54, 58, AD5G, ADPO, ADRO, ADW8, ADY8, AEAO, AEE8, AEF2, ADJ8, ADJ2, AD98	102 (4.00)	254 (10.00)	635 (25.00)	787 (31.00)
		5" flanged (150#)	JU6H-UF34, 54, AB76, 84, DO, D2, 30, 32, M8, M0, M2, 58, 50, 52, 60, 62, AAQ8, AARG, AD58, ADNG, ADNO, ADP8, AD88, ADMG, AAPG, AASO	127 (5.00)	305 (12.00)	762 (30.00)	965 (38.00)
			DP6H-UFAA50, AA62, AA88, AAX8				
		5" flanged (150#) quantity 2 per engine	DR8H-UFAA40, AA5G, AA68, AA62	152 (6.00)	356 (14.00)	889 (35.00)	1092 (43.00)
			DSOH-UFAANO, AA68, AA60, AAMO, AA98, AA92				
		6" flanged (150#)	JU6H-UFADPO, ADQO, ADR8, ADRO, ADS8, ADSO, ADW8, ADTO, ADX8, AD98	152 (6.00)	356 (14.00)	889 (35.00)	1092 (43.00)
			JW6H-UFAA60, AA80, ADFO, ADJO, AD70, AD80				
	DP6H-UFAA70						
	6" flanged (150#) quantity 2 per engine	DT2H-UFAA20, AA58, AA50, AA60, AA88, AA98, AA92	203 (8.00)	457 (18.00)	1143 (45.00)	1346 (53.00)	
	8" flanged (150#)	JX6H-UFADFO, AD60, ADNO, ADPO, AD88					

NOTES:

- 1 Dimensions are not to be used for construction purpose unless certified.
- 2 Data subject to change without notice.
- 3 All dimensions are in mm (inches).

FLEXIBLE EXHAUST CONNECTORS

ENGINE MANUFACTURER	TYPE	CONNECTION SIZE	ENGINE MODEL
Clarke	B	3" NPT	JU4H-UF10, 12, 14, 20, 22, 24, AEA0, AEE8, AEF2, ADJ8, ADJ2
		4" NPT	JU4H-UF34, H0, H2, 40, 42, 50, 52, 54, 58, AD5G, ADPO, ADRO, ADW8, ADY8, AD98
	C	5" flanged (150#)	JU6H-UF34, 54, AB76, 84, D0, D2, 30, 32, M8, M0, M2, 58, 50, 52, 60, 62, AAQ8, AARG, AD58, ADNG, ADNO, ADP8, AD88, ADMG, AAPG, AASO
			DP6H-UFAA50, AA62, AA88, AAX8
	H	5" flanged (150#) Quantity 2 per engine	DR8H-UFAA40, AA5G, AA68, AA62
			DSOH-UFAANO, AA68, AA60, AAMO, AA98, AA92
	C	6" flanged (150#)	JU6H-UFADPO, ADQ0, ADR8, ADRO, ADS8, ADSO, ADW8, ADTO, ADX8, AD98
			JW6H-UFAA60, AA80, ADF0, ADJO, AD70, AD80
	H	6" flanged (150#)	DP6H-UFAA70
			DQ6H-UFAA50, AA60, AA88, AA98
	H	6" flanged (150#) Quantity 2 per engine	DT2H-UFAA20, AA58, AA50
	A	8" flanged (150#)	JX6H-UFADFO, AD60, ADNO, ADPO, AD88
	H	8" flanged (150#) Quantity 2 per engine	DT2H-UFAA60, AA88, AA98, AA92



TORONTO

23 BERTRAND AVENUE
TORONTO, ONTARIO
CANADA
M1L 2P3
+1 416 755 2291

BUFFALO

93 EAST AVENUE
NORTH TONAWANDA, NEW YORK
U.S.A.
14120-6594
+1 716 693 8813

BIRMINGHAM

HEYWOOD WHARF, MUCKLOW HILL
HALESOWEN, WEST MIDLANDS
UNITED KINGDOM
B62 8DJ
+44 (0) 8444 145 145

MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM
M11 2ET
+44 (0) 8444 145 145

BANGALORE

#59, FIRST FLOOR, 3RD MAIN
MARGOSA ROAD, MALLESWARAM
BANGALORE, INDIA
560 003
+91 (0) 80 4906 3555

SHANGHAI

NO. 1619 HU HANG ROAD, XI DU TOWNSHIP
FENG XIAN DISTRICT, SHANGHAI
P.R.C.
201401
+86 21 3756 6696