



DIMENSIONS SHOWN AS: Inches (mm)

EXCHANGER SIZE	DIMENSIONS								NOZZLE SCHEDULE		
	"A"		"B"		"C"		"D"		(N1) INLET	6" NPT (152)	
	Inches	mm	Inches	mm	Inches	mm	Inches	mm	(N2) OUTLET	3" NPT (76)	
THSX-1636-2-1	44 -1/8	1121	35-1/2	902	38	965	24-1/2	622	(N3) VENTS	1/2" NPT (13)	
THSX-1642-2-1	50 -1/8	1273	41-1/2	1054	44	1118	30-1/2	775	COLLAR ASSEMBLY		
THSX-1648-2-1	56 -1/8	1426	47-1/2	1207	50	1270	36-1/2	927	STANDARD		OVS. FOR STONE LINING
THSX-1654-2-1	62 -1/8	1578	53-1/2	1359	56	1422	42-1/2	1080	"E"	16 (406)	18 (457)
THSX-1660-2-1	68 -1/8	1730	59-1/2	1511	62	1575	48-1/2	1232	"F"	12 (305)	12 1/2 (318)
THSX-1666-2-1	74 -1/8	1883	65-1/2	1664	68	1727	54-1/2	1384	DESIGN CONDITIONS		
THSX-1672-2-1	80 -1/8	2035	71-1/2	1816	74	1880	60-1/2	1537	TUBES		
THSX-1678-2-1	86 -1/8	2188	77-1/2	1969	80	2032	66-1/2	1689	DESIGN PRESSURE	125 PSIG	862 KPa
THSX-1684-2-1	92 -1/8	2340	83-1/2	2121	86	2184	72-1/2	1842	DESIGN TEMPERATURE	375 F	191 C
THSX-1690-2-1	98 -1/8	2492	89-1/2	2273	92	2337	78-1/2	1994	M.D.M.T.	40 F	4.4 C
THSX-1696-2-1	104 -1/8	2645	95-1/2	2426	98	2489	84-1/2	2146	HYD. TEST PRESSURE	250 PSIG	1723 KPa
THSX-16102-2-1	110 -1/8	2797	101-1/2	2578	104	2642	90-1/2	2299	NOTES:		
THSX-16108-2-1	116 -1/8	2950	107-1/2	2731	110	2794	96-1/2	2451	1. COLLAR ASSEMBLY SUPPLIED SEPARATELY.		
THSX-16114-2-1	122 -1/8	3102	113-1/2	2883	116	2946	102-1/2	2604	2. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.		
THSX-16120-2-1	128 -1/8	3254	119-1/2	3035	122	3099	108-1/2	2756	3. DRAWING IS NOT TO SCALE.		
THSX-16126-2-1	134 -1/8	3407	125-1/2	3188	128	3251	114-1/2	2908	4. ALL DIMN'S 1/8 (3) UNLESS OTHERWISE SHOWN.		
THSX-16132-2-1	140 -1/8	3559	131-1/2	3340	134	3404	120-1/2	3061	5. DIMENSIONS SHOWN AS: In.(mm)		
THSX-16138-2-1	146 -1/8	3712	137-1/2	3493	140	3556	126-1/2	3213	CUSTOMER:		
THSX-16144-2-1	152 -1/8	3864	143-1/2	3645	146	3708	132-1/2	3366	LOCATION:		
THSX-16150-2-1	158 -1/8	4016	149-1/2	3797	152	3861	138-1/2	3518	ENGINEER :		
THSX-16156-2-1	164 -1/8	4169	155-1/2	3950	158	4013	144-1/2	3670	ORDER No.:		
THSX-16162-2-1	170 -1/8	4321	161-1/2	4102	164	4166	150-1/2	3823	PROJECT/JOB:		
									LOCATION:		
									TAG:		
									QUOTE #		

TITLE G.A. 150 LB. TANK HEATERS

ARMSTRONG

NUMBER

REV.

DATE : 24/05/95

BY : D.C.R

TORONTO - CANADA
TEL : (416) 755-2291

MONTREAL - CANADA
TEL : (514) 421-2424

BUFFALO - N. Y.
TEL : (716) 693-8813

COLCHESTER - U.K.
TEL : (44) 120-657-9491

Thsx-16-2P-1