



DIMENSIONS SHOWN AS: inches (mm)

EXCHANGER SIZE	DIMENSIONS								NOZZLE SCHEDULE		
	"A"		"B"		"C"		"D"		N1	N2	N3
	Inches	mm	Inches	mm	Inches	mm	Inches	mm			
THSX-612-2-3	14 -1/4	362	11-3/8	289	13	330	-	-	2" NPT (51)	1" NPT (25)	1/2" NPT (13)
THSX-618-2-3	20 -1/4	514	17-3/8	441	19	483	-	-	COLLAR ASSEMBLY		
THSX-624-2-3	26 -1/4	667	23-3/8	594	25	635	12-1/8	308	STANDARD	OVS. FOR STONE LINING	
THSX-630-2-3	32 -1/4	819	29-3/8	746	31	787	18-1/8	460	"E"	6 5/8" (168)	8 5/8" (219)
THSX-636-2-3	38 -1/4	972	35-3/8	899	37	940	24-1/8	613	"F"	6-1/2" (165)	8" (203)
THSX-642-2-3	44 -1/4	1124	41-3/8	1051	43	1092	30-1/8	765	DESIGN CONDITIONS		
THSX-648-2-3	50 -1/4	1276	47-3/8	1203	49	1245	36-1/8	918	TUBES		
THSX-654-2-3	56 -1/4	1429	53-3/8	1356	55	1397	42-1/8	1070	DESIGN PRESSURE	150 PSIG	1034 KPa
THSX-660-2-3	62 -1/4	1581	59-3/8	1508	61	1549	48-1/8	1222	DESIGN TEMPERATURE	375 F	191 C
THSX-666-2-3	68 -1/4	1734	65-3/8	1661	67	1702	54-1/8	1375	M.D.M.T.	35 F	1.7 C
THSX-672-2-3	74 -1/4	1886	71-3/8	1813	73	1854	60-1/8	1527	HYD. TEST PRESSURE	225 PSIG	1551 KPa
THSX-678-2-3	80 -1/4	2038	77-3/8	1965	79	2007	66-1/8	1680	NOTES:		
THSX-684-2-3	86 -1/4	2191	83-3/8	2118	85	2159	72-1/8	1832	1. COLLAR ASSEMBLY SUPPLIED SEPARATELY.		
THSX-690-2-3	92 -1/4	2343	89-3/8	2270	91	2311	78-1/8	1984	2. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.		
THSX-696-2-3	98 -1/4	2496	95-3/8	2423	97	2464	84-1/8	2137	3. DRAWING IS NOT TO SCALE.		
THSX-6102-2-3	104 -1/4	2648	101-3/8	2575	103	2616	90-1/8	2289	4. ALL DIM'S 1/8 (3) UNLESS OTHERWISE SHOWN.		
THSX-6108-2-3	110 -1/4	2800	107-3/8	2727	109	2769	96-1/8	2442	5. DIMENSIONS SHOWN AS: in.(mm)		
THSX-6114-2-3	116 -1/4	2953	113-3/8	2880	115	2921	102-1/8	2594	CUSTOMER: LOCATION: ENGINEER : ORDER No.: PROJECT/JOB: LOCATION: TAG: QUOTE #		
THSX-6120-2-3	122 -1/4	3105	119-3/8	3032	121	3073	108-1/8	2746			
THSX-6126-2-3	128 -1/4	3258	125-3/8	3185	127	3226	114-1/8	2899			
THSX-6132-2-3	134 -1/4	3410	131-3/8	3337	133	3378	120-1/8	3051			
THSX-6138-2-3	140 -1/4	3562	137-3/8	3489	139	3531	126-1/8	3204			