

File No.	6052.126
Date:	October 28, 2003
Supersedes:	6052.126
Date:	January 20, 2003

# **ARMSTRONG**

# **PARTS LIST**

# **SERIES 5400**


**SEWAGE PUMP**

**FOR PUMPS  
SERIAL NUMBER 71854 AND LATER**

**NEW DESIGN**



# 5400 SEWAGE PUMP PARTS IDENTIFICATION



ITEM	DESCRIPTION	PAGE	ITEM	DESCRIPTION	PAGE	ITEM	DESCRIPTION	PAGE
101	Volute	2	225	Int. Brg. Capscrew	10	347	Lubrication Tubing (Grease)	19
102	Impeller	2	226	Int. Brg. Caps. Washer	10	347	Lubrication Tubing (Oil)	20
104	Volute Capscrew	10	303	Thrust Bearing	4	348	Brg. Collar Threaded	6
106	Discharge Flange	2	304	Int. Bearing Assy.	4	349	Brg. Frame Screw	10
107	Discharge Flange Gasket	2	305	Int. Bearing Only	4	401	Coupler	6
108	Flange Nut	10	316	Retaining Ring (external)	4	503	Floor Plate	6
109	Flange Bolt	10	317	Retaining Ring (internal)	5	606	Float Switch	7
116	Impeller Nut	3	321	Oil Seal	5	607	Switch Stand	7
118	Imp. Nut Lockwasher	3	331	Grease Fitting	5	608	Float Rod Guide	8
124	Discharge Pipe 3D	11	333	Locknut	5	609	Float Rod (Brass)	21
124	Discharge Pipe 4D	12	338	Shaft 3D (Steel)	15	609	Float Rod (SST)	22
124	Discharge Pipe 4E	12	338	Shaft 3D (304 S/S)	16	610	Float	8
128	Dis. Pipe Caps. & Washer	10	338	Shaft 4D & 4E (Steel)	17	612	Stop & Set Screws	8
201	Cvrplt. & Lwr. Brg. Assy.	3	338	Shaft 4D & 4E (304 S/S)	18	614	Sw. Stand Screw & Wshr.	10
201A	Lower Bearing Only	3	340	Impeller Key	5	615	Guide Capscrew	10
202	Coverplate Capscrew	10	341	Coupler Key	5	616	Float Sw. Screw & Wshr.	10
206	Motor Support	4	343	Pipe Nipple	5	617	Float Switch Nut	10
207	Motor Caps. & Washer	10	344	Pipe Coupling	5	618	Water Slinger	6
223	Support Caps. & Washer	10	345	Tube Connector	6	619	Packing Gland Cover	8
224	Pump Leg 3D	13	346	Street Elbow	6	620	Packing (5 Rings Req'd)	8
224	Pump Leg 4D & 4E	14		Oil Lub. Accessories	9			

# SEWAGE PUMP PARTS LIST SERIES 5400

<b>ITEM 101 VOLUTE</b>			
PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
3D	A.I./B.F.	440516-011	
4D	A.I./B.F.	441256-011	
4E	A.I./B.F.	441251-011	

<b>ITEM 102 IMPELLER**</b>			
PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
3D	A.I	440518-011	
3D	B.F.	440518-041	
4D	A.I	441296-011	
4D	B.F.	441296-041	
4E	A.I	441252-011	
4E	B.F.	441252-041	

**\*\* NOTES:** Impeller Part Numbers are for full or maximum diameter Impellers. Specify the Serial Number when ordering and, where possible, advise the diameter of the Impeller being replaced

<b>ITEM 106 DISCHARGE FLANGE</b>			
PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
3D	A.I./B.F.	440081-010	
4D	A.I./B.F.	441254-010	
4E	A.I./B.F.	441254-010	

<b>ITEM 107 DISCHARGE FLANGE GASKET</b>			
PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
3D	A.I./B.F.	440162-000	
4D	A.I./B.F.	440198-000	
4E	A.I./B.F.	440198-000	

# SEWAGE PUMP PARTS LIST SERIES 5400

<b>ITEM 116 IMPELLER NUT</b>			
PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
3D	A.I./B.F.	441269-000	
4D			
4E			

<b>ITEM 118 IMPELLER NUT LOCKWASHER</b>			
PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
ALL SIZES	A.I./B.F.	927217-100	

<b>ITEM 201 COVERPLATE &amp; LOWER BRG. ASSY.</b>			
PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
3D & 4D	A.I./B.F. (Std. Grs. Lub.)	440496-012	
4E	A.I./B.F. (Std. Grs. Lub.)	441250-012	
3D & 4D	A.I./B.F. (Cutlass Rubber)	440496-014	
4E	A.I./B.F. (Cutlass Rubber)	441250-014	
3D & 4D	A.I./B.F. (Carbon)	440496-082	
4E	A.I./B.F. (Carbon)	441250-082	
3D & 4D	A.I./B.F. (Oil Lub.)	441438-012	
4E	A.I./B.F. (Oil Lub.)	441439-012	

<b>ITEM 201A LOWER BEARING ONLY</b>			
PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
ALL SIZES	A.I./B.F. (Std. Grs. Lub.)	441260-012	
ALL SIZES	A.I./B.F. (Carbon)	441436-000	
ALL SIZES	A.I./B.F. (Cutlass)	441418-003	

# SEWAGE PUMP PARTS LIST SERIES 5400

<b>ITEM 206 MOTOR SUPPORT</b>			
MOTOR FRAME SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
56 C	A.I./B.F.	441639-011	
143 TC - 145 TC	A.I./B.F.	441639-011	
182 TC - 184 TC	A.I./B.F.	441656-011	
213 TC - 215 TC	A.I./B.F.	441656-011	
254TC - 256 TC	A.I./B.F.	441656-011**	
<b>**NOTE: Also requires Spacer Part Number 441243-001</b>			

<b>ITEM 303 THRUST BALL BEARING</b>			
PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
ALL SIZES	A.I./B.F.	971101-364	

<b>ITEM 304 INTERMEDIATE BRG.ASSY.</b>			
PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
ALL SIZES	A.I./B.F. (Std. Oil & Grs. Lub.)	440991-012	
ALL SIZES	A.I./B.F. (Cutlass)	440991-014	
ALL SIZES	A.I./B.F. (Carbon)	440991-082	

<b>ITEM 305 INTERMEDIATE BRG. ONLY</b>			
PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
ALL SIZES	A.I./B.F. (Std. Oil & Grs. Lub.)	441260-011	
ALL SIZES	A.I./B.F. (Cutlass)	441418-003	
ALL SIZES	A.I./B.F. (Carbon)	441436-000	

<b>ITEM 316 RETAINING RING (external)</b>			
PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
ALL SIZES	A.I./B.F.	923104-116	

# SUMP PUMP PARTS LIST SERIES 5400

## ITEM 317 RETAINING RING (internal)

PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
ALL SIZES	A.I./B.F.	923100-059	

## ITEM 321 OIL SEAL

PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
ALL SIZES	A.I./B.F.	965000-209	

## ITEM 331 GREASE FITTING

PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
ALL SIZES	A.I./B.F.	425030-011	

## ITEM 333 LOCKNUT

PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
ALL SIZES	A.I./B.F.	913608-100	

## ITEM 340 IMPELLER KEY

PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
ALL SIZES	A.I./B.F.	974515-100	

## ITEM 341 COUPLER KEY

PUMP SIZE	SIZE	PART NUMBER	BAR CODE
ALL SIZES	3/8" SQ.x1 1/2" LG.	428160-112	

## ITEM 343 PIPE NIPPLE

PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
ALL SIZES	A.I./B.F.	938000-000	

## ITEM 344 GREASE LINE COUPLING

PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
ALL SIZES	A.I./B.F.	931104-000	

# SEWAGE PUMP PARTS LIST SERIES 5400

<b>ITEM 345 TUBE CONNECTOR (mips)</b>			
PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
ALL SIZES	A.I./B.F.	939001-105	

<b>ITEM 346 TUBE CONNECTOR ELBOW (mips)</b>			
PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
ALL SIZES	A.I./B.F.	931100-000	

<b>ITEM 348 BEARING COLLAR THREADED</b>			
PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
ALL SIZES	A.I./B.F.	441641-000	

<b>ITEM 401 COUPLER</b>			
MOTOR FRAME SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
56 C	A.I./B.F.	841060-011	
143 TC - 145 TC	A.I./B.F.	841060-012	
182 TC - 184 TC	A.I./B.F.	841300-011	
213 TC - 215 TC	A.I./B.F.	841301-012	
254 TC - 256 TC	A.I./B.F.	841302-011	

<b>ITEM 503 FLOOR PLATE</b>			
PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
3D	A.I./B.F.	440984-003	
4D	A.I./B.F.	441311-003	
4E	A.I./B.F.	441266-003	

<b>ITEM 618 WATER SLINGER</b>			
PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
ALL SIZES	A.I./B.F.	406622-000	



# SEWAGE PUMP PARTS LIST SERIES 5400

<b>FLOAT SWITCH ACCESSORIES</b>				
<b>ITEM 606 FLOAT SWITCH</b>				
CLASS	ENCLOSURE	NEMA SIZE TYPE	PART NUMBER (ALL SIZES)	BAR CODE
9036	GEN. PURPOSE	NEMA 1 GG-2	440457-003	
	WATER TIGHT	NEMA 4 DW-1	440457-004	
	EXPL. PROOF	NEMA 7 DR-1	440457-002	
<b>ITEM 606 FLOAT SWITCH c/w MECH. ALT.</b>				
CLASS	ENCLOSURE	NEMA SIZE TYPE	PART NUMBER (ALL SIZES)	BAR CODE
9038	GEN. PURPOSE	NEMA 1 AG-1	440458-000	
	WATER TIGHT	NEMA 4 AW-1	440458-001	
	EXPL. PROOF	NEMA 7 AR-1	440458-002	
<b>ITEM 607 SWITCH STAND</b>				
PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE	
ALL SIZES	A.I./B.F.	441080-011		

# SEWAGE PUMP PARTS LIST SERIES 5400

## FLOAT SWITCH ACCESSORIES (Cont'd)

### ITEM 608 FLOAT ROD GUIDE ASSY.

PUMP SIZE	SUMP DEPTH	PART NUMBER	BAR CODE
ALL SIZES	2' - 0" TO 5' - 0"	441279-011	
	5' - 6" TO 7' - 6"	441279-012	
	8' - 0" TO 10' - 0"	441279-013	
	10' - 6" TO 12' - 0"	441279-014	

### ITEM 610 FLOAT

PUMP SIZE	MATERIAL	PART NUMBER	BAR CODE
ALL SIZES	COPPER	440460-041	
	STAINLESS STEEL	440460-071	

### ITEM 612 FLOAT STOP (c/w Set Screws)

PUMP SIZE	MATERIAL	PART NUMBER	BAR CODE
ALL SIZES	BRASS	440462-000	
	304 S/S	440462-071	

### ITEM 619 PACKING GLAND COVER

PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
ALL SIZES	A.I./B.F.	441640-000	

### ITEM 620 PACKING RING ( 5 req'd)

PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE
ALL SIZES	A.I./B.F.	966201-000	

# SEWAGE PUMP PARTS LIST SERIES 5400

<b>OIL LUBRICATION ACCESSORIES</b>				
<b>OILERS***</b>				
OILER TYPE	OILER SIZE	NUMBER OF FEEDS	PART NUMBER	BAR CODE
MANUAL	1 PINT	1	441329-001	
		2	441329-002	
		3	441329-003	
MANUAL	1 QUART	1	441330-001	
		2	441330-002	
		3	441330-003	
AUTOMATIC	1 PINT	1	441339-001	
		2	441339-002	
		3	441339-003	
AUTOMATIC	1 QUART	1	441340-001	
		2	441340-002	
		3	441340-003	
***NOTES: Automatic Oiler Part Numbers For 110Volt/1 Phase/60 Cycle only				
<b>OILER MOUNTING BRACKET</b>				
PUMP SIZE	CONSTRUCTION	PART NUMBER	BAR CODE	
ALL SIZES	A.I./B.F.	440467-000		

# SEWAGE PUMP PARTS LIST SERIES 5400

<b>HARDWARE (all sizes)</b>					
ITEM NO.	DESCRIPTION	SIZE	NO. REQ'D	PART NUMBER	BAR CODE
104	VOLUTE CAPSCREW				
	MODELS 3D & 4D	3/8"-16X1"	8	911121-108	
	MODEL 4E	7/16"-14X1"	12	911125-108	
108	FLANGE NUT	5/8"-11	2	913129-100	
109	FLANGE BOLT	5/8"-11X3 1/2"	2	911129-128	
128	DISCHARGE FLG. CAPSCREW	5/8"-11X1 3/4"	2	911129-114	
128	DISCH. FLG. WASHER	5/8"	2	927122-100	
202	COVERPLATE CAPSCREW	5/8"-11X1 1/4"	4	911129-110	
207	MOTOR CAPSCREW				
	FRAMES 56C TO 145TC	3/8"- 16x1 1/4"	4	911121-110	
	182 TO 184TC	1/2"-13x1"	4	911125-108	
	213 TO 256TC	1/2"-13x1 1/4"	4	911125-110	
207	MOTOR CAPSCREW WASHER				
	FRAMES 56C TO 145TC	3/8"	4	927114-100	
	FRAMES 182-184TC to	1/2"	4	927118-100	
223	SUPPORT CAPSCREW	1/2"-13X1 1/2"	2	911121-108	
223	SUPPORT WASHER	1/2"	2	927118-100	
225	INT. BRG. ASSY. CAPSCREWS	5/8"-11X3"	4	911129-124	
226	INT. BRG. CAPS. NUTS	5/8"	4	913125-100	
349	BEARING FRAME CAPSCREW	5/8"- 11x1 1/4"	4	911129-110	
614	SWITCH STAND CAPSCREW	1/2"- 13x7/8"	2	911125-107	
614	SWITCH STAND WASHER	1/2"	2	927117-100	
615	GUIDE CAPSCREW	3/8"- 16x1/2"	1	916521-712	
616	FLOAT SWITCH CAPSCREW	1/4"- 20X3/4"	4	911117-108	
616	FLOAT SWITCH WASHER	1/4"	4	927110-100	
617	FLOAT SWITCH NUT	1/4"- 20	4	913117-100	

# SEWAGE PUMP PARTS LIST SERIES 5400

<b>ITEM 124 DISCHARGE PIPE</b>			
<b>PUMP SIZE 3D</b>			
<b>SUMP DEPTH (ft. &amp; in.)</b>	<b>DISCHARGE PIPE LENGTH (in inches)</b>	<b>PART NUMBER</b>	<b>BAR CODE</b>
2'	15 1/2"	448066-015	
2" - 6"	21 1/2"	448066-021	
3'	27 1/2"	448066-027	
3' - 6"	33 1/2"	448066-033	
4'	39 1/2"	448066-039	
4' - 6"	45 1/2"	448066-045	
5'	49 5/8"	448066-049	
5' - 6"	55 5/8"	448066-055	
6'	61 5/8"	448066-061	
6' - 6"	67 5/8"	448066-067	
7'	73 5/8"	448066-073	
7' - 6"	79 5/8"	448066-079	
8'	85 5/8"	448066-085	
9'	98 3/4"	448066-098	
10'	110 3/4"	448066-110	
11'	122 3/4"	448066-122	
12'	134 3/4"	448066-134	

# SEWAGE PUMP PARTS LIST SERIES 5400

<b>ITEM 124 DISCHARGE PIPE (Cont'd)</b>			
<b>PUMP SIZES 4D &amp; 4E</b>			
<b>SUMP DEPTH (ft. &amp; in.)</b>	<b>DISCHARGE PIPE LENGTH (in inches)</b>	<b>PART NUMBER</b>	<b>BAR CODE</b>
2'	11 5/8"	448067-011	
2' - 6"	17 5/8"	448067-017	
3'	23 5/8"	448067-023	
3' - 6"	29 5/8"	448067-029	
4'	35 5/8"	448067-035	
4' - 6"	41 5/8"	448067-041	
5'	48 3/4"	448067-048	
5' - 6"	54 3/4"	448067-054	
6'	60 3/4"	448067-060	
6' - 6"	66 3/4"	448067-066	
7'	72 3/4"	448067-072	
7' - 6"	78 3/4"	448067-078	
8'	84 3/4"	448067-084	
9'	97 7/8"	448067-097	
10'	109 7/8"	448067-109	
11'	121 7/8"	448067-121	
12'	133 7/8"	448067-133	

# SEWAGE PUMP PARTS LIST SERIES 5400

<b>ITEM 220 &amp; 224 PUMP LEGS***</b>					
<b>PUMP SIZE 3 D</b>					
SUMP DEPTH (ft. & in.)	PUMP LEG PART NUMBER & QTY. REQ'D***				BAR CODE
	PART NUMBER	NO. REQ'D	PART NUMBER	NO. REQ'D	
2'	441263-002	1			
2' - 6"	441263-004	1			
3'	441263-006	1			
3' - 6"	441263-008	1			
4'	441263-010	1			
4' - 6"	441263-012	1			
5'	441263-005	2			
5' - 6"	441263-006	2			
6'	441263-007	2			
6' - 6"	441263-008	2			
7'	441263-009	2			
7' - 6"	441263-010	2			
8'	441263-011	2			
9'	441263-007	1	441263-008	2	
10'	441263-009	3			
11'	441263-010	2	441263-011	1	
12'	441263-011	1	441263-012	2	
<b>*** NOTES: LENGTHS OF PUMP LEGS:</b>					
441263-002 -- 15 3/16"	441263-007 -- 30 3/16"	441263-011 -- 42 3/16"			
441263-004 -- 21 3/16"	441263-008 -- 33 3/16"	441263-012 -- 45 3/16"			
441263-005 -- 24 3/16"	441263-009 -- 36 3/16"				
441263-006 -- 27 3/16"	441263-010 -- 39 3/16"				

# SEWAGE PUMP PARTS LIST SERIES 5400

<b>ITEM 220 &amp; 224 PUMP LEGS***</b>					
<b>PUMP SIZE 4D &amp; 4E</b>					
SUMP DEPTH (ft. & in.)	PUMP LEG PART NUMBER & QTY. REQ'D***				BAR CODE
	PART NUMBER	NO. REQ'D	PART NUMBER	NO. REQ'D	
2'	441263-001	1			
2' - 6"	441263-003	1			
3'	441263-005	1			
3' - 6"	441263-007	1			
4'	441263-009	1			
4' - 6"	441263-011	1			
5'	441263-005	2			
5' - 6"	441263-006	2			
6'	441263-007	2			
6' - 6"	441263-008	2			
7'	441263-009	2			
7' - 6"	441263-010	2			
8'	441263-011	2			
9'	441263-007	1	441263-008	2	
10'	441263-009	3			
11'	441263-010	2	441263-011	1	
12'	441263-011	1	441263-012	2	
<b>*** NOTES: LENGTHS OF PUMP LEGS:</b>					
441263-001 -- 12"	441263-005 -- 24 3/16"		441263-011 -- 42 3/16"		
441263-002 -- 15 3/16"	441263-006 -- 27 3/16"		441263-012 -- 45 3/16"		
441263-003 -- 18"	441263-007 -- 30 3/16"		441263-011 -- 42 3/16"		
441263-004 -- 21 3/16"	441263-008 -- 33 3/16"		441263-012 -- 45 3/16"		



# SEWAGE PUMP PARTS LIST SERIES 5400

<b>ITEM 338 SHAFT (STEEL SHAFT MATERIAL)**</b>			
<b>PUMP SIZE 3D</b>			
<b>SUMP DEPTH (ft. &amp; in.)</b>	<b>SHAFT LENGTH (in inches)</b>	<b>PART NUMBER</b>	<b>BAR CODE</b>
2'	28 1/32"	441642-002	
2' - 6"	34 1/32"	441642-004	
3'	40 1/32"	441642-006	
3' - 6"	46 1/32"	441642-008	
4'	52 1/32"	441642-010	
4' - 6"	58 1/32"	441642-012	
5'	62 5/32"	441642-013	
5' - 6"	68 5/32"	441642-015	
6'	74 5/32"	441642-017	
6' - 6"	80 5/32"	441642-019	
7'	86 5/32"	441642-021	
7' - 6"	92 5/32"	441642-023	
8'	98 5/32"	441642-025	
9'	111 9/32"	441642-027	
10'	123 9/32"	441642-029	
11'	135 9/32"	441642-031	
12'	147 9/32"	441642-033	

\*\* FOR STAINLESS STEEL SHAFTS SEE PAGE 16

# SEWAGE PUMP PARTS LIST SERIES 5400

<b>ITEM 338 SHAFT (304 S/S SHAFT MATERIAL)**</b>			
<b>PUMP SIZE 3D</b>			
<b>SUMP DEPTH (ft. &amp; in.)</b>	<b>SHAFT LENGTH (in inches)</b>	<b>PART NUMBER</b>	<b>BAR CODE</b>
2'	28 1/32"	441642-702	
2" - 6"	34 1/32"	441642-704	
3'	40 1/32"	441642-706	
3' - 6"	46 1/32"	441642-708	
4'	52 1/32"	441642-710	
4' - 6"	58 1/32"	441642-712	
5'	62 5/32"	441642-713	
5' - 6"	68 5/32"	441642-715	
6'	74 5/32"	441642-717	
6' - 6"	80 5/32"	441642-719	
7'	86 5/32"	441642-721	
7' - 6"	92 5/32"	441642-723	
8'	98 5/32"	441642-725	
9'	111 9/32"	441642-727	
10'	123 9/32"	441642-729	
11'	135 9/32"	441642-731	
12'	147 9/32"	441642-733	

\*\* FOR STEEL SHAFTS SEE PAGE 15

# SEWAGE PUMP PARTS LIST SERIES 5400

<b>ITEM 338 SHAFT (STEEL SHAFT MATERIAL)**</b>			
<b>PUMP SIZES 4D &amp; 4E</b>			
<b>SUMP DEPTH (ft. &amp; in.)</b>	<b>SHAFT LENGTH (in inches)</b>	<b>PART NUMBER</b>	<b>BAR CODE</b>
2'	25 1/32"	441642-001	
2" - 6"	31 1/32"	441642-003	
3'	37 1/32"	441642-005	
3' - 6"	43 1/32"	441642-007	
4'	49 1/32"	441642-009	
4' - 6"	55 1/32"	441642-011	
5'	62 5/32"	441642-013	
5' - 6"	68 5/32"	441642-015	
6'	74 5/32"	441642-017	
6' - 6"	80 5/32"	441642-019	
7'	86 5/32"	441642-021	
7' - 6"	92 5/32"	441642-023	
8'	98 5/32"	441642-025	
9'	111 9/32"	441642-027	
10'	123 9/32"	441642-029	
11'	135 9/32"	441642-031	
12'	147 9/32"	441642-033	

**\*\* FOR STAINLESS STEEL SHAFTS SEE PAGE 18**

# SEWAGE PUMP PARTS LIST SERIES 5400

<b>ITEM 338 SHAFT (304 S/S SHAFT MATERIAL)**</b>			
<b>PUMP SIZE 4D &amp; 4E</b>			
<b>SUMP DEPTH (ft. &amp; in.)</b>	<b>SHAFT LENGTH (in inches)</b>	<b>PART NUMBER</b>	<b>BAR CODE</b>
2'	25 1/32"	441642-701	
2' - 6"	31 1/32"	441642-703	
3'	37 1/32"	441642-705	
3' - 6"	43 1/32"	441642-707	
4'	49 1/32"	441642-709	
4' - 6"	55 1/32"	441642-711	
5'	62 5/32"	441642-713	
5' - 6"	68 5/32"	441642-715	
6'	74 5/32"	441642-717	
6' - 6"	80 5/32"	441642-719	
7'	86 5/32"	441642-721	
7' - 6"	92 5/32"	441642-723	
8'	98 5/32"	441642-725	
9'	111 9/32"	441642-727	
10'	123 9/32"	441642-729	
11'	135 9/32"	441642-731	
12'	147 9/32"	441642-733	

\*\* FOR STEEL SHAFTS SEE PAGE 17

# SEWAGE PUMP PARTS LIST SERIES 5400

<b>ITEM 347 LUBRICATION TUBING**</b>			
<b>GREASE LUBRICATION***</b>			
SUMP DEPTH (ft. & in.)	TUBING LENGTH (in inches)	PART NUMBER	BAR CODE
2'	27"	997529-003	
2' - 6"	27"	997529-003	
3'	33"	997529-003	
3' - 6"	39"	997529-003	
4'	45"	997529-003	
4' - 6"	51"	997529-003	
5'	90"	997529-003	
5' - 6"	99"	997529-003	
6'	108"	997529-003	
6' - 6"	117"	997529-003	
7'	126"	997529-003	
7' - 6"	135"	997529-003	
8'	144"	997529-003	
9'	189"	997529-003	
10'	210"	997529-003	
11'	231"	997529-003	
12'	252"	997529-003	

**\*\* NOTES:** When ordering Lubrication Tubing you must order by the Part Number followed by the tubing length as illustrated above.

**\*\*\* NOTES:** For Oil Lubrication see Page 20

# SEWAGE PUMP PARTS LIST SERIES 5400

<b>ITEM 347 LUBRICATION TUBING**</b>			
<b>OIL LUBRICATION***</b>			
SUMP DEPTH (ft. & in.)	TUBING LENGTH (in inches)	PART NUMBER	BAR CODE
2'	39"	997302-003	
2' - 6"	39"	997302-003	
3'	45"	997302-003	
3' - 6"	51"	997302-003 (	
4'	57"	997302-003	
4' - 6"	63"	997302-003	
5'	102"	997302-003	
5' - 6"	111"	997302-003	
6'	120"	997302-003	
6' - 6"	129"	997302-003	
7'	138"	997302-003	
7' - 6"	147"	997302-003	
8'	156"	997302-003	
9'	201"	997302-003	
10'	222"	997302-003	
11'	243"	997302-003	
12'	264"	997302-003	

**\*\* NOTES:** When ordering Lubrication Tubing you must order by the Part Number followed by the tubing length as illustrated above.

**\*\*\* NOTES:** For grease Lubrication see Page 19

# SEWAGE PUMP PARTS LIST SERIES 5400

<b>ITEM 609 FLOAT ROD</b>			
<b>SUMP DEPTH (ft. &amp; in.)</b>	<b>FLOAT ROD LENGTH (in inches)</b>	<b>PART NUMBER ADM. BRASS</b>	<b>BAR CODE</b>
2'	27"	997407-034	
2' - 6"	32"	997407-034	
3'	38"	997407-034	
3' - 6"	44"	997407-034	
4'	50"	997407-034	
4' - 6"	56"	997407-034	
5'	62"	997407-034	
5' - 6"	68"	997407-034	
6'	74"	997407-034	
6' - 6"	80"	997407-034	
7'	86"	997407-034	
7' - 6"	92"	997407-034	
8'	98"	997407-034	
8' - 6"	104"	997407-034	
9'	110"	997407-034	
9' - 6"	116"	997407-034	
10'	122"	997407-034	
10' - 6"	128"	997407-034	
11'	134"	997407-034	
11' - 6"	140"	997407-034	
12'	146"	997407-034	

**\*\*\* NOTES; When ordering Float Rods you must order by the Part Number followed by the rod length as illustrated above.**

**\*\*\* NOTES; For Stainless Steel Float Rods see Page 22**

# SEWAGE PUMP PARTS LIST SERIES 5400

<b>ITEM 609 FLOAT ROD</b>			
<b>SUMP DEPTH</b> (ft. & in.)	<b>FLOAT ROD LENGTH</b> (in inches)	<b>PART NUMBER</b> 304 S/S	<b>BAR CODE</b>
2'	27"	997601-002	
2' - 6"	32"	997601-002	
3'	38"	997601-002	
3' - 6"	44"	997601-002	
4'	50"	997601-002	
4' - 6"	56"	997601-002	
5'	62"	997601-002	
5' - 6"	68"	997601-002	
6'	74"	997601-002	
6' - 6"	80"	997601-002	
7'	86"	997601-002	
7' - 6"	92"	997601-002	
8'	98"	997601-002	
8' - 6"	104"	997601-002	
9'	110"	997601-002	
9' - 6"	116"	997601-002	
10'	122"	997601-002	
10' - 6"	128"	997601-002	
11'	134"	997601-002	
11' - 6"	140"	997601-002	
12'	146"	997601-002	

**\*\*\* NOTES; When ordering Float Rods you must order by the Part Number followed by the rod length as illustrated above.**

**\*\*\* NOTES; For Brass Float Rods see Page 21**