

VERTICAL IN-LINE | 50 HZ | SELECTION CHARTS

File No: F43.205
Date: AUGUST 10, 2016
Supersedes: F43.213
Date: FEBRUARY 01, 2010

PUMP	FLOW USgpm (L/s)	SPEED rpm	PRESSURE RANGE PSI (kPa)		
			UL	ULC	FM
2×1.5 LA-F	50 (3)	2945	—	—	40 (276) – 92 (634)
	75 (5)	2945	—	—	40 (276) – 91 (627)
2×2×8 FM 43PF	50 (3)	2945	43 (296) – 86 (593)	43 (296) – 86 (593)	44 (303) – 86 (593)
	75 (5)	2945	—	—	44 (303) – 86 (593)
	100 (60)	2945	41 (283) – 86 (593)	41 (283) – 86 (593)	43 (296) – 86 (593)
2×2×8 43MF	50 (3)	2900	—	42 (290) – 84 (579)	—
	75 (5)	2900	—	42 (290) – 83.5 (576)	—
	100 (60)	2900	—	40 (276) – 83 (572)	—
	150 (9)	2900	—	40 (276) – 79 (545)	—
3×3×8 FM 43PF	200 (13)	2945	44 (303) – 83 (572)	44 (303) – 83 (572)	43 (296) – 83 (572)
	250 (16)	2945	42 (290) – 83 (572)	42 (290) – 83 (572)	42 (290) – 83 (572)
	300 (19)	2945	40 (276) – 82 (565)	40 (276) – 82 (565)	40 (276) – 82 (565)
6×4 LA-F	400(25)	2945	—	—	40 (276) – 91 (627)
8×8×15 FM	1000(63)	1480	49 (338) – 72 (496)	49 (338) – 72 (496)	49 (338) – 72 (496)
	1250(79)	1480	46 (317) – 70 (483)	46 (317) – 70 (483)	46 (317) – 70 (483)
8×8×16 FM	1000(63)	1480	56 (386) – 68 (469)	56 (386) – 68 (469)	56 (386) – 68 (469)
	1250(79)	1480	52 (359) – 64 (441)	52 (359) – 64 (441)	52 (359) – 64 (441)

TORONTO

23 BERTRAND AVENUE
TORONTO, ONTARIO
CANADA
M1L 2P3
+1 416 755 2291

BUFFALO

93 EAST AVENUE
NORTH TONAWANDA, NEW YORK
U.S.A.
14120-6594
+1 716 693 8813

BIRMINGHAM

HEYWOOD WHARF, MUCKLOW HILL
HALESOWEN, WEST MIDLANDS
UNITED KINGDOM
B62 8DJ
+44 (0) 8444 145 145

MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM
M11 2ET
+44 (0) 8444 145 145

BANGALORE

#59, FIRST FLOOR, 3RD MAIN
MARGOSA ROAD, MALLESWARAM
BANGALORE, INDIA
560 003
+91 (0) 80 4906 3555

SHANGHAI

NO. 1619 HU HANG ROAD, XI DU TOWNSHIP
FENG XIAN DISTRICT, SHANGHAI
P.R.C.
201401
+86 21 3756 6696

SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO,
1370 GALPÃO 6
EMBU DAS ARTES
SAO PAULO, BRAZIL
+55 11 4781 5500

ARMSTRONG FLUID TECHNOLOGY
ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM

**SAFETY
HAS A
HOME**