



EXCHANGER SIZE	DIMENSIONS								NOZZLE SCHEDULE		
	"A"		"B"		"C"		"D"		N1 INLET	6" FLG (152)	
	inches	mm	inches	mm	inches	mm	inches	mm	N2 OUTLET	6" FLG (152)	
THWX-1436-2-2	50 -5/8	1286	35-3/4	908	38	965	24-1/2	622	N3 DRAIN	1/2" NPT (13)	
THWX-1442-2-2	56 -5/8	1438	41-3/4	1060	44	1118	30-1/2	775	COLLAR ASSEMBLY		
THWX-1448-2-2	62 -5/8	1591	47-3/4	1213	50	1270	36-1/2	927	STANDARD OVS. FOR STONE LINING		
THWX-1454-2-2	68 -5/8	1743	53-3/4	1365	56	1422	42-1/2	1080	"E"	14" (356)	16" (406)
THWX-1460-2-2	74 -5/8	1895	59-3/4	1518	62	1575	48-1/2	1232	"F"	10-1/2" (267)	12" (305)
THWX-1466-2-2	80 -5/8	2048	65-3/4	1670	68	1727	54-1/2	1384	DESIGN CONDITIONS		
THWX-1472-2-2	86 -5/8	2200	71-3/4	1822	74	1880	60-1/2	1537	TUBES		
THWX-1478-2-2	92 -5/8	2353	77-3/4	1975	80	2032	66-1/2	1689	DESIGN PRESSURE	150 PSIG	1034 KPa
THWX-1484-2-2	98 -5/8	2505	83-3/4	2127	86	2184	72-1/2	1842	DESIGN TEMPERATURE	375 F	191 C
THWX-1490-2-2	104 -5/8	2657	89-3/4	2280	92	2337	78-1/2	1994	M.D.M.T.	40 F	4.4 C
THWX-1496-2-2	110 -5/8	2810	95-3/4	2432	98	2489	84-1/2	2146	HYD. TEST PRESSURE	300 PSIG	2068 KPa
THWX-14102-2-2	116 -5/8	2962	101-3/4	2584	104	2642	90-1/2	2299	NOTES:		
THWX-14108-2-2	122 -5/8	3115	107-3/4	2737	110	2794	96-1/2	2451	1. COLLAR ASSEMBLY SUPPLIED SEPARATELY.		
THWX-14114-2-2	128 -5/8	3267	113-3/4	2889	116	2946	102-1/2	2604	2. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.		
THWX-14120-2-2	134 -5/8	3419	119-3/4	3042	122	3099	108-1/2	2756	3. DRAWING IS NOT TO SCALE.		
THWX-14126-2-2	140 -5/8	3572	125-3/4	3194	128	3251	114-1/2	2908	4. ALL DIM'S 1/8 (3) UNLESS OTHERWISE SHOWN.		
THWX-14132-2-2	146 -5/8	3724	131-3/4	3346	134	3404	120-1/2	3061	5. DIMENSIONS SHOWN AS: in.(mm)		
THWX-14138-2-2	152 -5/8	3877	137-3/4	3499	140	3556	126-1/2	3213	CUSTOMER:		
THWX-14144-2-2	158 -5/8	4029	143-3/4	3651	146	3708	132-1/2	3366	LOCATION:		
THWX-14150-2-2	164 -5/8	4181	149-3/4	3804	152	3861	138-1/2	3518	ENGINEER :		
THWX-14156-2-2	170 -5/8	4334	155-3/4	3956	158	4013	144-1/2	3670	ORDER No.:		
THWX-14162-2-2	176 -5/8	4486	161-3/4	4108	164	4166	150-1/2	3823	PROJECT/JOB:		
									LOCATION:		
									TAG:		
									QUOTE #		

TITLE	G.A. 150 LB. TANK HEATERS				ARMSTRONG				NUMBER	Thwx-14-2P-2		REV.
DATE : 24/05/95	BY : D.C.R	TORONTO - CANADA	MONTREAL - CANADA	BUFFALO - N. Y.	COLCHESTER - U.K.	TEL : (416) 755-2291	TEL : (514) 421-2424	TEL : (716) 693-8813	TEL : (44) 120-657-9491			