



DIMENSIONS SHOWN AS: inches (mm)

EXCHANGER SIZE	DIMENSIONS								NOZZLE SCHEDULE		
	"A"		"B"		"C"		"D"		N1	INLET	2" FLG (51)
	Inches	mm	Inches	mm	Inches	mm	Inches	mm			
THWX-612-2-4	21 -7/8	556	11-3/8	289	13	330	-	-	N2	OUTLET	2" FLG (51)
THWX-618-2-4	27 -7/8	708	17-3/8	441	19	483	-	-	COLLAR ASSEMBLY		
THWX-624-2-4	33 -7/8	860	23-3/8	594	25	635	12-1/8	308		STANDARD	OVS. FOR STONE LINING
THWX-630-2-4	39 -7/8	1013	29-3/8	746	31	787	18-1/8	460	"E"	6 5/8" (168)	8 5/8" (219)
THWX-636-2-4	45 -7/8	1165	35-3/8	899	37	940	24-1/8	613	"F"	6-1/2" (165)	8" (203)
THWX-642-2-4	51 -7/8	1318	41-3/8	1051	43	1092	30-1/8	765	DESIGN CONDITIONS		
THWX-648-2-4	57 -7/8	1470	47-3/8	1203	49	1245	36-1/8	918	TUBES		
THWX-654-2-4	63 -7/8	1622	53-3/8	1356	55	1397	42-1/8	1070	DESIGN PRESSURE	150 PSIG	1034 KPa
THWX-660-2-4	69 -7/8	1775	59-3/8	1508	.61	1549	48-1/8	1222	DESIGN TEMPERATURE	375 F	191 C
THWX-666-2-4	75 -7/8	1927	65-3/8	1661	67	1702	54-1/8	1375	M.D.M.T.	35 F	1.7 C
THWX-672-2-4	81 -7/8	2080	71-3/8	1813	73	1854	60-1/8	1527	HYD. TEST PRESSURE	225 PSIG	1551 KPa
THWX-678-2-4	87 -7/8	2232	77-3/8	1965	79	2007	66-1/8	1680	NOTES:		
THWX-684-2-4	93 -7/8	2384	83-3/8	2118	85	2159	72-1/8	1832	1. COLLAR ASSEMBLY SUPPLIED SEPARATELY.		
THWX-690-2-4	99 -7/8	2537	89-3/8	2270	91	2311	78-1/8	1984	2. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.		
THWX-696-2-4	105 -7/8	2689	95-3/8	2423	97	2464	84-1/8	2137	3. DRAWING IS NOT TO SCALE.		
THWX-6102-2-4	111 -7/8	2842	101-3/8	2575	103	2616	90-1/8	2289	4. ALL DIM'S 1/8 (3) UNLESS OTHERWISE SHOWN.		
THWX-6108-2-4	117 -7/8	2994	107-3/8	2727	109	2769	96-1/8	2442	5. DIMENSIONS SHOWN AS: In.(mm)		
THWX-6114-2-4	123 -7/8	3146	113-3/8	2880	115	2921	102-1/8	2594	CUSTOMER:		
THWX-6120-2-4	129 -7/8	3299	119-3/8	3032	121	3073	108-1/8	2746	LOCATION:		
THWX-6126-2-4	135 -7/8	3451	125-3/8	3185	127	3226	114-1/8	2899	ENGINEER :		
THWX-6132-2-4	141 -7/8	3604	131-3/8	3337	133	3378	120-1/8	3051	ORDER No.:		
THWX-6138-2-4	147 -7/8	3756	137-3/8	3489	139	3531	126-1/8	3204	PROJECT/JOB:		
									LOCATION:		
									TAG:		
									QUOTE #		

TITLE G.A. 150 LB. TANK HEATERS	ARMSTRONG				NUMBER Thwx-6-2P-4	REV.
DATE : 12/02/94	BY : D.C.R	TORONTO - CANADA TEL : (416) 755-2291	MONTREAL - CANADA TEL : (514) 421-2424	BUFFALO - N. Y. TEL : (716) 693-8813	COLCHESTER - U.K. TEL : (44) 120-657-9491	