

# 3760 PRO 2MP FLOOR STANDING DIGITAL PRESSURISATION UNITS | TWIN PUMP | DATA SHEET

File No: 37.8513UK  
Date: JULY 13, 2023  
Supersedes: 37.8513UK  
Date: DECEMBER 21, 2022

## OVERVIEW

Compact and totally enclosed digital pressurisation units with electronic pressure transducer and user-friendly microprocessor for use on sealed system in order to provide a minimum system pressure requirement.

The Pro 2MP is a floor standing, flow rate (up to 18 l/min) top-up pressurisation unit with 18 litre internal break tank. Ideal for Industrial, commercial or large domestic applications.

## APPLICATION

Commercial, Industrial and Residential.

**System Volume (Guide): < 300,000 litres.**

## ADVANTAGES

### Product Features

- For system volumes up to 300,000 litres.
- Pressure setting in 0.1 bar increments.
- Dry Run Protection.
- Anti-Seize Routine (Pump is pulsed for 2 seconds if inactive for 60 days, must be enabled at time of commissioning).
- Electric pump, 230V 50Hz & 60Hz 1ph .
- Colour: Red (RAL 440-5).
- System fill mode.
- Onscreen Service Reminder - 12 Months.
- MODBUS RTU Communication Protocol.
- Password protected.
- Bi-directional programming menu.
- Flood Protection (Pump Runtime Limiter, Excessive Start Alarm).
- Pump pulse option.
- Event logging: Alarm activations, Pump Run counter (activations per pump), Cumulative run timer (hours per pump), Electrical interruption.
- Volt free contacts: Common Alarm (N/C), High Pressure Alarm (N/O), Low Pressure Alarm (N/O), Sensor Health (N/O), Pump 1 Health (N/O), Pump 2 Health (N/O).
- Optional Additional Volt Free Contacts (Requires an additional factory fitted expansion board): Low Pressure Warning (N/O), High Pressure Warning (N/O), Low Water In Break Tank (N/O), Low Additive In Holding Tank (N/O),



Pump 1 Run For Topup (N/O), Pump 2 Run For Topup (N/O).

## TECHNICAL SPECIFICATIONS

### Operating Conditions:

- **System temperature range at point of connection:** 5 °C / 85 °C.
- **Ambient temperature range:** 5 °C / 40 °C.
- **Pressure rating:** PN 10.
- Relative humidity 95% non-condensing.
- Noise Rating Data: < 75 dBA.

### Certifications and Standards Applied:

- PED 2014/68/EU Sound Engineering Practice.
- IEE - Electrical Safety Guidance.
- EMC 2004/108/EC.
- BS 7074 Parts 1 to 3.
- Machinery Directive 2006/42/EC.v
- Electronic Components have been tested and comply with the EMC Directives.
- **EN 61000-6-2:** Generic Standards - Immunity standard for industrial environments.
- **EN 61000-6-3:** Generic Standards - Emission standard for residential, commercial and light industrial environment.

2


- CE marked components, where applicable.
- WRAS approved float valve to BS1212.
- IP54 (BS EN60529) rated controller.

**Material of Construction:**

- **Cabinet:** Mild steel CR4 Powder Coated.
- **Float:** WRAS Approved.
- **Break Tank:** Polypropylene.
- **Connection:** Brass / Polypropylene.
- **Pipework:** Braided Flexhose / EPDM / Copper.
- **Valves:** Brass/ PTFE.

<b>Description</b>	3760 2MP Floor standing PU
<b>GTIN</b>	08712874216044
<b>Model</b>	3760 Pro 2MP
<b>Pump quantity</b>	2
<b>Connections</b>	System (mm) - 15 (½")
	Mains Supply (mm) - 15 (½")
	Overflow (mm) - 22
<b>Max. Delivery Pressure (bar)</b>	6
<b>Power Consumption (kW)</b>	2 x 0.5
<b>Full Load Current (A)</b>	6.8
<b>Weight (kg)</b>	39

**DIMENSIONS**



TORONTO  
+1 416 755 2291

BUFFALO  
+1 716 693 8813

DROITWICH SPA  
+44 121 550 5333

MANCHESTER  
+44 161 223 2223

BANGALORE  
+91 80 4906 3555

SHANGHAI  
+86 21 5237 0909

BEIJING  
+86 21 5237 0909

SÃO PAULO  
+55 11 4785 1330

DUBAI  
+971 4 887 6775

JIMBOLIA  
+40 256 360 030

Type	DIMENSIONS (MM)								
	A	B	C	D	E	F	H	K	M
3760 Pro 2MP	609	325	915	500	150	500	235	587	627