





ING MANCE

ontinued and accelerated demand for sustained efficiency and maximum lifetime value has inspired next-level thinking in pumping solution design.

Decades of innovation have brought us to this point. Engineers, contractors, developers and owners have seen the possibilities for well-designed solutions to provide exponentially more value than the solutions offered just a few years ago.

Now, with the technological advances in digital control and internet-based connectivity, Armstrong has taken innovation to a new level.

GET SUPERIOR VALUE WITH DESIGN ENVELOPE TANGO

DFSIGN ENVELOPE


- Unmatched energy efficiency
- Absolute lowest installed cost
- Always available: redundancy AND performance, at last

NEXT LEVEL THINKING

PARALLEL SENSORLESS

arallel Sensorless Pump Control (PSPC) is a patented technology that improves the efficiency of a multipump installation through optimised load sharing. The traditional approach to control in a multi-pump installation involves staging pumps on the basis of motor speed. PSPC technology stages pumps based on operating efficiency rather than motor speed and improves the efficiency of the full pump array by up to 30% over traditional multipump installations.

HVAC loads and flow requirements change throughout the day. In the graph below, the point where the dotted vertical lines intersect the system efficiency curves represent the flow level at which one pump in the array should be staged on or off. Staging pumps at any other point forces the pump array to operate at efficiency levels that are less than optimal. In a multi-pump installation, Parallel Sensorless Pump Control monitors pump speed and stages pumps at the correct flow levels to optimise efficiency.







Advanced hydraulic design supports industry-leading flow efficiency

Built-in Parallel Sensorless pump control saves up to 30% more energy

Armstrong iECM intelligent motor technology delivers an additional 3%-12% efficiency, meeting IE5 efficiency standards

Control algorithm reviews operating conditions constantly and adjusts output to meet immediate flow requirements at a minimum of energy consumption




Saves one pipe drop plus related valves and fittings for greatly reduced installation costs

Saves up to 80% in mechanical room space with reduced footprint

One rotating assembly can be removed for service: remaining unit provides 75-100% of total flow

Weight of motor and casing is reduced by up to 80% for easier handling





	Two pump duty/standby	One Tango pump	Tango savings
Total pump weight	811.9 kg	86.6 kg	89%
Installation weight	1198.4 kg	322.9 kg	73%
Installation footprint	1.12 m ²	0.46 m²	81%
Installation cost	₹ 3,23,000	₹ 1,36,000	58%



ost building HVAC systems operate at the design point (100% load) less than 1% of the time. Traditional system design applies 100% redundancy and duplication of components to ensure that the design point can always be met. This creates huge overcapacity with related inflation of costs.

he traditional duty/standby approach to redundancy in HVAC systems inflates the installed costs for equipment and labuor, and adds to the carbon footprint of the building. The dual-pumping configuration of Tango enables an updated approach to redundancy. Pumps and motors are selected from a range of sizes to achieve a level of redundancy that matches the requirements of the application.


For example, instead of a pump configuration of $2 \times 100\%$ for full redundancy, designers can choose $2 \times 50\%$. In this configuration, if one pump fails, the remaining pump provides 75–80% of the total flow. This low-level supports 90–95% of design point heat transfer, resulting in a temperature variation of only 2° .

With the proper approach to redundancy, even in the event of a breakdown, HVAC requirements can be met for all but the most extreme days of the year; and for those few days, variation in temperature will be minimal.

POWER > FLOW > HEAT TRANSFER


HVAC system flow rate depends on the pressure created by the pump, and pumping pressure is created by motor power. But it's not the straight-line relationship one might imagine.

Number of pumps	% of total kW of each pump	Redundancy range (flow)	Resulting heat transfer
1	100%	0%	0%
2	50%	75-80%	90-95%
2	70%	85-90%	97%+
2	100%	100%	100%



GOODBYE DUTY STANDBY

DESIGN ENVELOPE PARALLEL SAVINGS



omparing the Design **Envelope Tango** in different redundancy configurations against a standard end suction horizontal duty/standby configuration reveals the savings in installed cost, operating cost and five-year lifecycle cost. **Even in mission-critical** applications requiring 100% redundancy, the operating cost savings from Design Envelope technology and Parallel **Sensorless Pump Control** combined with the installed cost savings of Tango, saves more than 23% over the first five years.

Redundancy level (min)	General use ≥ 70%	Highly comfort- sensitive sectors ≥ 85%	Mission critical ≥ 100%
Sample buildings	School, apt/condo, factory/warehouse	University, campus, commercial hotel, office, mixed-use, outpatients	Data center, critical care, blood bank, labs/R&D, hospital
Recommendation	Tango 2×50%	Tango 2×70%	Tango 2×100%



Built-in Wi-Fi capability supports remote control, real-time monitoring and management for lowest operating costs

Local and remote access from any smart device

Adaptive browser-compatible software and intuitive user interface

NEXT LEVEL THINKING

ADVANCED PERFORMANCE CONTROL

Expanded performance range (and options)

One-touch auto-flow balancing

Pump speed modulation based on an adjustable quadratic control curve for better part-load efficiency

Armstrong has reinvented and redesigned pumping solutions to include connectivity and performance management services. Design Envelope provides optimal lifetime efficiency through:

Flow monitoring accuracy (+/- 5%)

Operating data and notifications to support diagnostics and service

Advanced onboard control functions

OPTIONAL SERVICES FOR SUPERCHARGED VALUE

PERFORMANCE PACKAGES



Sensorless Bundle (standard)

FUNCTIONS INCLUDED

- Sensorless control
- Flow readout
- Constant flow
- Constant pressure



Parallel Sensorless (standard on Tango and dualARMs)

 Parallel Sensorless control



Energy Performance Bundle

- Auto-flow balancing
- Maximum flow control



Protection Bundle

- Minimum flow control
- Bypass valve control



Zone optimisation

 Accept up to two dP sensor control signals



Dual-season setup

 Pre-set heating and cooling parameters for two-pipe systems

PERFORMANCE MANAGEMENT

Studies of HVAC systems suggest that improper installation can reduce system-wide efficiency by up to 30%. Separate studies conducted by the Lawrence Berkeley national laboratory found that regular commissioning of the equipment prevented a 9% performance degradation over time. Leveraging the embedded intelligence and Wi-Fi capabilities of Design Envelope, Armstrong now offers Pump Manager, a service to help operators maintain optimal long-term pump efficiency and overall performance.

Maximise uptime

Avoid emergency repair costs through cost-effective, proactive maintenance

Maintain "as commissioned" efficiency

TORONTO

23 BERTRAND AVENUE TORONTO, ONTARIO CANADA, M1L 2P3 +1 416 755 2291

BUFFALO

93 EAST AVENUE NORTH TONAWANDA, NEW YORK U.S.A., 14120-6594 +1 716 693 8813

BIRMINGHAM

HEYWOOD WHARF, MUCKLOW HILL HALESOWEN, WEST MIDLANDS UNITED KINGDOM, B62 8DJ +44 (0) 8444 145 145

MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM, M11 2ET
+44 (0) 8444 145 145

BANGALORE

#59, FIRST FLOOR, 3RD MAIN MARGOSA ROAD, MALLESWARAM BANGALORE, INDIA, 560 003 +91 (0) 80 4906 3555

SHANGHAL

unit 903, 888 north sichuan rd. Hongkou district, shanghai China, 200085 +86 (0) 21 5237 0909

SÃO PAULO

rua josé semião rodrigues agostinho, 1370 galpão 6 embu das artes sao paulo, brazil +55 11 4785 1330

LYON

93 RUE DE LA VILLETTE LYON, 69003 FRANCE +33 (0) 420 102 625

DUBAI

JAFZA VIEW 19, OFFICE 402 P.O.BOX 18226 JAFZA, DUBAI - UNITED ARAB EMIRATES +971 4 887 6775

MANNHEIM

DYNAMOSTRASSE 13 68165 MANNHEIM GERMANY +49 (0) 621 3999 9858

ARMSTRONG FLUID TECHNOLOGY

ESTABLISHED 1934


TANGO APPLICATION RANGE

4322 SPLIT-COUPLED DESIGN ENVELOPE

INDOORS	OUTDOORS
0.75-7.5 kW	0.75-7.5 kW

4372 CLOSE-COUPLED DESIGN ENVELOPE

INDOORS	OUTDOORS
0.75-7.5 kW	0.75-7.5 kW
	Armstrong Design Envelope pumps are available for outdoor applications in Series 4322 and 4372.



4322/4372 Split and close-coupled Tango

For applications requiring more than 7.5 kW, please use the Armstrong dualArm pump (up to 75 kW).

For more information on Tango pumps or Design Envelope technology please contact your local Armstrong representative or visit our website at:

ArmstrongFluidTechnology.com