

# **DESIGN ENVELOPE 4322 & 4372** BLANKING PLATE INSTALLATION AND OPERATING INSTRUCTIONS

File No: 100.8167

Date: JULY 07, 2021

Supersedes: NEW

Date: NEW

#### **CAUTION**



Always disconnect power supply from motor before beginning service work.

# A Install new adapter O-ring

Insert new adapter O-ring into the O-ring groove of the adapter and apply silicon or glycerine lubricant around the O-ring.

## в Clamp Ring

Insert Clamp Ring thru the impeller and adapter flange. Tighten the nut on the clamp ring to 90-100 lbs-in.

#### **MAINTENANCE**

## **GENERAL CARE**

Vertical In-Line pumps are built to operate without periodic maintenance, other than motor lubrication on larger units. A systematic inspection made at regular intervals, will ensure years of trouble-free operation, giving special attention to the following:

- Keep unit clean
- Provide the motor with correctly sized overload protection.
   Keep moisture, refuse, dust or other loose particles away from the pump and ventilating openings of the motor.
- Avoid operating the unit in overheated surroundings (Above 100°F/40°C).


If one pump requires service, install the blanking plate to allow the other pump head to continue operating

## WARNING



Whenever any service work is to be performed on a pumping unit, disconnect the power source to the driver, lock it off and tag with the reason. Any

possibility of the unit starting while being serviced must be eliminated. If mechanical seal environmental accessories are installed, ensure water is flowing through the sight flow indicator and that filter cartridges are replaced as recommended. (See Armstrong files 43.85 and 43.86 for seal environmental instructions).



#### TORONTO

23 BERTRAND AVENUE TORONTO, ONTARIO CANADA, M1L 2P3 +1 416 755 2291

#### BUFFALO

93 EAST AVENUE NORTH TONAWANDA, NEW YORK U.S.A., 14120-6594 +1 716 693 8813

#### DROITWICH SPA

POINTON WAY, STONEBRIDGE CROSS BUSINESS PARK DROITWICH SPA, WORCESTERSHIRE UNITED KINGDOM, WR9 OLW +44 8444 145 145

#### MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM, M11 2ET
+44 8444 145 145

## BANGALORE

#59, FIRST FLOOR, 3RD MAIN MARGOSA ROAD, MALLESWARAM BANGALORE, INDIA, 560 003 +91 80 4906 3555

#### SHANGHAI

unit 903, 888 north sichuan rd. Hongkou district, shanghai China, 200085 +86 21 5237 0909

## SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES SAO PAULO, BRAZIL +55 11 4785 1330

## LYON

93 RUE DE LA VILLETTE LYON, 69003 FRANCE +33 4 26 83 78 74

## DUBAI

JAFZA VIEW 19, OFFICE 402 P.O.BOX 18226 JAFZA, DUBAI - UNITED ARAB EMIRATES +971 4 887 6775

## MANNHEIM

DYNAMOSTRASSE 13 68165 MANNHEIM GERMANY +49 621 3999 9858

## JIMBOLIA

STR CALEA MOTILOR NR. 2C JIMBOLIA 305400, JUD.TIMIS ROMANIA +40 256 360 030

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

# FOR SERVICE RELATED PARTS & KITS

Use ADEPT Select to quickly and easily select.
Visit adept.armstrongfluidtechnology.com to learn more

