

Series 4300 Vertical in-line

**Equal suction & dis-
charge 'M' designation**

Parts list

TC motors only, groups 5 to 20

1 $\frac{1}{4}$ " impeller bore

1 $\frac{5}{8}$ " mechanical seal

File No: 6043.134

Date: NOVEMBER 20, 2015

Supersedes: 6043.134

Date: OCTOBER 7, 2015

4300 POWER FRAMES: ALL SPEEDS

PUMP SIZE	GROUP NUMBER	MOTOR FRAMES									
		143 145	182 184	FT215 213 215	254 256	284 286	324 326	FF300/FF350 364 365	404 405	444 445	447 449
1 $\frac{1}{2}$ ×1×6	1	TC	—	—	—	—	—	—	—	—	—
	2	—	TC	—	—	—	—	—	—	—	—
2×2×6	1	TC	—	—	—	—	—	—	—	—	—
	2	—	TC	—	—	—	—	—	—	—	—
3×3×6	3	—	—	TC	—	—	—	—	—	—	—
	1	TC	—	—	—	—	—	—	—	—	—
4×4×6	2	—	TC	—	—	—	—	—	—	—	—
	3	—	—	TC	—	—	—	—	—	—	—
4×4×6	4	—	—	—	TC	—	—	—	—	—	—
	1	TC	—	—	—	—	—	—	—	—	—
1 $\frac{1}{2}$ ×1 $\frac{1}{2}$ ×8	2	—	TC	—	—	—	—	—	—	—	—
	3	—	—	TC	—	—	—	—	—	—	—
2×2×8	1	TC	—	—	—	—	—	—	—	—	—
	2	—	TC	—	—	—	—	—	—	—	—
2×2×8	3	—	—	TC	—	—	—	—	—	—	—
	4	—	—	—	TC	—	—	—	—	—	—
2×2×8	5	—	—	—	—	TSC	—	—	—	—	—
	1	TC	—	—	—	—	—	—	—	—	—
3×3×8	2	—	TC	—	—	—	—	—	—	—	—
	3	—	—	TC	—	—	—	—	—	—	—
3×3×8	4	—	—	—	TC	—	—	—	—	—	—
	5	—	—	—	—	TSC	—	—	—	—	—
3×3×8	6	—	—	—	—	—	TSC	—	—	—	—
	1	TC	—	—	—	—	—	—	—	—	—
4×4×8	2	—	TC	—	—	—	—	—	—	—	—
	3	—	—	TC	—	—	—	—	—	—	—
4×4×8	4	—	—	—	TC	—	—	—	—	—	—
	5	—	—	—	—	TSC	—	—	—	—	—
4×4×8	6	—	—	—	—	—	TSC	TSC	—	—	—
	7	—	—	—	—	—	—	—	TSC	—	—
5×5×8	1	TC	—	—	—	—	—	—	—	—	—
	2	—	TC	—	—	—	—	—	—	—	—
5×5×8	3	—	—	TC	—	—	—	—	—	—	—
	4	—	—	—	TC	—	—	—	—	—	—
5×5×8	5	—	—	—	—	TSC	—	—	—	—	—
	6	—	—	—	—	—	TSC	—	—	—	—
6×6×8	2	—	TC	—	—	—	—	—	—	—	—
	3	—	—	TC	—	—	—	—	—	—	—
6×6×8	4	—	—	—	TC	—	—	—	—	—	—
	1	TC	—	—	—	—	—	—	—	—	—
8×8×8	2	—	TC	—	—	—	—	—	—	—	—
	3	—	—	TC	—	—	—	—	—	—	—
8×8×8	4	—	—	—	TC	—	—	—	—	—	—
	1	TC	—	—	—	—	—	—	—	—	—
2×2×10	2	—	TC	—	—	—	—	—	—	—	—
	3	—	—	TC	—	—	—	—	—	—	—
2×2×10	4	—	—	—	TC	—	—	—	—	—	—
	5	—	—	—	—	TSC	—	—	—	—	—
2×2×10	6	—	—	—	—	—	TSC	—	—	—	—

4300 POWER FRAMES: ALL SPEEDS (continued)

4300 POWER FRAMES: ALL SPEEDS (continued)


4300 POWER FRAMES: ALL SPEEDS (continued)

4300 GROUP NUMBER	5	6	7	8	9	10	11	12
SEAL SIZE AND PUMP SHAFT DIAMETER	1 $\frac{5}{8}$	1 $\frac{5}{8}$	1 $\frac{5}{8}$	1 $\frac{5}{8}$	1 $\frac{5}{8}$	1 $\frac{5}{8}$	1 $\frac{5}{8}$	1 $\frac{5}{8}$
IMPELLER BORE	1 $\frac{1}{4}$	1 $\frac{1}{4}$	1 $\frac{1}{4}$	1 $\frac{1}{4}$	1 $\frac{1}{4}$	1 $\frac{1}{4}$	1 $\frac{1}{4}$	1 $\frac{1}{4}$
COUPLING BORE	MOTOR SHAFT DIAMETER	1 $\frac{5}{8}$	1 $\frac{7}{8}$	2 $\frac{1}{8}$	1 $\frac{7}{8}$	2 $\frac{1}{8}$	2 $\frac{3}{8}$	1 $\frac{1}{8}$
	PUMP SHAFT DIAMETER	1 $\frac{5}{8}$						
SHAFT GAP BETWEEN PUMP AND MOTOR	2 $\frac{3}{4}$	2 $\frac{7}{8}$	2 $\frac{3}{8}$	1 $\frac{3}{8}$	1 $\frac{3}{8}$	1 $\frac{3}{8}$	2 $\frac{1}{2}$	2

4300 GROUP NUMBER	13	14	15	16	17	18	19	20
SEAL SIZE AND PUMP SHAFT DIAMETER	1 $\frac{5}{8}$	1 $\frac{5}{8}$	1 $\frac{5}{8}$	1 $\frac{5}{8}$	1 $\frac{5}{8}$	1 $\frac{5}{8}$	1 $\frac{5}{8}$	1 $\frac{5}{8}$
IMPELLER BORE	1 $\frac{1}{4}$	1 $\frac{1}{4}$	1 $\frac{1}{4}$	1 $\frac{1}{4}$	1 $\frac{1}{4}$	1 $\frac{1}{4}$	1 $\frac{1}{4}$	1 $\frac{1}{4}$
COUPLING BORE	MOTOR SHAFT DIAMETER	1 $\frac{5}{8}$	1 $\frac{7}{8}$	2 $\frac{1}{8}$	1 $\frac{7}{8}$	2 $\frac{3}{8}$	1 $\frac{7}{8}$	2 $\frac{3}{8}$
	PUMP SHAFT DIAMETER	1 $\frac{5}{8}$						
SHAFT GAP BETWEEN PUMP AND MOTOR	1 $\frac{3}{8}$	1 $\frac{3}{8}$	1 $\frac{3}{8}$	2 $\frac{7}{8}$	1 $\frac{3}{8}$	2 $\frac{7}{8}$	2 $\frac{7}{8}$	1 $\frac{7}{8}$

CROSS SECTION VIEW

Groups 5, 6, 7, 8, 9 & 10




Series 4300 Equal suction & discharge 'M' designation
1 $\frac{1}{4}$ " Impeller bore - 1 $\frac{5}{8}$ " Mechanical seal

PARTS LIST


6

MECHANICAL SEAL

Exploded view



OUTSIDE MECHANICAL SEAL



INSIDE MECHANICAL SEAL

INDEX

ITEM	DESCRIPTION	PAGE
21	Shaft	24
36	Impeller key	24
43	Lockwasher	20
44	Motor capscrew	20
50	Stuffing box/adapter	16 to 18
51	Seal chamber bushing	24
52	Seal cover capscrew	24 & 25
54	Seal cover	24
55	Inside seal cover gasket	25
58	Male straight connector	25
59	Tubing	25
60	Inside seal seat	
62	Outside mechanical seal John crane STD.	24
62	Outside mechanical seal John crane T.C.	24
62	Outside mechanical seal Durametallic STD.	24
62	Outside mechanical seal Durametallic T.C.	24
62	Inside mechanical seal head B.F. & A.I. construction	25
63	1/4" NPT tee	25
68	Air vent	25
80	Impeller	10 & 11
83	Impeller washer	24
86	Impeller capscrew	24
90	Case wear ring	11 & 12
100	Casing	8&9

ITEM	DESCRIPTION	PAGE
101	Casing gasket	13
102	Gauge plug	24
103	Casing capscrew washer	14
104	Casing capscrew	14
105	Casing drain plug	15
140	Coupler	23
144	Coupler capscrew	24
145	Lockwasher	24
146	Coupler collar set screw	22
147	Motor shaft coupler collar	22
148	Pump shaft coupler collar	24
149	Coupler square key (pump)	24
150	Coupling guard (not shown)	19
151	Coupler guard bolt (not shown)	19
152	Nut (not shown)	19
153	Washer (not shown)	19
154	Coup. Square key (motor)	21
155	Capscrew lockwasher	24
156	Shaft capscrew	24
160	Inside seal retaining ring	25
163	Seal cover capscrew washer	24 & 25
194	Male 90° angle connection	25
195	Adapter ring (not shown)	

ITEM 100 CASING**

PUMP SIZE	PRESSURE RATING (LB)	CONSTRUCTION	PART NUMBER
2×2×8	125#	Cast iron	427047-011
	250#	Ductile iron	427048-031
	125#	All bronze	427047-041
3×3×8	125#	Cast iron	427051-011
	250#	Ductile iron	427052-031
	125#	All bronze	427051-041
4×4×8	125#	Cast iron	427053-011
	250#	Ductile iron	427054-031
	125#	All bronze	427053-041
5×5×8	125#	Cast iron	427024-011
	250#	Ductile iron	427025-031
	125#	All bronze	427024-041
2×2×10	125#	Cast iron	427059-011
	250#	Ductile iron	427060-031
	125#	All bronze	427059-041
3×3×10	125#	Cast iron	427061-011
	250#	Ductile iron	427062-031
	125#	All bronze	427061-041
4×4×10	125#	Cast iron	427063-011
	250#	Ductile iron	427064-031
	125#	All bronze	427063-041
6×6×10	125#	Cast iron	427065-011
	250#	Ductile iron	427066-031
	125#	All bronze	427065-041
8×8×10	125#	Cast iron	427067-011
	250#	Ductile iron	427068-031
	125#	All bronze	427067-041
4×4×11½	125#	Cast iron	426119-011
	250#	Ductile iron	426120-031
	125#	All bronze	426119-041
5×5×11½	125#	Cast iron	426123-011
	250#	Ductile iron	426124-031
	125#	All bronze	426123-041
6×6×11½	125#	Cast iron	426127-011
	250#	Ductile iron	426128-031
	125#	All bronze	426127-041

ITEM 100 CASING (continued)**

PUMP SIZE	PRESSURE RATING (LB)	CONSTRUCTION	PART NUMBER
8×8×11 $\frac{1}{2}$	125#	Cast iron	426131-011
	250#	Ductile iron	426132-031
	125#	All bronze	426131-041
3×3×13	125#	Cast iron	427071- 011
	250#	Ductile iron	427072- 031
	125#	Stainless steel	427071- 071
	125#	All bronze	427071- 041
4×4×13	125#	Cast iron	427073- 011
	250#	Ductile iron	427074- 031
	125#	Stainless steel	427073- 071
	125#	All bronze	427074- 041
5×5×13	125#	Cast iron	427193-011
	250#	Ductile iron	427194-031
5×5×13H	125#	Cast iron	427193-017
	250#	Ductile iron	427194-037
6×6×13 [†]	125#	Cast iron	427183-011
	250#	Ductile iron	427184-031
6×6×13H	125#	Cast iron	427183-017
	250#	Ductile iron	427184-037
8×8×13*** (PRE AUGUST 2015)	125#	Cast iron	427077-011
	250#	Ductile iron	427078-031
	125#	Stainless steel	427207-071
	125#	All bronze	427207-041
8×8×13*** (POST AUGUST 2015)	125#	Cast iron	427207-011
	250#	Ductile iron	427208-031
10×10×13	125#	Cast iron	427328-011
	250#	Ductile iron	427329-031
	125#	Stainless steel	427328-071
	125#	All bronze	427328-041

NOTES:

** Casing part numbers are for casing only, casing wear ring is sold separately. If new casing is required, it must be ordered c/w wear ring

† For 6x6x13 units pre-June 2011, casing & impeller must be replaced together. Contact Armstrong for details.

*** For 8x8x13 pumps, there was a revision to the the casing and impeller done in August 2015. These two parts are not interchangeable between the old and new pumps. Please consult your Armstrong representative if you need extra assistance.

ITEM 80 IMPELLER 1 $\frac{1}{4}$ " BORE**

PUMP SIZE	MATERIAL	IMPELLER BORE	MAXIMUM DIAMETER	PART NUMBER
2×2×8	Bronze	1 $\frac{1}{4}$ "	8"	427122-041
	Cast iron	1 $\frac{1}{4}$ "	8"	427122-011
3×3×8	Bronze	1 $\frac{1}{4}$ "	8"	427130-041
	Cast iron	1 $\frac{1}{4}$ "	8"	427130-011
4×4×8	Bronze	1 $\frac{1}{4}$ "	8"	427138-041
	Cast iron	1 $\frac{1}{4}$ "	8"	427138-011
5×5×8	Bronze	1 $\frac{1}{4}$ "	8"	427132-041
	Cast iron	1 $\frac{1}{4}$ "	8"	427138-011
2×2×10	Bronze	1 $\frac{1}{4}$ "	10"	427152-041
	Cast iron	1 $\frac{1}{4}$ "	10"	427152-011
3×3×10	Bronze	1 $\frac{1}{4}$ "	10"	427164-041
	Cast iron	1 $\frac{1}{4}$ "	10"	427164-011
4×4×10	Bronze	1 $\frac{1}{4}$ "	10"	427150-041
	Cast iron	1 $\frac{1}{4}$ "	10"	427150-011
6×6×10	Bronze	1 $\frac{1}{4}$ "	10"	427154-041
	Cast iron	1 $\frac{1}{4}$ "	10"	427154-011
8×8×10	Bronze	1 $\frac{1}{4}$ "	10"	427157-041
	Cast iron	1 $\frac{1}{4}$ "	10"	427157-011
6×6×10	Bronze	1 $\frac{1}{4}$ "	10"	427154-041
	Cast iron	1 $\frac{1}{4}$ "	10"	427154-011
8×8×10	Bronze	1 $\frac{1}{4}$ "	10"	427157-041
	Cast iron	1 $\frac{1}{4}$ "	10"	427157-011
4×4×11 $\frac{1}{2}$	Bronze	1 $\frac{1}{4}$ "	11 $\frac{1}{2}$ "	426282-041
	Cast iron	1 $\frac{1}{4}$ "	11 $\frac{1}{2}$ "	426282-011
5×5×11 $\frac{1}{2}$	Bronze	1 $\frac{1}{4}$ "	11 $\frac{1}{2}$ "	426284-041
	Cast iron	1 $\frac{1}{4}$ "	11 $\frac{1}{2}$ "	426284-011
6×6×11 $\frac{1}{2}$	Bronze	1 $\frac{1}{4}$ "	11 $\frac{1}{2}$ "	426288-041
	Cast iron	1 $\frac{1}{4}$ "	11 $\frac{1}{2}$ "	426288-011
8×8×11 $\frac{1}{2}$	Bronze	1 $\frac{1}{4}$ "	11 $\frac{1}{2}$ "	426289-041
	Cast iron	1 $\frac{1}{4}$ "	11 $\frac{1}{2}$ "	426289-011
3×3×13	Bronze	1 $\frac{1}{4}$ "	13"	427165-041
	Cast iron	1 $\frac{1}{4}$ "	13"	427165-011
4×4×13	Bronze	1 $\frac{1}{4}$ "	13"	427169-041
	Cast iron	1 $\frac{1}{4}$ "	13"	427169-011

ITEM 80 IMPELLER** 1 $\frac{1}{4}$ " BORE (continued)

PUMP SIZE	MATERIAL	IMPELLER BORE	MAXIMUM DIAMETER	PART NUMBER
5×5×13	Bronze	1 $\frac{1}{4}$ "	13"	427186-041
	Cast iron	1 $\frac{1}{4}$ "	13"	427186-011
5×5×13H	Bronze	1 $\frac{1}{4}$ "	13"	427182-041
	Cast iron	1 $\frac{1}{4}$ "	13"	427182-011
6×6×13†	Bronze	1 $\frac{1}{4}$ "	13"	427182-041
6×6×13H	Bronze	1 $\frac{1}{4}$ "	13"	427177-041
8×8×13*** (PRE AUGUST 2015)	Cast iron	1 $\frac{1}{4}$ "	13"	427205-041
	Ductile iron	1 $\frac{1}{4}$ "	13"	427205-011
8×8×13*** (POST AUGUST 2015)	Cast iron	1 $\frac{1}{4}$ "	13"	427177-041
	Ductile iron	1 $\frac{1}{4}$ "	13"	427177-011
	Stainless steel	1 $\frac{1}{4}$ "	13"	427177-071
10×10×13	Bronze	1 $\frac{1}{4}$ "	13"	427332-041
	Cast iron	1 $\frac{1}{4}$ "	13"	427332-011

NOTES:

** Impeller part numbers are for full or maximum diameter impellers. Always specify pump serial number and where possible, measure

and advise the diameter of the Impeller being replaced on these Pumps.

† For 6×6×13 units pre-June 2011, casing & impeller must be replaced together. Contact Armstrong for details.

*** For 8×8×13 pumps, there was a revision to the the casing and impeller done in August 2015. These two parts are not interchangeable between the old and new pumps. Please consult your Armstrong representative if you need extra assistance.

ITEM 90 CASE WEAR RING

PUMP SIZE	CONSTRUCTION	MATERIAL	PART NUMBER
2×2×8	All bronze, Bronze fitted	SAE 660 BRONZE	426413-404
	All iron, Ductile iron	CLASS 30 CAST IRON	426413-104
3×3×8	All bronze, Bronze fitted	SAE 660 BRONZE	426413-407
	All iron, Ductile iron	CLASS 30 CAST IRON	426413-107
4×4×8	All bronze, Bronze fitted	SAE 660 BRONZE	426413-410
	All iron, Ductile iron	CLASS 30 CAST IRON	426413-110
5×5×8	All bronze, Bronze fitted	SAE 660 BRONZE	426413-413
	All iron, Ductile iron	CLASS 30 CAST IRON	426413-113
2×2×10	All bronze, Bronze fitted	SAE 660 BRONZE	426413-404
	All iron, Ductile iron	CLASS 30 CAST IRON	426413-104
3×3×10	All bronze, Bronze fitted	SAE 660 BRONZE	426413-404
	All iron, Ductile iron	CLASS 30 CAST IRON	426413-104

ITEM 90 CASE WEAR RING (continued)

PUMP SIZE	CONSTRUCTION	MATERIAL	PART NUMBER
4×4×10	All bronze, Bronze fitted	SAE 660 BRONZE	426413-408
	All iron, Ductile iron	CLASS 30 CAST IRON	426413-108
6×6×10	All bronze, Bronze fitted	SAE 660 BRONZE	426413-412
	All iron, Ductile iron	CLASS 30 CAST IRON	426413-112
8×8×10	All bronze, Bronze fitted	SAE 660 BRONZE	426413-414
	All iron, Ductile iron	CLASS 30 CAST IRON	426413-114
4×4×11½	All bronze, Bronze fitted	SAE 660 BRONZE	426412-405
	All iron, Ductile iron	CLASS 30 CAST IRON	426412-105
5×5×11½	All bronze, Bronze fitted	SAE 660 BRONZE	426412-411
	All iron, Ductile iron	CLASS 30 CAST IRON	426412-111
6×6×11½	All bronze, Bronze fitted	SAE 660 BRONZE	426412-420
	All iron, Ductile iron	CLASS 30 CAST IRON	426412-120
8×8×11½	All bronze, Bronze fitted	SAE 660 BRONZE	426412-421
	All iron, Ductile iron	CLASS 30 CAST IRON	426412-121
3×3×13	All bronze, Bronze fitted	SAE 660 BRONZE	426413-409
	Stainless steel	STAINLESS STEEL	426413-709
	All iron, Ductile iron	CLASS 30 CAST IRON	426413-109
4×4×13	All bronze, Bronze fitted	SAE 660 BRONZE	426413-412
	Stainless steel	STAINLESS STEEL	426413-712
	All iron, Ductile iron	CLASS 30 CAST IRON	426413-112
5 × 5 × 13	All bronze, Bronze fitted	SAE 660 BRONZE	426412-411
	Stainless steel 316	STAINLESS STEEL	426412-711
5 × 5 × 13H	All bronze, Bronze fitted	SAE 660 BRONZE	NA
	Stainless steel 316	STAINLESS STEEL	NA
6×6×13	Bronze fitted	SAE 660 BRONZE	426412-420
6×6×13H	—	—	—
8×8×13	All bronze, Bronze fitted	SAE 660 BRONZE	426413-415
	Stainless steel	STAINLESS STEEL	426413-715
	All iron, Ductile iron	CLASS 30 CAST IRON	426413-115
10×10×13	All bronze, Bronze fitted	SAE 660 BRONZE	426413-417
	Stainless steel	STAINLESS STEEL	426413-717
	All iron, Ductile iron	CLASS 30 CAST IRON	426413-117

ITEM 101 CASING GASKET

PUMP SIZE	CONSTRUCTION	PART NUMBER
2×2×8	ALL	426401-003
3×3×8		
4×4×8		
5×5×8		
2×2×10	ALL	426401-004
3×3×10		
4×4×10		
6×6×10		
8×8×10	ALL	426401-006
4×4×11 $\frac{1}{2}$		
5×5×11 $\frac{1}{2}$		
6×6×11 $\frac{1}{2}$		
8×8×11 $\frac{1}{2}$	ALL	426401-005
3×3×13		
4×4×13		
5×5×13		
5×5×13H	ALL	426401-005
6×6×13		
6×6×13H		
8×8×13		
10×10×13		

ITEM 104 CASING CAPSCREW & ITEM 103 WASHER

PUMP SIZE	NUMBER REQUIRED	FRAMES 182 TO 256-10 CAPSCREW	NUMBER REQUIRED	FRAMES 182 TO 256-10 WASHER	NUMBER REQUIRED	FRAMES 284 TO 405-16 CAPSCREW	NUMBER REQUIRED	FRAMES 284 TO 405-16 WASHER
2×2×8	—	—	—	—	8	5/8"-11NC 1 1/2" LG. 911129-112	8	5/8" FLAT 927121-100
3×3×8								
4×4×8								
5×5×8								
2×2×10	—	—	—	—	12	5/8"-11NC 1 1/2" LG. 911129-112	12	5/8" FLAT 927121-100
3×3×10								
6×6×10								
8×8×10								
4×4×10					12	5/8"-11NC 1 3/4" LG. 911129-114	12	5/8" LOCK- WASHER 927215-100
4×4×11 1/2	—	—	—	—	16	1/2"-13NC 1 1/2" LG. 911125-112	16	1/2" FLAT 927114-100
5×5×11 1/2								
6×6×11 1/2								
8×8×11 1/2								
3×3×13	16	5/8"-11NC 2" LG. 911129-116	16	5/8" FLAT 927121-100	16	5/8"-11NC 2" LG. 911129-116	16	5/8" FLAT 927121-100
4×4×13								
5×5×13								
5×5×13H								
6×6×13								
6×6×13H								
8×8×13								
10×10×13	—	—	—	—				

ITEM 105 CASING DRAIN PLUG

PUMP SIZE	MATERIAL	NUMBER REQUIRED	SIZE	PART NUMBER
2×2×8				
3×3×8				
4×4×8				
5×5×8				
2×2×10				
3×3×10	CAD PLATED	1	1 $\frac{1}{4}$ " NPT	937105-201
4×4×10				
8×8×10				
4×4×11 $\frac{1}{2}$				
5×5×11 $\frac{1}{2}$				
3×3×13				
4×4×13				
5×5×8				
6×6×10				
6×6×11 $\frac{1}{2}$				
8×8×11 $\frac{1}{2}$				
5×5×13	CAD PLATED	1	1 $\frac{1}{2}$ " NPT	937105-203
5×5×13H				
6×6×13				
6×6×13H				
8×8×13				
10×10×13				

Series 4300 Equal suction & discharge 'M' designation

PARTS LIST

1¼" Impeller bore - 1½" Mechanical seal

16

ITEM 50 ADAPTER

Bronze fitted and All iron construction

PUMP SIZE	MOTOR FRAME SIZE	MATERIAL	PART NUMBER	
2×2×8	284 – 286TSC	Cast iron	427707-011	
3×3×8				
4×4×8	324 – 326TSC	Cast iron	427710-015	
5×5×8				
6×6×8				
2×2×10	284 – 286TSC	Cast iron	427708-011	
3×3×10				
6×6×10	324 – 326TSC	Cast iron	427711-011	
8×8×10				
4×4×10	284 – 286TSC	Cast iron	427708-015	
	324 – 326TSC		427711-015	
4×4×11½	284 – 286TC	Cast iron	427709-011	
	324 – 326TC		427712-011	
3×3×13	182 – 256TC	Cast iron	427840-011	
	284 – 286TC		427841-011	
	324 – 405TSC		427842-011	
	444 – 445TSC		427856-011	
4×4×13	184 – 256TC	Cast iron	427840-011	
	284 – 286TC		427841-011	
	324TSC		427842-011	
5×5×13	215 – 256TC	Cast iron	427840-011	
	284 – 286TC		427841-011	
	324 – 365TC		427842-011	
6×6×13	215 – 256TC	Cast iron	427840-011	
	284 – 286TC		427841-011	
	324 – 365TC		427842-011	
8×8×13	215 – 256TC	Cast iron	427840-011	
	284 – 286TC		427841-011	
	324 – 365TC		427842-011	
10×10×13	284 – 286TC	Cast iron	427841-011	
	324 – 326TC		427842-011	

ITEM 50 PUMPS STUFFING BOX

13" Bronze fitted and All iron construction

PUMP SIZE	MOTOR FRAME SIZE	MATERIAL	PART NUMBER
13" PUMPS	ALL	Cast iron	427884-011

ITEM 150

13" pumps motor adapter ring all constructions

PUMP SIZE	MOTOR FRAME SIZE	MATERIAL	PART NUMBER
ALL	284 – 286TC	Steel	427850-000
ALL	364 – 365TC	Steel	427730-000

ITEM 50 ADAPTER

Ductile iron construction

PUMP SIZE	MOTOR FRAME SIZE	MATERIAL	PART NUMBER
2×2×8	284 – 286TSC	Cast iron	427707-011
3×3×8			
4×4×8	324 – 326TSC	Cast iron	427710-015
5×5×8			
6×6×8			
2×2×10	284 – 286TSC	Cast iron	427708-011
3×3×10			
6×6×10	324 – 326TSC	Cast iron	427711-011
8×8×10			
4×4×10	284 – 286TSC	Cast iron	427708-015
	324 – 326TSC		427711-015
4×4×11½	284 – 286TC	Cast iron	427709-011
5×5×11½			
6×6×11½	324 – 326TC	Cast iron	427712-011
8×8×11½			
	182 – 256TC	Cast iron	427840-011
3×3×13	284 – 286TC		427841-011
	324 – 405TSC		427842-011
	444 – 445TSC		427856-011
	184 – 256TC	Cast iron	427840-011
4×4×13	284 – 286TC		427841-011
	324TSC		427842-011
	215 – 256TC	Cast iron	427840-011
5×5×13	284 – 286TC		427841-011
5×5×13H	324 – 365TC		427842-011
	215 – 256TC	Cast iron	427840-011
6×6×13	284 – 286TC		427841-011
6×6×13H	324 – 365TC		427842-011
	215 – 256TC	Cast iron	427840-011
8×8×13	284 – 286TC		427841-011
	324 – 365TC		427842-011
10×10×13	284 – 286TC	Cast iron	427841-011
	324 – 326TC		427842-011

ITEM 50 PUMPS STUFFING BOX

13" Bronze fitted and All iron construction

PUMP SIZE	MOTOR FRAME SIZE	MATERIAL	PART NUMBER
13" PUMPS	ALL	Cast iron	427884-011

Series 4300 Equal suction & discharge 'M' designation

PARTS LIST 1 1/4" Impeller bore - 1 5/8" Mechanical seal

18

ITEM 50 ADAPTER

All bronze construction

PUMP SIZE	MOTOR FRAME SIZE	MATERIAL	PART NUMBER	
2x2x8	284 - 286TSC	Bronze	427707-041	
3x3x8				
4x4x8	324 - 326TSC	Cast bronze	427710-045	
5x5x8				
6x6x8				
2x2x10	284 - 286TSC	Cast bronze	427708-041	
3x3x10				
6x6x10	324 - 326TSC	Cast bronze	427711-041	
8x8x10				
4x4x10	284 - 286TSC	Cast bronze	427708-045	
	324 - 326TSC		427711-045	
4x4x11 1/2	284 - 286TC	Cast bronze	427709-041	
	324 - 326TC			
			427712-041	
3x3x13	182 - 256TC	Cast bronze	427840-041	
	284 - 286TC		427841-041	
	324 - 405TSC		427842-041	
	444 - 445TSC		427856-041	
4x4x13	184 - 256TC	Cast bronze	427840-041	
	284 - 286TC		427841-041	
	324TSC		427842-041	
5x5x13	215 - 256TC	Cast bronze	427840-041	
	284 - 286TC		427841-041	
	324 - 365TC		427842-041	
6x6x13	215 - 256TC	Cast bronze	427840-041	
	284 - 286TC		427841-041	
	324 - 365TC		427842-041	
8x8x13	215 - 256TC	Cast bronze	427840-041	
	284 - 286TC		427841-041	
	324 - 365TC		427842-041	
10x10x13	284 - 286TC	Cast bronze	427841-041	
	324 - 326TC		427842-041	

ITEM 50 PUMPS STUFFING BOX

13" Bronze fitted and All iron construction

PUMP SIZE	MOTOR FRAME SIZE	MATERIAL	PART NUMBER
13" PUMPS	ALL	Cast bronze	427884-041

ITEM 150

13" pumps motor adapter ring all constructions

PUMP SIZE	MOTOR FRAME SIZE	MATERIAL	PART NUMBER
ALL	284 - 286TC	Steel	427850-000
ALL	364 - 365TC	Steel	427730-000

ITEM 150 COUPLER GUARD

PUMP SIZE	MOTOR FRAME SIZE	PART NUMBER
2x2x8		
3x3x8	284 - 286TSC	
4x4x8		427761-007
5x5x8	324 - 326TSC	
6x6x8		
2x2x10		
3x3x10	284 - 286TSC	427761-008
4x4x10		
6x6x10	324 - 326TSC	427761-007
8x8x10		
4x4x11 $\frac{1}{2}$	284 - 286TC	427761-008
5x5x11 $\frac{1}{2}$		
6x6x11 $\frac{1}{2}$	324 - 326TC	427761-007
8x8x11 $\frac{1}{2}$		
3x3x13		
4x4x13	182TC- 286TC	427859-000
5x5x13		
5x5x13H		
6x6x13		
6x6x13H	324 - 445TC & TSC	427858-000
8x8x13		
10x10x13		

COUPLER GUARD FASTENERS

ITEM NUMBER	DESCRIPTION	NUMBER REQUIRED	SIZE	PART NUMBER
151	Bolt - RD. HD.	2	#8-32x1 $\frac{1}{2}$ "	916262-100
152	Nut	2	#8-32	913162-100
153	Washer	2	#8-32	927105-100

Series 4300 Equal suction & discharge 'M' designation
1 $\frac{1}{4}$ " Impeller bore - 1 $\frac{5}{8}$ " Mechanical seal

PARTS LIST

20

ITEM 44 MOTOR CAPSCREW & ITEM 43 LOCKWASHER

PUMP SIZE	MOTOR FRAME SIZE	ITEM DESCRIPTION	PART NUMBER
1 $\frac{1}{2}$ ×1 $\frac{1}{2}$ ×8	284 - 286TSC	CAPSCREW	911125-110
2×2×8		LOCKWASHER	927213-100
3×3×8	324 - 326TSC	CAPSCREW	911129-112
4×4×8		LOCKWASHER	927215-100
5×5×8	324 - 326TSC	CAPSCREW	911125-110
6×6×8		LOCKWASHER	927213-100
2×2×10	284 - 286TSC	CAPSCREW	911129-112
3×3×10		LOCKWASHER	927215-100
4×4×10	324 - 326TSC	CAPSCREW	911125-110
6×6×10		LOCKWASHER	927213-100
8×8×10	284 - 286TC	CAPSCREW	911129-112
4×4×11 $\frac{1}{2}$		LOCKWASHER	927215-100
5×5×11 $\frac{1}{2}$	324 - 326TC	CAPSCREW	911125-110
6×6×11 $\frac{1}{2}$		LOCKWASHER	927213-100
6×6×11 $\frac{1}{2}$	324 - 326TC	CAPSCREW	911129-112
8×8×11 $\frac{1}{2}$		LOCKWASHER	927215-100
3×3×13	184 - 286TC	CAPSCREW	911125-114
4×4×13		LOCKWASHER	927213-100
5×5×13	324 - 446TC	CAPSCREW	911129-112
5×5×13H		LOCKWASHER	927215-100
6×6×13			
6×6×13H			
8×8×13			
10×10×13			

ITEM 154 MOTOR KEY

PUMP SIZE	MOTOR FRAME SIZE	PART NUMBER	PUMP SIZE	MOTOR FRAME SIZE	PART NUMBER
1 $\frac{1}{2}$ ×1 $\frac{1}{2}$ ×8			3×3×13		
2×2×8	284 -286TSC	428163-714	4×4×13		
3×3×8			5×5×13		
4×4×8			5×5×13H		
5×5×8	324 - 326TSC	428164-112	6×6×13	284 - 326TC	428164-116
6×6×8			6×6×13H		
2×2×10			8×8×13		
3×3×10	284 -286TSC	428163-714	10×10×13		
4×4×10			4×4×13		
6×6×10	324 - 326TSC	428164-112	5×5×13	324 - 325TSC	
8×8×10			5×5×13H		
4×4×11 $\frac{1}{2}$			6×6×13		428164-112
5×5×11 $\frac{1}{2}$	284 - 286TC	428164-116	6×6×13H		
6×6×11 $\frac{1}{2}$			8×8×13	364 - 365TSC	
8×8×11 $\frac{1}{2}$	324 - 326TC	428164-720	10×10×13		
3×3×13			5×5×13		
4×4×13			5×5×13H		
5×5×13			6×6×13	364 - 365TC	428164-117
5×5×13H	182 - 215TC	428162-112	6×6×13H		
6×6×13			3×3×13	404 - 405TC	428167-103
6×6×13H					
8×8×13					
3×3×13					
4×4×13					
5×5×13					
5×5×13H	254 - 256TC	428163-714			
6×6×13					
6×6×13H					
8×8×13					

Series 4300 Equal suction & discharge 'M' designation
1 $\frac{1}{4}$ " Impeller bore - 1 $\frac{5}{8}$ " Mechanical seal

PARTS LIST

22

ITEM 147 MOTOR COUPLER COLLAR

PUMP SIZE	MOTOR FRAME SIZE	PART NUMBER	PUMP SIZE	MOTOR FRAME SIZE	PART NUMBER
1 $\frac{1}{2}$ x 1 $\frac{1}{2}$ x 8			3 x 3 x 13		
2 x 2 x 8	284 - 286TSC	427751-000	4 x 4 x 13	284 - 286TC	
3 x 3 x 8			5 x 5 x 13		
4 x 4 x 8			5 x 5 x 13H	324 - 326TSC	427752-000
5 x 5 x 8	324 - 326TSC	427752-000	6 x 6 x 13		
6 x 6 x 8			6 x 6 x 13H		
2 x 2 x 10			8 x 8 x 13	364 - 365TSC	
3 x 3 x 10	284 - 286TSC	427751-000	10 x 10 x 13		
4 x 4 x 10			3 x 3 x 13		
6 x 6 x 10	324 - 326TSC	427752-000	4 x 4 x 13	324 - 325TSC	
8 x 8 x 10			5 x 5 x 13		
4 x 4 x 11 $\frac{1}{2}$			5 x 5 x 13H		427753-000
5 x 5 x 11 $\frac{1}{2}$	284 - 286TC	427752-000	6 x 6 x 13		
6 x 6 x 11 $\frac{1}{2}$			6 x 6 x 13H	404 - 405TSC	
8 x 8 x 11 $\frac{1}{2}$	324 - 326TC	427753-000	8 x 8 x 13		
3 x 3 x 13			10 x 10 x 13		
4 x 4 x 13	182 - 184TC	427749-000	3 x 3 x 13		
3 x 3 x 13			5 x 5 x 13	364 - 365TC	
4 x 4 x 13			5 x 5 x 13H		427754-000
5 x 5 x 13			6 x 6 x 13		
5 x 5 x 13H	213 - 215TC	427750-000	6 x 6 x 13H	445 - 446TSC	
6 x 6 x 13			8 x 8 x 13		
6 x 6 x 13H			3 x 3 x 13	404 - 405TC	427889-000
8 x 8 x 13					
3 x 3 x 13					
4 x 4 x 13					
5 x 5 x 13					
5 x 5 x 13H	254 - 256TC	427751-000			
6 x 6 x 13					
6 x 6 x 13H					
8 x 8 x 13					

ITEM 146 MOTOR COUPLER COLLAR SET SCREW

PUMP SIZE	MOTOR FRAME SIZE	PART NUMBER
All	TCS & TC 182 - 445	916519-106

ITEM 140 COUPLER

PUMP SIZE	MOTOR FRAME SIZE	PART NUMBER	SHAFT GAP	PUMP SIZE	MOTOR FRAME SIZE	PART NUMBER	SHAFT GAP
1 $\frac{1}{2}$ x 1 $\frac{1}{2}$ x 8				3 x 3 x 13			
2 x 2 x 8	284 - 286TSC	427735-000		4 x 4 x 13			
3 x 3 x 8			—	5 x 5 x 13			
4 x 4 x 8				5 x 5 x 13H	254 - 256TC	427866-000	1.375
5 x 5 x 8	324 - 326TSC	427737-000		6 x 6 x 13			
6 x 6 x 8				6 x 6 x 13H			
2 x 2 x 10				8 x 8 x 13			
3 x 3 x 10	284 - 286TSC	427735-000		3 x 3 x 13			
4 x 4 x 10			—	4 x 4 x 13			
6 x 6 x 10	324 - 326TSC	427737-000		5 x 5 x 13			
8 x 8 x 10				5 x 5 x 13H	284 - 286TC	427736-000	1.375
4 x 4 x 11 $\frac{1}{2}$	284 - 286TC	427736-000		6 x 6 x 13H			
5 x 5 x 11 $\frac{1}{2}$			—	8 x 8 x 13			
6 x 6 x 11 $\frac{1}{2}$				10 x 10 x 13			
8 x 8 x 11 $\frac{1}{2}$	324 - 326TC	427738-000		3 x 3 x 13	324 - 326TSC	427737-000	2.875
3 x 3 x 13				3 x 3 x 13	364 - 365TSC		
4 x 4 x 13	182 - 184TC	427864-000	2.505	4 x 4 x 13			
3 x 3 x 13				5 x 5 x 13			
4 x 4 x 13				5 x 5 x 13H			
5 x 5 x 13				6 x 6 x 13	324 - 326TC	427738-000	1.375
5 x 5 x 13H	213 - 215TC	427865-000	2.005	6 x 6 x 13H			
6 x 6 x 13				8 x 8 x 13			
6 x 6 x 13H				10 x 10 x 13			
8 x 8 x 13				5 x 5 x 13			
				5 x 5 x 13H			
				6 x 6 x 13	364 - 365TC	427739-000	1.375
				6 x 6 x 13H			
				8 x 8 x 13			
				3 x 3 x 13	404 - 405TSC	427740-000	2.375
				3 x 3 x 13	445 - 446TSC	427839-000	1.375

Series 4300 Equal suction & discharge 'M' designation

PARTS LIST

1 $\frac{1}{4}$ " Impeller bore - 1 $\frac{5}{8}$ " Mechanical seal

24

COMMON PARTS

All constructions

ITEM NUMBER	DESCRIPTION	PART NUMBER
21	1 $\frac{5}{8}$ " pump shaft	427714-000
36	Impeller key	428161-714
51	Seal chamber bushing	425520-001
83	Impeller washer	425742-003
86	Impeller capscrew	911900-119
102	Gauge plug (4 required) 1 $\frac{1}{4}$ "NPT. CAD plated	937105-201
144	Coupler capscrew (6 required) Frames 182TC to 365TC and 324-446TSC	911821-116
145	Lockwasher (for item 144)	927211-100
148	Shaft coupler collar	427757-000
149	Cplr. Key (pump shaft)	428163-712
155	Capscrew lockwasher	927213-400
156	Coupler collar capscrew	911125-408

PARTS FOR 1 $\frac{5}{8}$ " OUTSIDE SEAL

ITEM NUMBER	DESCRIPTION	CONSTRUCTION	PART NUMBER
62	Mechanical seal		
	Armstrong seal	All	975002-334
	Durametallic STD.	All	975002-033
	Durametallic T.C.	All	975002-031
	John crane STD.	All	975000-956
	John crane T.C.	All	975000-966
52	Capscrew - 4 required 1 $\frac{1}{2}$ "-13NCx1 $\frac{3}{4}$ " S/S	All	911125-414
163	Washer - 4 required 1 $\frac{1}{2}$ " FLAT S/S	All	427118-100
54	Seal cover	Bronze fitted, All bronze, Ductile bronze fitted	426485-002
		All iron, Ductile iron	426485-001

PARTS FOR 1 $\frac{5}{8}$ " INSIDE MECHANICAL SEAL ARRANGEMENT

ITEM NUMBER	DESCRIPTION	CONSTRUCTION	PART NUMBER
62	Mechanical seal	All	810150-135
52	Capscrew - 4 required 1 $\frac{1}{2}$ "-13NC×1 $\frac{3}{4}$ " S/S	All	911125-414
163	Washer - 4 required 1 $\frac{1}{2}$ " FLAT S/S	All	427118-100
54	Seal cover	All	426465-011
55	Gasket	All	426467-002
160	Retaining ring	All	923104-442

STANDARD MECHANICAL SEAL FLUSH LINE PARTS

ITEM NUMBER	DESCRIPTION	NUMBER REQUIRED	CONSTRUCTION	PART NUMBER
58	MALE STRAIGHT CONNECTION 3 $\frac{1}{8}$ " TUBE × 1 $\frac{1}{4}$ " NPT	1	Bronze fitted, All bronze, Ductile bronze fitted	939001-114
			All iron, Ductile iron	939001-314
59	TUBING 20" REQUIRED 3 $\frac{1}{8}$ " OD × .035 WALL	20"	Bronze fitted, All bronze, Ductile bronze fitted	997531-004
			All iron, Ductile iron	997153-004
63	TEE 1 $\frac{1}{4}$ " NPT	1	Bronze fitted, All bronze, Ductile bronze fitted	935101-001
			All iron, Ductile iron	931101-101
64	BUSHING 1 $\frac{1}{4}$ " MNPT × 1 $\frac{1}{8}$ " FNPT	1	Bronze fitted, All bronze, Ductile bronze fitted	935123-050
			All iron, Ductile iron	931123-150
67	NIPPLE 1 $\frac{1}{4}$ " NPT × 2 $\frac{1}{2}$ " NPT	1	Bronze fitted, All bronze, Ductile bronze fitted	938103-001
			All iron, Ductile iron	938003-101
68	AIR VENT	1	Bronze fitted, All bronze, Ductile bronze fitted	939018-101
			All iron, Ductile iron	218644-000
194	MALE 90° CONNECTION 3 $\frac{1}{8}$ " TUBE × 1 $\frac{1}{4}$ " NPT	1	Bronze fitted, All bronze, Ductile bronze fitted	939003-109
			All iron, Ductile iron	939003-309

FOR OTHER FLUSH LINE OPTIONS, SEE FLUSH LINE OPTIONS PARTS LIST

TORONTO

23 BERTRAND AVENUE
TORONTO, ONTARIO
CANADA
M1L 2P3
+1 416 755 2291

BUFFALO

93 EAST AVENUE
NORTH TONAWANDA, NEW YORK
U.S.A.
14120-6594
+1 716 693 8813

BIRMINGHAM

HEYWOOD WHARF, MUCKLOW HILL
HALESOWEN, WEST MIDLANDS
UNITED KINGDOM
B62 8DJ
+44 (0) 8444 145 145

MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM
M11 2ET
+44 (0) 8444 145 145

BANGALORE

#59, FIRST FLOOR, 3RD MAIN
MARGOSA ROAD, MALLESWARAM
BANGALORE, INDIA
560 003
+91 (0) 80 4906 3555

SHANGHAI

NO. 1619 HU HANG ROAD, XI DU TOWNSHIP
FENG XIAN DISTRICT, SHANGHAI
P.R.C.
201401
+86 21 3756 6696

SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO,
1370 GALPÃO 6
EMBU DAS ARTES
SAO PAULO, BRAZIL
+55 11 4781 5500

MAKING
ENERGY
SENSETM
MAKE