





he Armstrong Series
4600F represents
the state of the art in
Horizontal Split Case pumps,
meeting or exceeding the
requirements of NFPA as well as
fire protection testing laboratories
such as UL, ULC and FM.

The compact pump design and reduced footprint make the 4600F perfectly suited for use in new construction, packaged fire systems and retrofit installations.

SAVES INSTALLATION COSTS AND LIFECYCLE COSTS

Industry-leading, high-efficiency pump designs require smaller driver selections, which in turn require smaller controllers. Smaller drivers and controllers draw less power, so they can be supported by lower-rated electrical components. All these factors contribute to reduced equipment cost.

At critical duties Armstrong HSC 4600 models installed offer cost savings of up to 20%.

HIGH EFFICIENCY >

SMALLER DRIVER >

LOWER INSTALLED COST





DURABILITY

Oversized stainless steel shaft is rated for minimum 5000 run hours

Double suction impeller prevents wear due to imbalanced flow

Sealed, permanently-greased bearings prevent seizing

Externally mounted combination bearing and seal housing minimizes shaft deflection

EASY MAINTENANCE

Fitted with drain connection for drip containment

Replaceable case wear rings – locked to prevent rotation or axial displacement

Hydraulically balanced double suction impeller minimizes axial thrust


Three-piece split gland shaft sealing

Replaceable shaft sleeves

ARMSTRONG HSC 4600F FIRE PUMPS - 50Hz


Performance Selection Chart

1500 rpm 3000 rpm Coming soon
Also available with diesel drive at various speeds





eb-based sizing and selection software makes it easy to choose the Armstrong fire pump that's right for your building project. All supporting literature, performance curves, 3D CAD files and Revit models are available for download.



CONTRACTOR FRIENDLY



he contractor-friendly design approach means easy access for repair, easy replacement of bearings, and flexibility on installation. If needed, the pump can be reversed from the left-hand to right-hand drive at the site.

The innovative 3-piece gland seal packing design means that the packing can be changed without removing the rotating assembly

The Armstrong 4600F leads the industry with its Tilted-parting casing design that places suction and discharge on the same center line. This makes it easy for contractors to install piping in advance of the pump delivery, which can compress construction schedules and reduce labor.

The pump shafts and all related parts are identical for left and right-hand drive configurations. This means the 4600F can be reconfigured on-site to rotate in the opposite direction, if needed.

Lastly, with a small overall footprint, there's plenty of space around the pump to make installation, commissioning and maintenance easier.

Contractors can save time and minimize costs with features that reduce maintenance



Tilted-parting casing design – rotating element can be removed without disturbing piping

Ergonomic design of stuffing box extension

Removable bearing housing – without removing top casing

Readily available spare parts kits

TORONTO

23 BERTRAND AVENUE TORONTO, ONTARIO CANADA, M1L 2P3 +1 416 755 2291

BUFFALO

93 EAST AVENUE NORTH TONAWANDA, NEW YORK U.S.A., 14120-6594 +1 716 693 8813

DROITWICH SPA

POINTON WAY, STONEBRIDGE CROSS BUSINESS PARK DROITWICH SPA, WORCESTERSHIRE UNITED KINGDOM, WR9 OLW +44 8444 145 145

MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM, M11 2ET
+44 8444 145 145

BANGALORE

#59, FIRST FLOOR, 3RD MAIN MARGOSA ROAD, MALLESWARAM BANGALORE, INDIA, 560 003 +91 80 4906 3555

SHANGHAI

unit 903, 888 north sichuan rd. Hongkou district, shanghai China, 200085 +86 21 5237 0909

SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES SAO PAULO, BRAZIL +55 11 4785 1330

LYON

93 RUE DE LA VILLETTE LYON, 69003 FRANCE +33 4 26 83 78 74

DUBAI

JAFZA VIEW 19, OFFICE 402 P.O.BOX 18226 JAFZA, DUBAI - UNITED ARAB EMIRATES +971 4 887 6775

MANNHEIM

DYNAMOSTRASSE 13 68165 MANNHEIM GERMANY +49 621 3999 9858

JIMBOLIA

STR CALEA MOTILOR NR. 2C
JIMBOLIA 305400, JUD.TIMIS
ROMANIA
+40 256 360 030

ARMSTRONG FLUID TECHNOLOGY

ESTABLISHED 1934

For more information on Armstrong Fire Pumps please contact your local Armstrong representative or visit our website at:

ArmstrongFluidTechnology.com

