

## **E-Coating**

## White paper

File No: 100.2011

Date: AUGUST 22, 2023

Supersedes: 100.2011

Date: DECEMBER 8, 2020

Questions on Data Center Cooling Efficiency? Contact the authors here: info@armstrongfluidtechnology.com

Other whitepapers you might be interested in:

- Conversion from Constant flow to Variable flow
- Design Envelope IPC in humid applications

-			

# How E-Coating pumps can reduce maintenance and repair costs and improve HVAC system efficiency

Without a protective coating, iron components exposed to water will naturally oxidize and introduce rust to a system. Cathodic Electrodeposition (CED) coating, commonly known as E-coating, can be applied to pumps as an effective method of preventing oxidization and erosion.

In HVAC applications, during periods of inactivity, the formation of rust between the impeller and the casing can cause the impeller to stick or seize. Prevention of seizing requires regular maintenance. When maintenance practices are neglected and a pump seizes, the issue may require repair or even a complete replacement of the pump. If a pump is seized after long periods of inactivity, maintenance personnel may have to jog the pump or externally torque the pump with a wrench to break the seizure.

In some fluid-flow applications, the system fluid can cause wear or erosion in a pump casing over years of operation. Eventually this results in enlarged clearances between the impeller and casing, increased internal leakage, and reduced efficiency. Erosion and oxidation on internal surfaces of pump volutes and piping can also reduce system efficiency. Surfaces that are rough or pock-marked increase hydrodynamic drag, which increases energy costs.

In addition to seizing and reduced pumping efficiency, oxidation of surfaces within the pump can have serious consequences for components of the broader mechanical system. Particles of rust entrained in the system fluid can clog filters or cause degradation in boilers, chillers and valves.

The E-coating process involves submerging a metal part in a bath of paint emulsion and then applying an electrical current that binds the paint to all surfaces of the part. The result is a thin, uniform coating on all surfaces that provides corrosion resistance and abrasion resistance.

The application of E-coating prevents oxidation, which in turn avoids the issue of seizing and prevents damage to the pump during start-up. E-coating a pump also protects internal surfaces from erosion, averting the declines in hydraulic performance and efficiency that would otherwise occur.

FIGURE 1: RUSTING ON THE CASING WITHOUT E-COATING





### FIGURE 2: WATER LEAKAGE FROM RUSTED CASING, WITHOUT E-COATING



#### **KEY VALUES OF E-COATING**

- Reduced energy costs By eliminating or delaying the decline of pump performance and efficiency caused by internal corrosion and surface roughness, e-coatings can provide important energy savings.
- Reduced lifecycle costs E-coating yields savings on pump maintenance, repair, and related downtime.
- Reduced component costs E-coating can be used in a variety
  of fluid applications for which uncoated cast iron may not
  be chemically compatible. Without E-coating application
  specifications may require that component manufacturers use
  more expensive metals.
- Preserves the performance and efficiency of other components by eliminating the movement of rust into the larger HVAC system.

FIGURE 3: CASING WITH E-COATING



For best efficiency, reduced maintenance and repair costs, and improved uptime, E-coating is always recommended for pumps.

#### TORONTO

23 BERTRAND AVENUE, TORONTO, ONTARIO, CANADA, M1L 2P3 +1 416 755 2291

#### BUFFALO

93 EAST AVENUE, NORTH TONAWANDA, NEW YORK, USA, 14120-6594 +1 716 693 8813

#### DROITWICH SPA

POINTON WAY, STONEBRIDGE CROSS BUSINESS PARK, DROITWICH SPA, WORCESTERSHIRE, UNITED KINGDOM, WR9 OLW +44 121 550 5333

#### MANCHESTER

WOLVERTON STREET, MANCHESTER UNITED KINGDOM, M11 2ET +44 161 223 2223

#### BANGALORE

#18, LEWIS WORKSPACE, 3<sup>80</sup> FLOOR, OFF MILLERS - NANDIDURGA ROAD, JAYAMAHAL CBD, BENSON TOWN, BANGALORE, INDIA 560 046 +91 80 4906 3555

#### SHANGHAI

unit 903, 888 north sichuan rd. Hongkou district, shanghai China, 200085 +86 21 5237 0909

#### BEIJING

ROOM 1612, NANYIN BUILDING NO.2 NORTH EAST THRID RING ROAD CHAOYANG DISTRICT, BEIJING, CHINA 100027 +86 21 5237 0909

#### SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES, SAO PAULO, BRAZIL +55 11 4785 1330

#### LYON

93 RUE DE LA VILLETTE LYON, 69003 FRANCE +33 4 26 83 78 74

#### DUBAI

JAFZA VIEW 19, OFFICE 402 P.O.BOX 18226 JAFZA, DUBAI - UNITED ARAB EMIRATES +971 4 887 6775

#### JIMBOLIA

STR CALEA MOTILOR NR. 2C JIMBOLIA 305400, JUD.TIMIS ROMANIA +40 256 360 030

#### FRANKFURT

WESTERBACHSTRASSE 32, D-61476 KRONBERG IM TAUNUS GERMANY +49 6173 999 77 55 Questions on Data Center Cooling Efficiency? Contact the authors here: info@armstrongfluidtechnology.com

Other whitepapers you might be interested in:

- Conversion from Constant flow to Variable flow
- Design Envelope IPC in humid applications

ARMSTRONG FLUID TECHNOLOGY® ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM