



ARMSTRONG



Split Coupled Vertical In-Line Pumps

File no.:	43.10IN
Date:	AUGUST 14, 2013
Supersedes:	43.10IN
Date:	FEBRUARY 05, 2013

Best commercial HVAC pump design available since 1969



Life cycle value at every turn:

Installation

Vertical In-Line pumps, being integral components of the pipework, eliminate need for inertia bases, inertia base springs, flexible pipe connectors, field grouting and alignment. Pipe hangers sized for the weight of pump, piping and fittings are the only supports required. Pipe stools, with vibration isolating pads, may be installed under each pipe leg.

Space saving

Greatest floor space savings result when Vertical In-Line pumps are installed with Armstrong Suction Guides and Flo-Trex valves shown on the inlet and outlet of the pump above. Equivalent base mounted, horizontal split case pumps may take three times more floor space.

Maintenance

The mechanical seal is the critical service item in any pump. Removal of the Series 4300 split spacer coupling allows all mechanical seal components to be withdrawn for servicing, through the resulting space between pump and motor shafts, without disturbing other pump components or motor connection. Re-installing the rigid coupling brings the unit rotating assembly back to factory alignment specifications.

Reliability

Dynamically balanced impeller and shaft assembly rotating vertically on the Series 4300 centerline translate to a quiet, long-lasting pump with minimum vibration, as static shaft deflection is eliminated. There are no pump bearings to service in the Vertical In-Line design. Series 4300 is a reliable, time-proven unit with less down time.


Flexibility

Small footprint, low installation costs, reliable and easy to maintain. These features, combined with flow range in excess of 6800 m³/hr, affirms the Series 4300 as the most flexible pump design available.

Design features

Split coupled



- ① Industry standard motor designed for Vertical In-Line operation.
- ② Heavy cylindrical bracket with 360° register on each flange provides a rigid union of pump and motor.
- ③ Motor shaft run-out limited to 0.025 mm (0.001") TIR (Total Indicator Reading).
- ④ Axially split, spacer type rigid coupling permits seal maintenance without disturbing pump or motor. Lightweight high tensile aluminum, precision bored and designed to reduce bearing load.
- ⑤ Shaft deflection at mechanical seal limited to 0.05 mm (0.002") TIR.
- ⑥ Mechanical seal, accessible and easily replaceable outside multi-spring balanced mechanical seal illustrated, see page 5 for mechanical seal options).
- ⑦ Gland plate with flush connection ensures liquid at seal faces and positive venting of seal chamber.
- ⑧ Dynamically balanced impeller assures smooth vibration-free operation.
- ⑨ Radially split volute with equal suction and discharge flange sizes. Separate drilled and tapped openings for gauge, flush and drain connections.
- ⑩ Liberal inlet passageways and straightening vanes provide optimum suction performance and quiet operation.
- ⑪ Ribs cast integral with volute. Machined surface to accept floor support when specified.
- ⑫ Confined casing gasket to meet stringent industrial temperature and pressure applications.
- ⑬ OSHA coupling guard fully encloses access openings (not shown).



Enwave District Cooling Facility, Toronto, Canada.



District Cooling Project, Phoenix, U.S.A.



Split Coupled Vertical In-Line Pumps

Materials of construction

PUMP SERIES	ANSI FLANGE RATING PSIG	CONSTRUCTION	VOLUTE	GASKET	IMPELLER	CAPSCREW	WASHER	ACORN NUT	ADAPTER COVER	ADAPTER BRACKET	STUFFING BOX COVER	PUMP SHAFT	COUPLING	GLAND PLATE
4300	PN 16	BF	CI	F	BZ	S	SS-3	BR-2	CI	CI	CI	SS-6	AL	SS-5
	PN 16	AI	CI	F	CI	S	SS-3	S	CI	CI	CI	SS-6	AL	SS-5
	PN 16	AB	BZ	F	BZ	SS-5	SS-5	BR-2	BZ	CI	BZ	SS-6	AL	SS-5
	PN 25	DI	DI	F	CI	S	SS-3	S	DI	DI	DI	SS-6	AL	SS-5
	PN 25	DBF	DI	F	BZ	S	SS-3	BR-2	DI	DI	DI	SS-6	AL	SS-5

MATERIAL CONSTRUCTION CODE

BF - Iron body, Bronze fitted

AI - All iron

AB - All bronze

DI - Ductile iron

DBF - Ductile iron, Bronze fitted

AL - High tensile aluminum bar

BZ - Cast bronze ASTM B584 grade c84400

CI - Cast iron ASTM A48 class 30

DI - Cast ductile iron ASTM A536 grade 65-45-12

F - Fiber

s - Steel

BR-2 - Brass bar ASTM B16

SS-3 - Stainless steel ASTM A276 TYPE 303

SS-5 - Stainless steel ASTM A276 TYPE 316

SS-6 - Stainless steel ASTM A276 TYPE 416

Pressure/temperature parameters*

Cast iron - PN 16 flanges

Pressure up to 16 bar (232 psi)

Temperature upto 149°C (300°F)

Ductile iron - PN 25 flanges

Pressure up to 25 bar (375 psi)

Temperature upto 149°C (300°F)

*Please view ACEONLINE or submittal data for full details

Design and testing standards

Performance testing: HI/ANSI: 14.6 GR2 - 3" & smaller,

EN/ISO: ISO 9906 GR2 - 3" & smaller

Flange rating: ANSI B16.1, BS/EN 1092-2

Impeller balancing: HI/ANSI/EN/ISO 1940/1

Vibration/noise level: HI/ANSI 9.6.4

Pump design: HI/ANSI 9.3

Mechanical seal: HI/ANSI 1.3.4.7.6

Nozzle load: HI 9.6.2, ISO 5199, EN 5199




Dr. Arnaldo Hospital for women, Sao Paulo, Brazil.




Canary Wharf Tower Building, London, England.

Split coupled

The axially split, spacer type rigid coupling permits seal maintenance without disturbing the pump or motor connections. The mechanical seal is accessible and easily replaced. (Outside multi-spring balanced mechanical seal is illustrated).



1) Split coupling with outside seal. Axially split coupling shown with coupling guard removed. Coupling bolts are still in place. Rotating element of seal is seen below the coupling, above gland plate.



2) Remove the coupling bolts. The coupling halves (with drive and annular positioning keys) are taken from motor and pump shafts. Loosen set screws on seal rotating element and slide from pump shaft. (For inside seal see step 3)




3) Disconnect seal flush line and remove gland plate bolts. The gland plate and seal seat may then be taken out between the space in the shafts. With inside seal the complete seal is removed following the gland plate.




4) New Seal may now be installed. Reverse the procedure: Install new seal, replace gland plate, replace coupling and restart pump. Rigid coupling retains factory alignment.

Sealing arrangements

Armstrong series 4300 split coupled Vertical In-Line pumps are available with two mechanical seal arrangements. Both can be removed easily and quickly for servicing without costly removal of the motor or pump from the piping. The high performance outside type mechanical seal combines the advantages of a multi-spring balanced seal with premium quality and is the easiest to remove. The inside type mechanical seal provides an economical alternative.



- ① Pump shaft
- ② Rotating hardware
- ③ Spring(s)
- ④ Secondary seal
- ⑤ Rotating face
- ⑥ Stationary seat
- ⑦ Gland plate
- ⑧ Throttle bushing



Typical specifications


- 1 Provide Vertical In-Line (VIL) pumps, single stage, single or double suction type, with pump characteristics which provide rising heads to shut off. Refer to pump schedule for pump flows and heads and motor speed, enclosure, efficiency and power requirements and other system conditions. Provide Armstrong Series 4300 split-coupled type VIL units, with rigid spacer type coupling.
- 2 Pump construction: Pump casing - Cast iron with PN16 flanges for working pressure below 16 bar (232 PSI) and Ductile iron with PN25 flanges for working pressures to 25 bar (375 PSI). Suction and discharge connections shall be flanged and the same size and shall be drilled and tapped for seal flush and gauge connections.
- 3 Impeller - Bronze, fully enclosed type. Dynamically balanced. Two-plane balancing is required where installed impeller diameter is less than six times the impeller width.
- 4 Shaft - Provide stainless steel pump shaft.
- 5 Coupling - Rigid spacer type of high tensile aluminum alloy. Coupling to be designed to be easily removed on site to reveal a space between the pump and motor shafts sufficient to remove all mechanical seal components for servicing and to be replaced without disturbing the pump or motor.
- 6 Mechanical seals - Shall be stainless steel multi-spring outside balanced type with viton secondary seal, carbon rotating face and silicon carbide stationary seat. Provide 316 stainless steel gland plate. Provide factory installed flush line with manual vent.
- 7 All split coupled pumps shall be provided with a lower seal chamber throttle bushing to ensure seals maintain positively cooling and lubrication.
- 8 Seal flush line accessories, if required to improve seal chamber cleanliness: Supply in the flush line to the mechanical seal a 50 micron cartridge filter and sight flow indicator, to suit the working pressure encountered. If pressures exceed 21 m/70 ft/30 psig/200 kPa, a maintenance-free sediment separator, with sight flow indicator can be used.
- 9 Motor power requirements shown on the pump schedule are the minimum acceptable and have been sized for continuous operation without exceeding the full load name plate rating over the entire pump curve, exclusive of service factor.

Other Armstrong products

For even greater space savings, ease of installation and flexibility of use:

Specify Armstrong **dualArm** Vertical In-Line pump.

- Two (2) Armstrong time proven Vertical In-Line pumps in one (1) casing.
- Eliminates a complete set of piping and fittings.
- Stand-by or two pump parallel operation with no loss of single pump efficiency.
- Remove one pump for repair while the second pump continues to operate.



TORONTO
23 Bertrand Avenue
Toronto, Ontario
Canada, M1L 2P3
T +1 416 755 2291
F +1 416 759 9101

MANCHESTER
Wenlock Way
Manchester
United Kingdom, M12 5JL
T +44 (0) 8444 145 145
F +44 (0) 8444 145 146

BANGALORE
#59, First floor 3rd Main,
Margosa road, Malleswaram,
Bangalore India, 560 003
T +91 (80) 4906 3555
F +91 (80) 2334 3535

ARMSTRONG 

©ARMSTRONG FLUID TECHNOLOGY 2013