## **ARMSTRONG®**

## SERIES 4302 8 x 8 x 8 dualArm

FILE NO.:	43dL.527
DATE:	May 30, 2000
SUPERSEDES:	NEW
DATE:	NEW

## **SUBMITTAL**

Job:	Representative:		
	Order No:	Date:	
Engineer:	Submitted By:	Date:	
Contractor:	Approved By:	Date:	

PUMP DESIGN DATA						
No. of Pumps:						
Tag:						
Capacity:	m³/ h (l/s) USgpm	Head:		m (ft)		
Liquid:	WATER	Viscosity:	1.0 cps			
Temperature:	16°C (60°F)	Specific Gravity:	1.0			

MOTOR DESIGN DATA							
HP:		RPM:	-				
Frame Size:		Enclosure:	-				
Volts:	Hertz: 50 Hz	Phase:	-				
Efficiency:	<ul><li>Standard</li></ul>	□ Premium					
	□ Level %						

**FLANGE SIZE** 

MATERIALS OF CONSTRUCTION								
ANSI Flange Rating		125 lb. Cast li	ron	□ 250 lb. E	Ouctile Iron			
Construction	■ Bronze Fitted	□ All Iron	□ All Bronze	■ Bronze Fitted	■ Ductile Iron			
Casing	Cast Iron	Cast Iron	Bronze	Ductile Iron	Ductile Iron			
Impeller	Bronze	Cast Iron	Bronze	Bronze	Cast Iron			
Flush Line	Copper	Steel	Copper	Copper	Steel			
Pump Shaft		4	16 Stainless S	teel				
Coupling		Hiç	jh Tensile Alun	ninum				
Gasket	Confined Non-Asbestos							
Valve (s)			Stainless Ste	el				

Suction: 8 "	Discharge:	8 "					
MECHANICAL SE	AL DESIGN DATA	A					
See File No.43.50 for standard mechanical seal details as indicated below Armstrong Seal Reference Number							
C 1(a)							


MAXIMUM PUMP OPERATING CONDITIONS								
125 lb. Cast Iron	250 lb. Ductile Iron							
12 bars at 60 °C (175 psig at 140°F)	26 bars at 38 °C (375 psig at 100°F)							
7 bars at 149°C (100 psig at 300°F)	19 bars at 260°C (210 psig at 250°F)							

OPTIONAL EQUIPMENT



- Tolerance of ±3 mm (±0.125") should be used on dimensions shown below.
- For exact installation data please contact factory for certified dimensions.
- See page 2 for performance curves.
- Pump equipped with casing drain plug and 1/4" NPT suction and discharge gauge ports.

PUMP DIMENSIONS mm (inches)									
A1 A2 B1 B2 C1 C2 D									
mm	470	584	254	229	476	476	241	1156	
(inches)	(18.50)	(23)	(10)	(9)	(18.75)	(18.75)	(9.50)	(45.5)	



MOTOR HORSEPOWER					N	* ASSEMBI	LY WEIGHT			
00	)P	TE	FC	Frame	ODP / TEFC				kg (	(lbs)
3000	1500	3000	1500		E	F	Н	Х	ODP	TEFC
	5		5	184TC	162 (6.38)	241 (9.50)	692 (27.25)	806 (31.75)	354.1 (780)	363.2 (800)
	7.5		7.5	213TC	194 (7.63)	283 (11.13)	740 (29.13)	870 (34.25)	381.4 (840)	395.0 (870)
	10		10	215TC	194 (7.63)	283 (11.13)	778 (30.63)	870 (34.25)	390.4 (860)	408.6 (900)

\* Assembly weight combines pump and motor