


PUMP SIZE	MOTOR KW	FLC AMPS 3x415V	PUMP WEIGHT KGS	SET WEIGHT KGS	VESSEL SIZE LITRES	WORKING PRESSURE BAR	TEST PRESSURE BAR
402T05T	0.55	1.43	17.5	317	60	10	15.0
403T05T	0.55	1.43	18.5	321	60	10	15.0
404T07T	0.75	2.02	21.0	331	60	10	15.0
405T11T	1.10	2.61	22.0	335	60	10	15.0
406T11T	1.10	2.61	22.5	337	60	10	15.0
407T11T	1.10	2.61	23.0	339	60	10	15.0
408T15T	1.50	3.45	29.5	365	60	10	15.0
409T15T	1.50	3.45	30.0	367	60	10	15.0
411T21T	2.20	5.03	32.0	375	20	15	22.5
413T21T	2.20	5.03	33.0	379	20	15	22.5
414T30T	3.00	6.22	39.0	403	20	15	22.5

ALL FLANGES TO BS4504 16BAR



ANTI-VIBRATION MOUNTINGS OPTIONAL ONLY SUPPLIER WHEN ORDERED (4-PER SET K2092/1)

FLEXIBLE CONNECTORS OPTIONAL ONLY SUPPLIED WHEN ORDERED (2-PER SET)

NOTE :-

- 1) MAIN POWER SUPPLY TO PANEL MUST BE SIZED TO COVER ALL PUMP RUNNING AT SAME TIME
- 2) LARGE STORAGE VESSELS IF ORDERED WILL BE SUPPLIED LOOSE FOR POSITIONING BY CLIENT TO SUIT THE AVAILABLE FLOOR SPACE CLIENT IS TO PROVIDE A CONNECTION FROM THE VESSEL TO THE DELIVERY PIPEWORK ADJACENT TO THE SET ISOLATING AND DRAIN VALVES SHOULD BE FITTED IN THIS CONNECTION

LAST MODIFICATION DETAILS

DRAWING BORDER CHANGED	ALL DIMENSIONS IN mm DRAWN TO BS308 WELDING SYMBOLS TO BS499 SURFACE FINISH SHOWN IN MICROMETERS MACHINE WHERE SHOWN TO TOLERANCE ± 0.3MM UNLESS OTHERWISE STATED
ISSUE DATE: 15/02/2006	CHK: PJB
APP: PJB	

JOB No. - PART No. - WEIGHT KG - FILE NAME -

DESIGN No. -	PATTERN No. -	MATERIAL -	MAT'L SPEC. -
THIS DRAWING IS THE PRIVATE AND CONFIDENTIAL PROPERTY OF ARMSTRONG HOLDEN BROOKE PULLEN LTD. ALL COPYRIGHT, MANUFACTURING AND SALES RIGHTS RESERVED.			

TITLE

GENERAL ARRANGEMENT
HYDROPAK IVSL4 SET
4-PUMP MODELS C/W
VLT8000 AQUA CONTROL

DRG No. PX10467-1

DATE: 19/08/2004	DRN: BSD
CHK: EGU	APP: EGU
SCALE: NTS	SHEET: 1 OF 1



VENLOCK WAY, MANCHESTER, M12 5JL
TEL: +44 (0) 161 223 2223