

4030 END SUCTION BASE MOUNTED | 100-250A (5×4×10) | SUBMITTAL

File No: 40.64IEC
Date: AUGUST 10, 2020
Supersedes: 40.64IEC
Date: APRIL 26, 2016

Job: _____ Representative: _____
Order no.: _____ Date: _____
Engineer: _____ Submitted by: _____ Date: _____
Contractor: _____ Approved by: _____ Date: _____

PUMP DESIGN DATA

No. of pumps: _____ Tag: _____
Capacity: _____ m³/h (USgpm) Head: _____ m(ft)
Liquid: _____ Viscosity: _____
Temperature: _____ °C (°F) Specific gravity: _____
Suction: 125 mm (5") Flanged
Discharge: 100 mm (4") Flanged

MATERIALS OF CONSTRUCTION

FLANGE RATING	PN 16	PN 25
Construction	<input type="checkbox"/> BF	<input type="checkbox"/> DBF
Casing	Cast iron	Ductile iron

Impeller: Bronze
Gasket: Confined non-asbestos fiber
Bearing frame: Cast iron
Anti-friction bearings: Permanently lubricated
Shaft: Carbon steel
Shaft sleeve: Stainless steel
Coupler: Woods sure flex or equal
Coupler guard: Steel OSHA
Baseplate: Fabricated steel

MECHANICAL SEAL DATA

Seal type: 2A **Stationary seat:** Silicone carbide
Secondary seal: EPDM **Rotating hardware:** Stainless steel
Spring: Stainless steel

MOTOR DESIGN DATA

kW: _____ RPM: _____
Frame size: _____ Enclosure: _____
Volts: _____ Hertz: 50 Hz Phase: 3
Efficiency: IE1 IE2 IE3

MAXIMUM PUMP OPERATING CONDITIONS

PN 16
16 bars at 49°C (232 psig at 120°F)
7 bars at 150°C (100 psig at 300°F)
PN 25
25 bars at 65°C (362 psig at 149°F)
21 bars at 150°C (304 psig at 300°F)

- Tolerance of ±3 mm (±0.125") should be used
- For exact installation, data please write factory for certified dimensions
- Pump equipped with casing drain plug and ¼" NPT suction and discharge gauge ports.
- See performance curves on page 3

OPTIONAL EQUIPMENT

FLUID TYPE	ALL GLYCOLS > 30% WT CONC		ALL OTHER NON-POTABLE FLUIDS		POTABLE (DRINKING) WATER	
	up to 93°C (200°F)	over 93°C (200°F)	up to 93°C (200°F)	over 93°C (200°F)	up to 93°C (200°F)	over 93°C (200°F)
Rotating face	Silicone carbide		Resin bonded carbon	Antimony loaded carbon	Resin bonded carbon	
Seat elastomer	EPDM (L-cup)	EPDM (O-ring)	EPDM (L-cup)	EPDM (O-ring)	EPDM (L-cup)	EPDM (O-ring)
Material code	SCsc L EPSS 2A	SCsc O EPSS 2A	C-SC L EPSS 2A	ACsc O EPSS 2A	C-SC L EPSS 2A	C-SC O EPSS 2A


MOTOR	MOTOR kW @ RPM		FULL LOAD CURRENT (A)	STARTING CURRENT (A)		DIMENSIONS mm(INCHES)								WEIGHT*
	TEFC			STAR DELTA (SD)	DIRECT ON LINE (DOL)	HA	HB	HC	HD	HE	HF	HG	HL	kg (lbs)
FRAME	3000	1500	380-415V											
100L	-	3	6.4	-	37.1	406 (16.00)	1016 (40.00)	739 (29.11)	330 (13.00)	187 (7.38)	914 (36.00)	76 (3.00)	114 (4.50)	141.9 (313)
112M	-	4	8.41	18.5	58.9	406 (16.00)	1016 (40.00)	783 (30.85)	330 (13.00)	187 (7.38)	914 (36.00)	76 (3.00)	114 (4.50)	150.9 (333)
132S	-	5.5	10.90	24.0	81.8	356 (14.00)	838 (33.00)	856 (33.72)	330 (13.00)	162 (6.38)	737 (29.00)	76 (3.00)	114 (4.50)	171.9 (379)
132M	-	7.5	14.90	32.8	111.8	356 (14.00)	838 (33.00)	879 (34.62)	330 (13.00)	162 (6.38)	737 (29.00)	76 (3.00)	114 (4.50)	180.9 (399)
160M	-	11	21.9	50.4	168.6	406 (16.00)	1143 (45.00)	1082 (42.60)	330 (13.00)	187 (7.38)	1041 (41.00)	76 (3.00)	114 (4.50)	213.9 (471)
180M	22	-	40.9	114.5	368.1	483 (19.00)	1219 (48.00)	1082 (42.60)	356 (14.00)	225 (8.88)	1118 (44.00)	102 (4.00)	114 (4.50)	272.9 (602)
200L	30	-	55.9	139.8	436.0	483 (19.00)	1219 (48.00)	1259 (49.58)	356 (14.00)	225 (8.88)	1118 (44.00)	102 (4.00)	114 (4.50)	334.9 (738)
200L	37	-	68.7	171.8	535.9	483 (19.00)	1219 (48.00)	1259 (49.58)	356 (14.00)	225 (8.88)	1118 (44.00)	102 (4.00)	114 (4.50)	363.9 (802)
225M	45	-	81.5	179.3	570.5	483 (19.00)	1219 (48.00)	1294 (50.96)	356 (14.00)	225 (8.88)	1118 (44.00)	102 (4.00)	114 (4.50)	464.9 (1025)
250M	55	-	99.2	218.2	694.4	483 (19.00)	1473 (58.00)	1405 (55.33)	396 (15.60)	225 (8.88)	1372 (54.00)	102 (4.00)	114 (4.50)	521.9 (1150)
280S	75	-	135.0	324.0	1012.5	483 (19.00)	1473 (58.00)	1543 (60.75)	434 (17.10)	225 (8.88)	1372 (54.00)	102 (4.00)	114 (4.50)	738.9 (1629)

*Assembly weight combines pump and motor.


PUMP DIMENSIONS

mm (inches)

X	Y
318 (12.50)	102 (4.00)



4030 PERFORMANCE CURVES



Curve number
PT97-1-0-3000

Series
4030
4280

Size
100-250A


RPM
3000

BHP based on shown
Fluid's sp. gr.

Availability
4030 all ratings
4280 all ratings

Performance
guaranteed only at
operating point
indicated.

Curve shown for
clear, cold water
- SP. GR. 1.000



Curve number
PT96-1-0-1500

Series
4030
4280

Size
100-250A

RPM
1500

kwa based on shown
Fluid's sp. gr.

Availability
4030 all ratings
4280 all ratings

Performance
guaranteed only at
operating point
indicated.

Curve shown for
clear, cold water
- SP. GR. 1.000

Performance curves are for reference only.
Confirm current performance data with Armstrong ADEPT Quote or ADEPT Select selection software.

TORONTO

23 BERTRAND AVENUE
TORONTO, ONTARIO
CANADA, M1L 2P3
+1 416 755 2291

BUFFALO

93 EAST AVENUE
NORTH TONAWANDA, NEW YORK
U.S.A., 14120-6594
+1 716 693 8813

BIRMINGHAM

HEYWOOD WHARF, MUCKLOW HILL
HALESOWEN, WEST MIDLANDS
UNITED KINGDOM, B62 8DJ
+44 8444 145 145

MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM, M11 2ET
+44 8444 145 145

BANGALORE

#59, FIRST FLOOR, 3RD MAIN
MARGOSA ROAD, MALLESWARAM
BANGALORE, INDIA, 560 003
+91 80 4906 3555

SHANGHAI

UNIT 903, 888 NORTH SICHUAN RD.
HONGKOU DISTRICT, SHANGHAI
CHINA, 200085
+86 21 5237 0909

SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO,
1370 GALPÃO 6 EMBU DAS ARTES
SAO PAULO, BRAZIL
+55 11 4785 1330

LYON

93 RUE DE LA VILLETTE
LYON, 69003 FRANCE
+33 4 26 83 78 74

DUBAI

JAFZA VIEW 19, OFFICE 402
P.O.BOX 18226 JAFZA,
DUBAI - UNITED ARAB EMIRATES
+971 4 887 6775

MANNHEIM

DYNAMOSTRASSE 13
68165 MANNHEIM
GERMANY
+49 621 3999 9858