

## Vertical Multistage Pumps


## VMS 6 B - 2 pole - DIN

## SUBMITTAL

JOB: _____	REPRESENTATIVE: _____
_____	_____
ENGINEER: _____	ORDER NO: _____ DATE: _____
CONTRACTOR: _____	SUBMITTED BY: _____ DATE: _____
	APPROVED BY: _____ DATE: _____


### VM Closed coupled motor Construction type; IM 3619

CONNECTION	MIN. PRESSURE CLASS OPTIONS	MOTOR DIMENSIONS			VMS(S)-/E/V/T		VMS(C/S)F		UNIT WEIGHT
MODEL		kW	E1	E2	F1		F1		KG
6/2	PN10	0.37	138	109	427		452		17.9
6/3		0.75	160	150	496		521		24.7
6/4		1.1	160	150	521		546		25.2
6/5		1.1	160	150	546		571		25.7




### V Long coupled motor Construction type; V18


CONNECTION	MIN. PRESSURE CLASS OPTIONS	MOTOR DIMENSIONS			VMS(S)-/E/V/T		VMS(C/S)F		UNIT WEIGHT
MODEL		kW	E1	E2	F1	F2	F1	F2	KG
6/2	PN10	0.37	138	109	479	266	504	291	17.9
6/3		0.75	160	150	558	301	583	326	24.7
6/4		1.1	160	150	583	326	608	351	25.2
6/5		1.1	160	150	608	351	633	376	25.7
6/6		1.5	185	160	639	386	664	411	31.7
6/7		1.5	185	160	664	411	689	436	32.3
6/8		2.2	185	160	718	436	743	461	33.8
6/9		2.2	185	160	743	461	768	486	34.3
6/10		2.2	185	160	768	486	793	511	35.1
6/11		PN16	3	205	175	835	521	860	546
6/12	3		205	175	860	546	885	571	45.8
6/14	3		205	175	910	596	935	621	46.8
6/16	4		220	190	969	646	994	671	55.1
6/18	PN25/40	4	220	190	1016	696	1044	721	61.5



### V1 motor


CONNECTION	MIN. PRESSURE CLASS OPTIONS	MOTOR DIMENSIONS			VMS (S) -/E/V/T		VMS (C/S)F		UNIT WEIGHT
MODEL		kW	E1	E2	F1	F2	F1	F2	KG
6/20	PN25 PN40	5.5	260	220	1168	821.5	1193	847	96.1
6/22		5.5	260	220	1218	871.5	1243	897	97.1
6/24		5.5	260	220	1268	921.5	1293	947	98.0
6/26		5.5	260	220	1318	971.5	1343	997	99.0






### VMS E Male thread -

With non return valve insert at discharge side and pressure measurement plug at upstream side  
 Norm: G EN ISO 228  
 Size: G 6/4  
 Pressure Class: PN16  
 Option: Base plate in cast SS 1.4308




### VMS (S)

Counter flange with female thread included  
 DPV: Cataphoric coated cast iron  
 DPVS: Cast Stainless steel 1.4408  
 Norm: G EN ISO 228  
 Size: G 5/4  
 Pressure Class: PN16  
 Option: Flange and base plate in SS1.4308




### VMS (S) V Victaulic

Norm: -  
 Size: 42.2  
 Pressure Class: PN25  
 Option: Base plate in SS 1.4308




### VMS S T Tri-Clamp

Norm: 32676  
 Size: DN32  
 Pressure Class: PN416  
 Option: Baseplate in cast SS 1.4308



### VMS C F Cast Iron Flange

Norm: EN 1092-1/1092-2  
 Size: NW32  
 Pressure Class: PN40



### VMS (S) F Round collar flange

Cataphoric coated collar flange  
 Norm: EN 1092-1/1092-2  
 Size: NW32  
 Pressure Class: PN40  
 Option: Collar flange and/or base plate in cast SS 1.4308

#### ARMSTRONG INTEGRATED LIMITED

Wenlock Way  
 Manchester  
 United Kingdom, M12 5JL  
**T:** +44 (0) 8444 145 145  
**F:** +44 (0) 8444 145 146

#### S. A. ARMSTRONG LIMITED

23 Bertrand Avenue  
 Toronto, Ontario  
 Canada, M1L 2P3  
**T:** 416 755 2291  
**F:** 416 759 9101