

DESIGN ENVELOPE 4300 VIL 0208-003.0 SUBMITTAL

Armstrong seal reference number

☐ Others: __

□ c1 (a)

File No: 100.4036

Date: DECEMBER 17, 2015

Supersedes: 100.4030


Date: AUGUST 14, 2015

Job:		Represe	ntative:	
		Order N	0:	Date:
Engineer: Subn		Submitt	ed by:	Date:
Contractor: Appro		Approve	ed by:	Date:
PUMP DESIGN DATA		:	CONTROLS DATA	
No. of pumps:	Tag:		Sensorless Control:	Standard
Capacity:USgpm (L/s)	Head:f	t (m)	Minimum system pressure to be maintained:	ft (m)*
Temperature: °F (°C)			Orientation:	□ L1 (default) □ L2 □ L3 □ L4
Suction: 2" (50mm)	Discharge: 2" (50mm	•	Protocol (standard):	☐ Modbus RTU ☐ BACnet™ MS/TP☐ Johnson® N2 ☐ Siemens® FLN
OSHPD Seismic Certification OSP-	•	:	Protocol (optional):	☐ LonWorks®
UL STD 778 & CSA STD C22.2 NO.108 certified MOTOR DESIGN DATA HP: RPM: Frame size: Enclosure:			Enclosure:	☐ Indoor - UL TYPE 12 ☐ Outdoor - UL TYPE 4x with Weather Shield ☐ Outdoor - UL TYPE 4x less Weather Shield
Volts: Hertz: 60 H			Fused disconnect switch:	
Efficiency: NEMA premium 12.12			EMI/RFI control:	Integrated filter designed to meet EN61800-3
MAXIMUM PUMP OPERATIN	IG CONDITIONS	:	Harmonic suppression:	Dual pc-link reactors (Equivalent: 5% Ac line reactor) Supporting IEEE 519-1992 requirements**
ANSI 125 175 psig at 150°F (12 bars at 65°C)		:	Cooling:	Fan-cooled through back channel
100 psig at 300°F (7 bars at 150°C)			Ambient temperature:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)
ANSI 250 375 psig at 150°F (26 bars at 65°C)				Two current or voltage inputs, one current output
260 psig at 300°F (21 bars at 150°C)			Digital ı/o:	Six programmable inputs (two can be configured as outputs)
 Tolerance of ±0.125" (±3 mm) should be used For exact installation, data please write factory for 			Pulse inputs:	Two programmable
certified dimensions			Relay outputs:	Two programmable
			Communication port:	1-RS485, 1-USB
MECHANICAL SEAL DESIGN	DATA			
See file no. 43.50 for standard mechanical seal details as indicated below			**The IVS 102 drive is a low harmonic d guaranty performance to any system	ure is not known: Default to 40% of design head rive via built-in DC line reactors. This does not n wide harmonic specification or the costs to meet and with the system electrical details. Armstrong

will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation

and the costs for such mitigation.

2



Performance curves are for reference only.


Confirm current performance data with Armstrong ACE Online selection software.


DIMENSION DATA

	INDOOR (UL TYPE 12/ODP)	OUTDOOR (UL TYPE 4X/TEFC)	
Frame size:	182	182	
Size:	2×2×8	2×2×8	
HP:	3	3	
RPM:	1800	1800	
AB:	27.55(700)	33.51(851)	
в:	5.80(147)	5.80(147)	
c:	5.80(147)	5.80(147)	
D:	8.50(216)	8.50(216)	
E:	12.56(319)	17.83(453)	
P:	10.38(264)	9.56(243)	
F:	237(107.5)	27.33(694)	
s:	9.50(241)	9.50(241)	
SD:	18.00(457)	18.00(457)	
T:	5.09(129)	5.09(129)	
XY:	26.54(674)	26.42(671)	
Weight:	249(112.9)	280(127.0)	

Dimensions - inch (mm) Weight - lbs (kg)

OUTDOOR





+1 716 693 8813 BIRMINGHAM

TORONTO +1 416 755 2291

BUFFALO

+44 (0) 8444 145 145

MANCHESTER

+44 (0) 8444 145 145

BANGALORE

+91 (0) 80 4906 3555

SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM

INDOOR

