

DESIGN ENVELOPE 4300 VIL 0611-030.0 SUBMITTAL

Armstrong seal reference number

☐ Others: _

□ c1 (a)

File No: 100.4124

Date: DECEMBER 17, 2015

Supersedes: 100.4116


Date: AUGUST 14, 2015

Job:	Rep	presentative:	
	Ord	der No:	Date:
Engineer:		omitted by:	Date:
Contractor:		proved by:	Date:
PUMP DESIGN DATA		CONTROLS DATA	
No. of pumps: Tag:		Sensorless Control:	Standard
Capacity:USgpm (L/s) Hea		4. 6	ft (m)*
Liquid: Viscon V			□ L1 (default) □ L2 □ L3 □ L4
	charge: 6" (150mm)	- :	☐ Modbus RTU ☐ BACnet™ MS/TP☐ Johnson® N2 ☐ Siemens® FLN
OSHPD Seismic Certification OSP-0422	2-10	: Protocol (optional):	
MOTOR DESIGN DATA HP: RPM: Frame size: Enclosure:		:	☐ Indoor - UL TYPE 12 ☐ Outdoor - UL TYPE 4X with Weather Shield ☐ Outdoor - UL TYPE 4X less Weather Shield
Volts: Hertz: 60 Hz		Fused disconnect switch:	
Efficiency: NEMA premium 12.12		EMI/RFI control:	Integrated filter designed to meet EN61800-3
MAXIMUM PUMP OPERATING CONDITIONS		Harmonic suppression:	Dual DC-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**
ANSI 125 175 psig at 150°F (12 bars at 65°C)		Cooling:	Fan-cooled through back channel
100 psig at 300°F (7 bars at 150°C)		Ambient temperature:	-10°C to +45°C up to 1000 meters abov sea level (-14°F to +113°F, 3300 ft)
ANSI 250 375 psig at 150°F (26 bars at 65°C)		Analog ı/o:	Two current or voltage inputs, one current output
260 psig at 300°F (21 bars at 150°C)		Digital ı/o:	Six programmable inputs (two can be configured as outputs)
 Tolerance of ±0.125" (±3 mm) should be used For exact installation, data please write factory for certified dimensions 		: Pulse inputs:	Two programmable
		: Relay outputs:	Two programmable
		Communication port:	1-RS485, 1-USB
MECHANICAL SEAL DESIGN DAT	ΓΑ		
See file no. 43.50 for standard mechanical seal details as indicated below		**The IVS 102 drive is a low harmonic of guaranty performance to any system	sure is not known: Default to 40% of design head drive via built-in pc line reactors. This does not m wide harmonic specification or the costs to meel lied with the system electrical details, Armstrong

will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation

and the costs for such mitigation.

2




Performance curves are for reference only.


 $Confirm\ current\ performance\ data\ with\ Armstrong\ ACE\ Online\ selection\ software.$


DIMENSION DATA


	INDOOR (UL TYPE 12/ODP)	OUTDOOR (UL TYPE 4X/TEFC)	
Frame size:	286	286	
Size:	6×6×11.5	6×6×11.5	
HP:	30	30	
RPM:	1800	1800	
AB:	42.56(1081)	47.96(1218)	
в:	9.88(251)	9.88(251)	
c:	8.64(219)	8.64(219)	
D:	16.50(419)	16.50(419)	
E:	18.48(470)	22.71(577)	
P:	13.38(340)	15.31(389)	
F:	36.98(939)	41.21(1047)	
s:	18.50(470)	18.50(470)	
SD:	35.00(889)	35.00(889)	
T:	9.75(248)	9.75(248)	
XY:	37.41(950)	43.54(1106)	
Weight:	965(437.7)	1060(480.8)	

Dimensions - inch (mm) Weight - lbs (kg)









TORONTO

+1 416 755 2291

BUFFALO

+1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER

+44 (0) 8444 145 145

BANGALORE

+91 (0) 80 4906 3555

SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM