

DESIGN ENVELOPE 4300 VIL 1415-300.0 SUBMITTAL

See file no. 43.50 for standard mechanical seal details as

indicated below

☐ c1 (a)

Armstrong seal reference number

☐ Others: _

File No: 100.4184

Date: DECEMBER 17, 2015

Supersedes: 100.4190


Date: AUGUST 14, 2015

Job:	Rep	presentative:	
	Ord	der No:	Date:
Engineer:		omitted by:	Date:
Contractor:		proved by:	Date:
PUMP DESIGN DATA		CONTROLS DATA	
No. of pumps:	Tag:	Sensorless Control:	Standard
Capacity:USgpm (L/s) Liquid:		to be maintained	ft (m)*
Temperature: °F (°C)		0.1	□ L1 (default) □ L2 □ L3 □ L4
Suction: 14" (350 mm)	Discharge: 14" (350 mm)		☐ Modbus RTU ☐ BACnet TM MS/TP☐ Johnson® N2 ☐ Siemens® FLN
OSHPD Seismic Certification OSP-0422-10 UL STD 778 & CSA STD C22.2 NO.108 certified MOTOR DESIGN DATA HP: RPM: Frame size: Enclosure:		Protocol (optional):	□ LonWorks®
		Enclosure:	☐ Indoor – UL TYPE 12
		Fused disconnect switch:	N/A
		:	Integrated filter designed to meet EN61800-3
Volts: Hertz: 60 Hz Phase: 3 Efficiency: NEMA premium 12.12		•	Dual DC-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**
		Cooling:	Fan-cooled through back channel
MAXIMUM PUMP OPERATING CONDITIONS		Ambient temperature:	-10°c to +45°c up to 1000 meters abov sea level (-14°F to +113°F, 3300 ft)
ANSI 125 175 psig at 150°F (12 bars at 65°C)		Analog ı/o:	Two current or voltage inputs, one current output
100 psig at 300°F (7 bars at 150°C) ANSI 250		Digital ı/o:	Six programmable inputs (two can be configured as outputs)
375 psig at 150°F (26 bars at 65°C)		Pulse inputs:	Two programmable
260 psig at 300°F (21 bars at 150°C)		Relay outputs:	Two programmable
 Tolerance of ±0.125" (±3 mm) should be used For exact installation, data please write factory for certified dimensions 		Communication port:	
MECHANICAL SEAL DESIGN DATA		**The IVS 102 drive is a low harmonic of guaranty performance to any syster a system wide specification. If supp	sure is not known: Default to 40% of design head drive via built-in pc line reactors. This does not m wide harmonic specification or the costs to mee lied with the system electrical details, Armstrong e system wide harmonics. If system harmonic

levels are exceeded Armstrong can also recommend additional harmonic mitigation

and the costs for such mitigation.

2



Performance curves are for reference only.

Confirm current performance data with Armstrong ACE Online selection software.

DIMENSION DATA

INDOOR (UL TYPE 12/ODP)

Frame size: 449

Size: 14×14×15

HP: 300

RPM: 1780

AB: 64.87(1648)

B: 20.50(521)

c: 13.80(351)

D: 27.00(686)

E: 25.05(636)

F: 25.05(636)

P: 22.44(570)

s: 25.00(635)


sp: 52.00(1321)

T: 13.80(351)

XY: 64.83(1647)

Weight: 4597(2085.2)

Dimensions - inch (mm) Weight - lbs (kg)



TORONTO

+1 416 755 2291

BUFFALO

+1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER

+44 (0) 8444 145 145

BANGALORE

+91 (0) 80 4906 3555

SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM



