

# DESIGN ENVELOPE 4300 VIL 2019-450.0 SUBMITTAL

See file no. 43.50 for standard mechanical seal details as

indicated below

□ c1 (a)

Armstrong seal reference number

☐ Others: \_

File No: 100.4254

Date: DECEMBER 17, 2015

Supersedes: 100.4234


Date: AUGUST 14, 2015

Job:		epresentative:	
	C	order No:	Date:
Engineer:		ubmitted by:	Date:
		approved by:	Date:
PUMP DESIGN DATA		: CONTROLS DATA	
No. of pumps:	Tag:	: Sensorless Control:	N/A
Capacity:USgpm (L/s) Liquid:	Head:ft (r	m) Minimum system pressure	ft (m)*
Temperature: °F (°C)			□ L1 (default) □ L2 □ L3 □ L4
Suction: 20" (500 mm)	Discharge: 20" (500 mr		☐ Modbus RTU ☐ BACnet <sup>TM</sup> MS/TP☐ Johnson® N2 ☐ Siemens® FLN
OSHPD Seismic Certification OSP-0422-10 UL STD 778 & CSA STD C22.2 NO.108 certified  MOTOR DESIGN DATA		Protocol (optional):	$\square$ LonWorks $^{\mathbb{R}}$
		Enclosure:	☐ Indoor – UL TYPE 12
		Fused disconnect switch:	N/A
HP: RPM: Frame size: Enclosure:		EMI/RFI control:	Integrated filter designed to meet EN61800-3
Volts: Hertz: 60 Hz Phase: 3 Efficiency: NEMA premium 12.12		Harmonic suppression:	Dual DC-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**
NOTE: Integrated pumping unit not available on 575v supply.		Cooling:	Fan-cooled through back channel
MAXIMUM PUMP OPERATING CONDITIONS		Ambient temperature:	-10°c to +45°c up to 1000 meters abov sea level (-14°F to +113°F, 3300 ft)
<b>ANSI 125</b> 175 psig at 150°F (12 bars at 65°C)		Analog 1/0:	Two current or voltage inputs, one current output
100 psig at 300°F (7 bars at 150°C)		Digital ı/o:	Six programmable inputs (two can be configured as outputs)
<b>ANSI 250</b> 375 psig at 150°F (26 bars at 65°C)		Pulse inputs:	Two programmable
260 psig at 300°F (21 bars at 150°C)		Relay outputs:	Two programmable
<ul> <li>Tolerance of ±0.125" (±3 mm) should be used</li> <li>For exact installation, data please write factory for certified dimensions</li> </ul> MECHANICAL SEAL DESIGN DATA		**The IVS 102 drive is a low harmonic of guaranty performance to any syster	1-RS485, 1-USB  Ture is not known: Default to 40% of design head drive via built-in DC line reactors. This does not in wide harmonic specification or the costs to mee lied with the system electrical details, Armstrong
			e system wide harmonics. If system harmonic

levels are exceeded Armstrong can also recommend additional harmonic mitigation

and the costs for such mitigation.

2



Performance curves are for reference only.

Confirm current performance data with Armstrong ACE Online selection software.

#### **DIMENSION DATA**

### INDOOR (UL TYPE 12/ODP)

Frame size: 500

**Size:** 20×20×19

**HP:** 450

**RPM:** 1180

**AB:** 82.04(2084)

**B:** 31.00(787)

**c:** 20.00(508)

**D:** 48.00(1219)

**E:** 26.11(663)

**P:** 25.00(635)

**F:** 26.11(663)


**s:** 40.00(1016)

**SD:** 88.00(2235)

**T:** 19.90(505)

**xy:** 88.13(2239) **Weight:** 11040(5007.7)

Dimensions - inch (mm) Weight - lbs (kg)



## TORONTO

+1 416 755 2291

#### BUFFALO

+1 716 693 8813

# BIRMINGHAM

+44 (0) 8444 145 145

#### MANCHESTER

+44 (0) 8444 145 145

## BANGALORE

+91 (0) 80 4906 3555

# SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM

