

# DESIGN ENVELOPE 4300 VIL 1415-450.0 SUBMITTAL

See file no. 43.50 for standard mechanical seal details as

indicated below

□ c1 (a)

Armstrong seal reference number

☐ Others: \_

File No: 100.4190

Date: DECEMBER 17, 2015


Supersedes: 100.4196

Date: AUGUST 14, 2015

Job:	Repre	sentative:	
	Order	No:	Date:
Engineer: Subm		itted by:	Date:
Contractor: Appro		oved by:	Date:
		•	
PUMP DESIGN DATA		: CONTROLS DATA	
No. of pumps:		Sensorless Control:	Standard
Capacity:USgpm (L/s) Liquid:		Minimum system pressure to be maintained:	ft (m)*
Temperature: °F (°C)		Orientation:	□ L1 (default) □ L2 □ L3 □ L4
Suction: 14" (350 mm)	Discharge: 14" (350 mm)	Protocol (standard):	☐ Modbus rtu ☐ BACnet <sup>™</sup> MS/TP☐ Johnson® N2 ☐ Siemens® FLN
OSHPD Seismic Certification OSP-0422-10 UL STD 778 & CSA STD C22.2 NO.108 certified		: Protocol (optional):	☐ LonWorks®
		Enclosure:	☐ Indoor - UL TYPE 12
MOTOR DESIGN DATA		: Fused disconnect switch:	N/A
нр: RPM: Frame size: Enclosure:		ЕМІ/RFI control:	Integrated filter designed to meet EN61800-3
Volts: Hertz: 60 Hz Phase: 3  Efficiency: NEMA premium 12.12		Harmonic suppression:	Dual DC-link reactors (Equivalent: 5% Ac line reactor) Supporting IEEE 519-1992 requirements**
NOTE: Integrated pumping unit not available on 575v supply.		: Coolina:	Fan-cooled through back channel
MAXIMUM PUMP OPERATING CONDITIONS		:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)
<b>ANSI 125</b> 175 psig at 150°F (12 bars at 65°C)		Analog ı/o:	Two current or voltage inputs, one current output
100 psig at 300°F (7 bars at 150°C)		Digital ı/o:	Six programmable inputs (two can be configured as outputs)
ANSI 250		: Pulse inputs:	Two programmable
375 psig at 150°F (26 bars at 65°C) 260 psig at 300°F (21 bars at 150°C)		·	Two programmable
200 poig at 300 1 (21 bails at 130 C)		Communication port:	
<ul> <li>Tolerance of ±0.125" (±3 mm) should be used</li> <li>For exact installation, data please write factory for certified dimensions</li> </ul>		*If minimum maintained system pressure is not known: Default to 40% of design head  **The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not quaranty performance to any system wide harmonic specification or the costs to meet	
MECHANICAL SEAL DESIGN DATA		• 3 ,.	ind with the system electrical details. Armstrong

<sup>\*\*</sup>The IVS 102 drive is a low harmonic drive via built-in Dc line reactors. This does not guaranty performance to any system wide harmonic specification or the costs to med a system wide specification. If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation.

2



Performance curves are for reference only.

Confirm current performance data with Armstrong ACE Online selection software.

#### **DIMENSION DATA**

INDOOR (UL TYPE 12/ODP)

Frame size: 500

**Size:** 14×14×15

**HP:** 450

**RPM:** 1780

**AB:** 64.87(1648)

**B:** 20.50(521)

**c:** 13.80(351)

**D:** 27.00(686)

**E:** 25.05(636)

**F:** 25.05(636)

**P:** 22.44(570)

**s:** 25.00(635)


**SD:** 52.00(1321)

**T:** 13.80(351)

**XY:** 64.83(1647)

Weight: 2200(997.9)

Dimensions - inch (mm) Weight - lbs (kg)



## TORONTO

+1 416 755 2291

#### BUFFALO

+1 716 693 8813

# BIRMINGHAM

+44 (0) 8444 145 145

#### MANCHESTER

+44 (0) 8444 145 145

# BANGALORE

+91 (0) 80 4906 3555

### SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM



