

DESIGN ENVELOPE 4300 VIL 1615-125.0 SUBMITTAL

indicated below

□ c1 (a)

Armstrong seal reference number

☐ Others: __


File No: 100.4194 **Date:** DECEMBER 17, 2015 Supersedes: 100.4198 **Date:** AUGUST 14, 2015

Job:	Representative:	
	Order No:	Date:
Engineer:	Submitted by:	Date:
Contractor:	Approved by:	Date:
PUMP DESIGN DATA	CONTROLS DATA	
No. of pumps: Tag:	Sensorless Control: S	Standard
Capacity:USgpm (L/s) Head:ft Liquid: Viscosity:	And the constitution to the	ft (m)*
Temperature: °F (°C) Specific gravity:		□ L1 (default) □ L2 □ L3 □ L4
Suction: 16" (400 mm) Discharge: 16" (400 r	mm) : Protocol (standard): [□ Modbus rtu □ bacnet™ ms/tp □ Johnson® n2 □ Siemens® fln
OSHPD Seismic Certification OSP-0422-10	Protocol (optional):	□ LonWorks®
UL STD 778 & CSA STD C22.2 NO.108 certified	Enclosure:	☐ Indoor – UL TYPE 12
	Fused disconnect switch:	
MOTOR DESIGN DATA HP: RPM: Frame size: Enclosure:		ntegrated filter designed to meet EN61800-3
Volts: Hertz: 60 Hz Phase: 3 Efficiency: NEMA premium 12.12		Dual oc-link reactors (Equivalent: 5% Ac line reactor) Supporting IEEE 519-1992 requirements**
MAXIMUM PUMP OPERATING CONDITIONS	Cooling: F	an-cooled through back channel
ANSI 125		-10°c to +45°c up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)
175 psig at 150°F (12 bars at 65°C) 100 psig at 300°F (7 bars at 150°C)		Two current or voltage inputs, one current output
ANSI 250 375 psig at 150°F (26 bars at 65°C)		Six programmable inputs (two can pe configured as outputs)
260 psig at 300°F (21 bars at 150°C)	Pulse inputs:	Two programmable
• See file no. 43.50 for maximum seal operating condition	Relay outputs:	Two programmable
 Tolerance of ±0.125" (±3 mm) should be used For exact installation, data please write factory for certified dimensions 	Communication port: 1	I-RS485, 1-USB
MECHANICAL SEAL DESIGN DATA See file no. 43.50 for standard mechanical seal details as	**The IVS 102 drive is a low harmonic dri guaranty performance to any system v a system wide specification. If supplie	re is not known: Default to 40% of design head ve via built-in DC line reactors. This does not wide harmonic specification or the costs to meet d with the system electrical details, Armstrong system wide harmonics. If system harmonic

will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation.

Design Envelope 4300 VIL

2




Performance curves are for reference only.

Confirm current performance data with Armstrong ACE Online selection software.

DIMENSION DATA


INDOOD		OUTDOOD
	INDOOR (UL TYPE 12/ODP)	OUTDOOR (UL TYPE 4X/TEFC)
Frame size:	445	445
Size:		16×16×15
Size:		10 10 10
HP:	125	125
RPM:	1200	1200
AB:	58.24(1479)	63.68(1617)
в:	20.27(515)	20.27(515)
c:	15.27(388)	15.27(388)
D:	36.00(914)	36.00(914)
E:	22.91(582)	25.54(649)
P:	23.13(587)	23.25(591)
F:	51.91(1318)	54.54(1385)
s:	29.00(737)	29.00(737)
SD:	65.00(1651)	65.00(1651)
T:	17.63(448)	17.63(448)
XY:	62.44(1586)	67.13(1705)
Weight:	4401(1996.3)	4821(2186.8)


Dimensions - inch (mm) Weight - lbs (kg)



INDOOR







TORONTO +1 416 755 2291

BUFFALO

+1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER

+44 (0) 8444 145 145

BANGALORE

+91 (0) 80 4906 3555

SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM