

DESIGN ENVELOPE 4322 TANGO | 2.5×2.5×5 (65–125) | File No: 102.5021

2505-007.5 | SUBMITTAL

 \square Others: $_$

Supersedes: 102.5021 Date: MAY 04, 2018

Job:		Representative:		
		Order No:	Date:	
Engineer:		Submitted by:	Date:	
		Approved by:	Date:	
PUMP DESIGN DATA		DEPM MOTOR AND CO	ONTROL DATA	
No. of pumps:	Tag:	:	7.5	
Total system design flow:	USgpm(L,		3000	
Head:ft(m)			TEFC	
Flow per pump head:		· Volter		
		Phase:	3	
Parallel flow:		Efficiency.	IE5	
Liquid:		: Offentation.		
Temperature:°F (°C)		:	□ BACnet™ MS/TP □ BACnet™ TCP	
Suction: 2.5" (65 mm)	3	:	☐ Modbus RTU	
UL STD 778 & CSA STD C22.2 N	o.108 certified	Control enclosure:	☐ Indoor - UL Type 12	
Test report is supplied with eac	h pump	Formal discourse at a with the	Outdoor - UL Type 4x	
		Fused disconnect switch:	·	
MATERIALS OF CONSTR	UCTION	: EMI/RFI CONTROI:	Integrated filter designed to meet EN61800-3	
☐ ANSI 125		: Harmonic suppression:	Equivalent: 5% Ac line reactor - Sup-	
CONSTRUCTION: LPDESF		: Harmonic suppression.	porting IEEE 519-1992 requirements*	
	6 Gr 65-45-12, stainless fitte	ed : Cooling:	Fan-cooled, surface cooling	
☐ ANSI 250		•	-10°C to +45°C up to 1000 meters abov	
CONSTRUCTION: HPDESF	6 Gr 120 - 90 - 2, stainless fitt		sea level (+14°F to +113°F, 3300 ft)	
L-coated ductile from A530) G1 120-90-2, Stailliess litt	Analog ı/o:	Two inputs, one output. Output can	
MAXIMUM PUMP OPERA	ATING CONDITIONS		be configured for voltage or current	
	ATTING CONDITIONS	Digital ı/o:	Two inputs, two outputs. Outputs ca	
☐ ANSI 125 175 psig at 150°F (12 bar at	65°C)	<u>.</u>	be configured as inputs	
1/5 psig at 150 F (12 bar at 150°C) 100 psig at 300°F (7 bar at 150°C)			Two programmable	
☐ ANSI 250		Communication port:	1-RS485	
375 psig at 150°F (26 bar at 65°C) 260 psig at 300°F (21 bar at 150°C)		simulation of the system wide ha	** If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation.	
MECHANICAL SEAL DES	IGN DATA	•		
See file no. 43.50 for standard mechanical seal details as		FLOW READOUT ACCU	RACY	
indicated below		•	The Design Envelope model selected will provide flow reading	
Armstrong seal reference number		on the controls local keypa	d & digitally for the вмs. The model	

readout will be factory tested to ensure ±5% accuracy.

2

OPTIONS

SENSORLESS BUNDLE (STANDARD)



Operation of pump without a remote sensor. Includes:

- Sensorless control
- Flow readout
- Constant flow
- Constant pressure

Minimum system pressure to be maintained ft (m)

 If minimum maintained system pressure is not known: Default to 40% of design head

☐ PARALLEL SENSORLESS



Operation of multiple pumps without a remote sensor

 $\label{eq:minimum} \mbox{Minimum system pressure to be maintained} \\ \mbox{ft (m)}$

* If minimum maintained system pressure is not known: Default to 40% of design head

☐ ENERGY PERFORMANCE BUNDLE



Provides energy savings on oversized systems by adjusting pump parameters to on-site conditions. Includes:

- Auto-flow balancing Automatically determines control curve between design flow at on-site system head, and minimum (zerohead) flow for energy savings
- Maximum flow control Limits flow rate to pre-set maximum for potential energy savings

Maximum flow rate gpm (L/s)

PROTECTION BUNDLE



Protects other flow sensitive equipment by setting limits of pump operation. Includes:

- Minimum flow control Attempts to maintain flow rate to pre-set minimum to protect equipment in system
- Bypass valve control Actuates a bypass valve to protect flow sensitive equipment if pre-set minimum flow rate is reached

Minimum flow rate gpm (L/s)

□ DUAL SEASON SETUP



Pre-sets heating and cooling parameters for pumps in 2-pipe systems

Coolina

Cooling		
Duty point	gpm (L/s) at	ft (m)
Minimum system	m pressure to be maint	ained
	ft (m)	
Heating		
Duty point	gpm (L/s) at	ft (m)
Minimum system	m pressure to be maint	ained
	ft (m)	

OPTIONAL SERVICES

ON-SITE PUMP COMMISSIONING



PUMP MANAGER



Online service for sustained pump performance and enhanced reliability.

Available in 3 or 5 year terms

- * Requires an internet connection to be provided by building
- * Includes an extended warranty for parts and labour (wearable parts excluded)


^{*}Only available if sensorless bundle is enabled

^{*}Available in single pump operation only

 $^{^\}star Only$ available if sensorless bundle is enabled

^{*}Available in single pump operation only


3




Performance curves are for reference only.

Confirm current performance data with Armstrong ADEPT Quote or ADEPT Select selection software.

INDOOR







DIMENSION DATA

	INDOOR	OUTDOOR	
	(UL TYPE 12/TEFC)	(UL TYPE 4X/TEFC)	
Size:	2.5×2.5×5	2.5×2.5×5	
HP:	7.5	7.5	
RPM:	3000	3000	
AB:	20.37 (517)	22.58 (573)	
B1:	5.50 (140)	5.50 (140)	
B2:	5.50 (140)	5.50 (140)	
C1:	9.50 (241)	9.50 (241)	
C2:	9.50 (241)	9.50 (241)	
CI:	-	5.00 (127)	
D:	6.15 (156)	6.15 (156)	
E:	8.18 (208)	8.60 (218)	
s:	7.24 (184)	7.24 (184)	
SD:	13.39 (340)	13.39 (340)	
T:	5.12 (130)	5.12 (130)	
Weight:	205 (93.0)	205 (93.0)	

Dimensions - inch (mm) Weight - lbs (kg)

- Tolerance of ± 0.125 " (± 3 mm) should be used
- For exact installation, data please write factory for certified dimensions

TORONTO

23 BERTRAND AVENUE TORONTO, ONTARIO CANADA, M1L 2P3 +1 416 755 2291

BUFFALO

93 EAST AVENUE NORTH TONAWANDA, NEW YORK U.S.A., 14120-6594 +1 716 693 8813

DROITWICH SPA

POINTON WAY, STONEBRIDGE CROSS BUSINESS PARK DROITWICH SPA, WORCESTERSHIRE UNITED KINGDOM, WR9 OLW +44 8444 145 145

MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM, M11 2ET
+44 8444 145 145

BANGALORE

#59, FIRST FLOOR, 3RD MAIN MARGOSA ROAD, MALLESWARAM BANGALORE, INDIA, 560 003 +91 80 4906 3555

SHANGHAI

unit 903, 888 north sichuan rd. Hongkou district, shanghai China, 200085 +86 21 5237 0909

SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES SAO PAULO, BRAZIL +55 11 4785 1330

LYON

93 RUE DE LA VILLETTE LYON, 69003 FRANCE +33 4 26 83 78 74

DUBAI

JAFZA VIEW 19, OFFICE 402 P.O.BOX 18226 JAFZA, DUBAI - UNITED ARAB EMIRATES +971 4 887 6775

MANNHEIM

DYNAMOSTRASSE 13 68165 MANNHEIM GERMANY +49 621 3999 9858

JIMBOLIA

STR CALEA MOTILOR NR. 2C JIMBOLIA 305400, JUD.TIMIS ROMANIA +40 256 360 030

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934