

DESIGN ENVELOPE EXPRESS PUMP 4300 |

0408-007.5 | SUBMITTAL

File No: 100.3040

Date: DECEMBER 24, 2015

Supersedes: 100.3040

Date: SEPTEMBER 22, 2015

| Job: | Re | epresentative: | |
|---|-----------------------|-----------------------|--|
| | 0 | rder No: | Date: |
| Engineer: | | ıbmitted by: | Date: |
| Contractor: | A | pproved by: | Date: |
| PUMP DESIGN DATA | | CONTROLS DATA | ∕ ⇒EXPRESS |
| No. of pumps: | Tag: | Sensorless Control: | Standard TV LANE |
| Capacity:USgpm (L/s) Liquid: | | : | ft (m)* |
| Temperature: °F (°C) | Specific gravity: | Orientation: | L1 |
| Suction: 4" (100mm) | Discharge: 4" (100mm) | Protocol: | BACnet TM |
| OSHPD Seismic Certification OSP-0422-10 | | Enclosure: | Indoor - UL TYPE 12 |
| UL STD 778 & CSA STD C22.2 NO.108 certified | | емі/RFI control: | Integrated filter designed to meet EN61800-3 |
| MOTOR DESIGN DATA HP: 7.5 RPM: 1800 Frame size: 213 Enclosure: TEFC | | Harmonic suppression: | Dual pc-link reactors (Equivalent: 5% Ac line reactor) Supporting IEEE 519-1992 requirements** |
| Volts: □ 230V □ 460V □ 575V Hertz: 60 Hz | | Cooling | Fan-cooled through back channel |
| Phase: 3 Efficiency: NEMA premium 12.12 | | Ambient temperature: | -10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft) |
| MAXIMUM PUMP OPERATING CONDITIONS ANSI 125 175 psig at 150°F (12 bars at 65°C) 100 psig at 300°F (7 bars at 150°C) | | Analog ı/o: | Two current or voltage inputs, one current output |
| | | Digital ı/o: | Six programmable inputs (two can be configured as outputs) |
| | | Pulse inputs: | Two programmable |
| ANSI 250 | | Relay outputs: | Two programmable |
| 375 psig at 150°F (26 bars at 65°C) 260 psig at 300°F (21 bars at 150°C) | | Communication port: | 1-RS485, 1-USB |
| | | * *16 | i |

*The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not guaranty performance to any system wide harmonic specification or the costs to meet a system wide specification. If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation.

certified dimensions

• Tolerance of ±0.125" (±3 mm) should be used


• For exact installation, data please write factory for

See file no. 43.50 for standard mechanical seal details as indicated below

Armstrong seal reference number: c1 (a)


MECHANICAL SEAL DESIGN DATA

2



Performance curves are for reference only.

 $\label{thm:confirm} \mbox{Confirm current performance data with Armstrong \ \mbox{ACE Online selection software}. }$



TORONTO

+1 416 755 2291

BUFFALO

+1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER

+44 (0) 8444 145 145

BANGALORE

+91 (0) 80 4906 3555

SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

DIMENSION DATA

| | INDOOR | |
|-------------|-------------------|--|
| | (UL TYPE 12/TEFC) | |
| Frame size: | 213 | |
| Size: | 4×4×8 | |
| HP: | 7.5 | |
| RPM: | 1800 | |
| AB: | 31.89(810) | |
| В: | 8.00(203) | |
| c: | 6.31(160) | |
| D: | 11.00(279) | |
| E: | 14.73(374) | |
| P: | 12.13(308) | |
| F: | 28.73(730) | |
| s: | 14.00(356) | |
| SD: | 25.00(635) | |
| T: | 8.00(203) | |
| XY: | 28.19(716) | |
| Weight: | 376(170.6) | |
| | | |

Dimensions - inch (mm) Weight - lbs (kg)

