

# **DESIGN ENVELOPE EXPRESS PUMP** 4300 |

0813-060.0 | SUBMITTAL

File No: 100.3060

Date: DECEMBER 24, 2015

Supersedes: 100.3060

Date: SEPTEMBER 22, 2015

Job:	F	lepresentative:	
	(	Order No:	Date:
Engineer: Su		ubmitted by:	Date:
Contractor: App		approved by:	Date:
PUMP DESIGN DATA		CONTROLS DATA	<b>∕</b> ⇒EXPRESS
No. of pumps:	Tag:	Sensorless Control:	►V LANE
Capacity:USgpm (L/s) Liquid:		· · · · · · · · · · · · · · · · · · ·	ft (m)*
Temperature: °F (°C)	Specific gravity:	Orientation:	L1
Suction: 8" (200mm)	Discharge: 8" (200mm	) Protocol:	BACnet <sup>TM</sup>
OSHPD Seismic Certification OSP-0422-10		Enclosure	Indoor – UL TYPE 12
UL STD 778 & CSA STD C22.2 NO.108 certified		EMI/RFI control:	Integrated filter designed to meet EN61800-3
MOTOR DESIGN DATA		Harmonic suppression:	Dual DC-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**
HP: 60 RPM: 1800 Frame size: 364 Enclosure: ODP		Cooling	Fan-cooled through back channel
Volts: ☐ 460V ☐ 575V Hertz: 60 Hz		:	-
Phase: 3 Efficiency: NEMA premium 12.12		Ambient temperature	: -10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)
MAXIMUM PUMP OPERATING CONDITIONS		Analog ı/o:	Two current or voltage inputs, one current output
<b>ANSI 125</b> 175 psig at 150°F (12 bars at 65°C)		Digital ı/o:	Six programmable inputs (two can be configured as outputs)
100 psig at 300°F (7 bars at 150°C)		Pulse inputs:	: Two programmable
ANSI 250		Relay outputs:	: Two programmable
375 psig at 150°F (26 bars at 65°C)		Communication port	1-RS485, 1-USB
260 psig at 300°F (21 bars at 150°C)			

\*If minimum maintained system pressure is not known: Default to 40% of design head

\*\*The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not
guaranty performance to any system wide harmonic specification or the costs to meet
a system wide specification. If supplied with the system electrical details, Armstrong
will run a computer simulation of the system wide harmonics. If system harmonic
levels are exceeded Armstrong can also recommend additional harmonic mitigation
and the costs for such mitigation.

# MECHANICAL SEAL DESIGN DATA

certified dimensions


• Tolerance of ±0.125" (±3 mm) should be used

• For exact installation, data please write factory for

See file no. 43.50 for standard mechanical seal details as indicated below


Armstrong seal reference number: c1 (a)

2



Performance curves are for reference only.

Confirm current performance data with Armstrong ACE Online selection software.



# TORONTO

+1 416 755 2291

#### BUFFALO

+1 716 693 8813

## BIRMINGHAM

+44 (0) 8444 145 145

#### MANCHESTER

+44 (0) 8444 145 145

## BANGALORE

+91 (0) 80 4906 3555

### SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

#### **DIMENSION DATA**

INDOOR
(UL TYPE 12/ODP)

Frame size: 364

**Size:** 8×8×13

**HP:** 60

**RPM:** 1800

**AB:** 47.90(1217)

**B:** 12.00(305)

**c:** 9.75(248)

**D:** 19.00(483)

**E:** 21.41(544)

**P:** 17.63(448)

**F:** 44.41(1128)

**s:** 23.00(584)

**sp:** 42.00(1067)

**T:** 9.94(252)

**XY:** 41.41(1052)

Weight: 1609(729.8)

Dimensions - inch (mm) Weight - lbs (kg)

