

# **DESIGN ENVELOPE EXPRESS PUMP** 4300 |

0813-075.0 | SUBMITTAL

File No: 100.3062

Date: DECEMBER 24, 2015

Supersedes: 100.3062

Date: SEPTEMBER 22, 2015

Job:	R	epresentative:	
	C	rder No:	Date:
Engineer: 9		ubmitted by:	Date:
Contractor:	А	pproved by:	Date:
PUMP DESIGN DATA		CONTROLS DATA	<b>/⇒</b> EXPRESS
No. of pumps:	Tag:	Sensorless Control:	✓ LANE
Capacity:USgpm (L/s) Liquid:		:	ft (m)*
Temperature: °F (°C)	Specific gravity:	Orientation:	L1
Suction: 8" (200mm)	Discharge: 8" (200mm	) Protocol:	BACnet <sup>TM</sup>
OSHPD Seismic Certification OSP-C	0422-10	Enclosure:	Indoor - UL TYPE 12
UL STD 778 & CSA STD C22.2 NO.108 certified		емі/RFI control:	Integrated filter designed to meet EN61800-3
MOTOR DESIGN DATA  HP: 75 RPM: 1800 Frame size: 365 Enclosure: ODP		Harmonic suppression:	Dual pc-link reactors (Equivalent: 5% Ac line reactor) Supporting IEEE 519-1992 requirements**
Volts: ☐ 460V ☐ 575V Hertz: 60 Hz		Cooling:	Fan-cooled through back channel
Phase: 3 Efficiency: NEMA premium 12.12		Ambient temperature:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)
MAXIMUM PUMP OPERATING CONDITIONS		Analog ı/o:	Two current or voltage inputs, one current output
<b>ANSI 125</b> 175 psig at 150°F (12 bars at 65°C)		Digital ı/o:	Six programmable inputs (two can be configured as outputs)
100 psig at 300°F (7 bars at 150°C)		Pulse inputs:	Two programmable
ANSI 250		Relay outputs:	Two programmable
375 psig at 150°F (26 bars at 65°C) 260 psig at 300°F (21 bars at 150°C)		Communication port:	1-RS485, 1-USB

\*If minimum maintained system pressure is not known: Default to 40% of design head

\*\*The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not
guaranty performance to any system wide harmonic specification or the costs to meet
a system wide specification. If supplied with the system electrical details, Armstrong
will run a computer simulation of the system wide harmonics. If system harmonic
levels are exceeded Armstrong can also recommend additional harmonic mitigation
and the costs for such mitigation.

# MECHANICAL SEAL DESIGN DATA

certified dimensions


• Tolerance of ±0.125" (±3 mm) should be used

• For exact installation, data please write factory for

See file no. 43.50 for standard mechanical seal details as indicated below


Armstrong seal reference number: c1 (a)

2



Performance curves are for reference only.

Confirm current performance data with Armstrong ACE Online selection software.



# TORONTO

+1 416 755 2291

#### BUFFALO

+1 716 693 8813

## BIRMINGHAM

+44 (0) 8444 145 145

#### MANCHESTER

+44 (0) 8444 145 145

## BANGALORE

+91 (0) 80 4906 3555

## SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

#### **DIMENSION DATA**

	INDOOR (UL TYPE 12/ODP)	
Frame size:	365	
Size:	8×8×13	
HP:	75	
RPM:	1800	
AB:	43.72(1111)	
в:	12.00(305)	
c:	9.75(248)	
D:	19.00(483)	
E:	19.90(505)	
P:	17.63(448)	
F:	42.90(1090)	
s:	23.00(584)	
SD:	42.00(1067)	
T:	9.94(252)	

**XY:** 41.41(1052)

Weight: 1419(643.6)

Dimensions - inch (mm) Weight - lbs (kg)

