

# DESIGN ENVELOPE 4302 DUALARM | 0810-100.0 |

SUBMITTAL

☐ c1 (a)

☐ Others: \_\_

File No: 100.4500

Date: OCTOBER 30, 2015


Supersedes: NEW

Job:	Repres	sentative:	
	Order	No:	Date:
Engineer:	Submi	tted by:	Date:
Contractor:	Appro	ved by:	Date:
PUMP DESIGN DATA		: CONTROLS DATA	
No. of pumps: Tag: _		: Sensorless Control:	Standard
Capacity:USgpm (L/s) Head: Liquid:Visco	ft (m)	Minimum system pressure to be maintained:	ft (m)*
Temperature:°F (°C) Specif		Protocol (standard):	☐ Modbus RTU ☐ BACnet™ MS/TP
	arge: 8" (200mm)	Protocol (optional):	☐ Johnson® N2 ☐ Siemens® FLN ☐ LonWorks®
OSHPD Seismic Certification OSP-0422-10		•	☐ Indoor - UL TYPE 12
UL STD 778 & CSA STD C22.2 NO.108 certified		Eliciosure.	Outdoor - UL TYPE 4x with Weather Shield
MOTOR DESIGN DATA			Outdoor - UL TYPE 4x less Weather Shield
HP: RPM: Frame size:	_ Enclosure:	Fused disconnect switch:	
Volts: Hertz: 60 Hz	Phase: 3	Duty/standby pre-wired bridge:	
Efficiency: NEMA premium 12.12		емі/RFI control:	Integrated filter designed to meet EN61800-3
MAXIMUM PUMP OPERATING CONDITIONS ANSI 125		Harmonic suppression:	Dual pc-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**
175 psig at 150°F (12 bars at 65°C)		Cooling:	Fan-cooled through back channel
140 psig at 250°F (10 bars at 121°C)  ANSI 250		Ambient temperature:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)
250 psig at 150°F (17 bars at 65°C) 250 psig at 250°F (17 bars at 121°C)		Analog ı/o:	Two current or voltage inputs, one current output
<ul> <li>Tolerance of ±0.125" (±3 mm) should be used</li> <li>For exact installation, data please write factory for certified dimensions</li> </ul>		Digital ı/o:	Six programmable inputs (two can be configured as outputs)
		Pulse inputs:	Two programmable
certified differsions		Relay outputs:	Two programmable
MECHANICAL SEAL DESIGN DATA		Communication port:	1-RS485, 1-USB
See file no. 43.50 for standard mechanical seal details as indicated below  Armstrong seal reference number		*If minimum maintained system pressure is not known: Default to 40% of design head  **The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not guaranty performance to any system wide harmonic specification or the costs to meet a system wide specification. If supplied with the system electrical details, Armstrong	

will run a computer simulation of the system wide harmonics. If system harmonic

and the costs for such mitigation.

levels are exceeded Armstrong can also recommend additional harmonic mitigation



900

FLOW

1000

70

1250

80

Performance curves are for reference only.  $Confirm\ current\ performance\ data\ with\ Armstrong\ ACE\ Online\ selection\ software.$ 

40

700

45

800

50

ARMSTRONG FLUID TECHNOLOGY

ESTABLISHED 1934

600

#### **DIMENSION DATA**

	INDOOR (UL TYPE 12/ODP)	OUTDOOR (UL TYPE 4X/TEFC)
	(OL TIPE 12/ODF)	(01 1176 4x/1670)
Frame size:	404	404
Size:	8×8×10	8×8×10
HP:	100	100
RPM:	1800	1800
AB:	47.88(1216)	47.88(1216)
B1:	12.00(305)	12.00(305)
B2:	11.50(292)	11.50(292)
C1:	20.56(522)	20.56(522)
C2:	21.00(533)	21.00(533)
D1:	21.00(533)	21.00(533)
D2:	25.00(635)	25.00(635)
E:	17.69(449)	17.69(449)
F:	24.77(629)	24.77(629)
P:	19.10(485)	19.10(485)
SD:	46.00(1168)	46.00(1168)
T:	8.86(225)	8.86(225)
XY:	46.57(1183)	46.57(1183)
Weight:	3166(1436.1)	3324(1507.9)

OUTDOOR

WEATHER

SHIELD

Dimensions - inch (mm) Weight - lbs (kg)

# TORONTO

+1 416 755 2291

100 -

35

30

#### BUFFALO

+1 716 693 8813

## BIRMINGHAM

+44 (0) 8444 145 145

#### MANCHESTER


+44 (0) 8444 145 145

### BANGALORE

+91 (0) 80 4906 3555

# SHANGHAI


+86 21 3756 6696



INDOOR

USGPM

1500 L/S



ARMSTRONGFLUIDTECHNOLOGY.COM