

# DESIGN ENVELOPE 4302 DUALARM | 0811-030.0 | SUBMITTAL

Date: OCTOBER 30, 2015 Supersedes: 100.4520 Date: AUGUST 14, 2015

File No: 100.4514

Job:		Represen	tative:			
		Order No	C	Dat	te:	
Engineer:		Submitted by:		Dat	te:	
Contractor: Appro		Approved			_ Date:	
PUMP DESIGN DATA		:	CONTROLS DATA			
No. of pumps:	Tag:	:	Sensorless Control:	Standard		
Capacity:USgpm (L/s)	Head:ft	t (m)	Minimum system pressure to be maintained:		ft (m)*	
Liquid:°F (°C)			Protocol (standard):	☐ Modbus RTU		
Suction: 8" (200mm) Discharge: 8" (200mm)  OSHPD Seismic Certification OSP-0422-10			Protocol (optional):			
UL STD 778 & CSA STD C22.2 NO.108 certified  MOTOR DESIGN DATA			Enclosure:	□ Indoor – UL TYPE 12 □ Outdoor – UL TYPE 4X with Weather Shield □ Outdoor – UL TYPE 4X less Weather Shield		
нр:	Enclosure:	:	Fused disconnect switch:			
Volts: Hertz: 60 Hz			Duty/standby			
Efficiency: NEMA premium 12.12			pre-wired bridge:			
			EMI/RFI control: Integrated filter designed to meet EN61800-3			
MAXIMUM PUMP OPERATING CONDITIONS  ANSI 125			Harmonic suppression:	Dual DC-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**		
175 psig at 150°F (12 bars at 65°C)			Cooling:	: Fan-cooled through back channel		
140 psig at 250°F (10 bars at 121°C)			Ambient temperature:			
ANSI 250		:			o +113°F, 3300 ft)	
250 psig at 150°F (17 bars at 65°C) 250 psig at 250°F (17 bars at 121°C)			Analog ı/o:	Two current or vone current outp	5 1 /	
<ul> <li>Tolerance of ±0.125" (±3 mm) should be used</li> <li>For exact installation, data please write factory for certified dimensions</li> </ul>			Digital ı/o:	Six programmab be configured as	lle inputs (two can outputs)	
			Pulse inputs:	Two programma	ble	
			Relay outputs:	Two programma	ble	
MECHANICAL SEAL DESIGN DATA			Communication port:	1-RS485, 1-USB		
See file no. 43.50 for standard mechanical seal details as indicated below			*If minimum maintained system pressure is not known: Default to 40% of design head  **The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not guaranty performance to any system wide harmonic specification or the costs to meet			
Armstrong seal reference number			a system wide specification. If supplied with the system electrical details. Armstrong			

☐ Others: \_\_\_\_\_


□ c1 (a)

#### **CONTROLS DATA**

Sensorless Control:	Standard		
Minimum system pressure to be maintained:	ft (m)*		
Protocol (standard):	☐ Modbus RTU ☐ BACnet™ MS/TF☐ Johnson® N2 ☐ Siemens® FLN		
Protocol (optional):	$\square$ LonWorks $^{\circledR}$		
Enclosure:	☐ Indoor - UL TYPE 12 ☐ Outdoor - UL TYPE 4X with Weather Shield ☐ Outdoor - UL TYPE 4X less Weather Shield		
Fused disconnect switch:			
Duty/standby pre-wired bridge:			
EMI/RFI control:	Integrated filter designed to meet EN61800-3		
Harmonic suppression:	Dual pc-link reactors (Equivalent: 5 Ac line reactor) Supporting IEEE 519-1992 requirements**		

 $<sup>^{\</sup>star\star}\text{The ivs}$  102 drive is a low harmonic drive via built-in DC line reactors. This does not guaranty performance to any system wide harmonic specification or the costs to meet a system wide specification. If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation.

2



Performance curves are for reference only.

 $\label{lem:confirm} \text{Confirm current performance data with Armstrong ACE Online selection software.}$ 

ARMSTRONG FLUID TECHNOLOGY

ESTABLISHED 1934

#### **DIMENSION DATA**

	INDOOR (UL TYPE 12/ODP)	OUTDOOR (UL TYPE 4X/TEFC)
Frame size:	286	286
Size:	8×8×11.5	8×8×11.5
HP:	30	30
RPM:	1800	1800
AB:	42.56(1081)	47.96(1218)
B1:	11.00(279)	11.00(279)
B2:	10.50(267)	10.50(267)
C1:	20.20(513)	20.20(513)
C2:	20.10(511)	20.10(511)
D1:	20.65(524)	20.65(524)
D2:	25.48(647)	25.48(647)
E:	11.75(298)	12.00(305)
P:	13.38(340)	15.31(389)
F:	20.69(526)	24.68(627)
SD:	46.94(1192)	46.94(1192)
T:	8.80(224)	8.80(224)
XY:	37.41(950)	43.54(1106)
Weight:	2030(920.8)	2220(1007.0)

OUTDOOR

Dimensions - inch (mm) Weight - lbs (kg)

## TORONTO

+1 416 755 2291

#### BUFFALO

+1 716 693 8813

### BIRMINGHAM

+44 (0) 8444 145 145

#### MANCHESTER


+44 (0) 8444 145 145


### BANGALORE


+91 (0) 80 4906 3555

## SHANGHAI

+86 21 3756 6696







 ${\tt ARMSTRONGFLUIDTECHNOLOGY.COM}$