

DESIGN ENVELOPE 4302 DUALARM

0608-060.0 | SUBMITTAL

File No: 104.5039

Date: DECEMBER 16, 2020

Supersedes: 104.5039

Date: JULY 8, 2019

Job:		Representative:		
		0	rder No:	Date:
Engineer:		Sı	ubmitted by:	Date:
Contractor: Appr			pproved by:	Date:
PUMP DESIG	IN DATA		CONTROL	S DATA
No. of pumps:_		Tag:	_ :	Protocol (standard): ☐ BACnet™ MS/TP
		USgpm(L/s	:	☐ BACnet™ TCP/IP
	_	Capacity split	:	☐ Modbus RTU
		USgpm(L/s	•	Enclosure: Indoor - UL TYPE 12
		USgpm(L/s	•	☐ Outdoor – UL TYPE 4X with
			•	Weather Shield
		Viscosity:	:	☐ Outdoor - UL TYPE 4X less Weather Shield
		Specific gravity:		d disconnect switch:
Suction: 6 (150	omm)	Discharge: 6" (150mm)		EMI/RFI control: Integrated filter designed to
оѕнро Seismic		-		meet EN61800-3
UL STD 778 & CS			Ha	rmonic suppression: Dual DC-link reactors
Test report is su	applied with eac	ch pump		(Equivalent: 5% Ac line reactor
MOTOR DESI	IGN DATA			Supporting IEEE 519-1992 requirements**
		Frame size: Hertz: 60 Hz	_	Cooling: Fan-cooled through back channel
		: NEMA premium 12.12	Aı	nbient temperature: -10°C to +45°C up to 1000 meter above sea level (+14°F to +113°l 3300 ft)
MAXIMUM P	UMP OPERA	TING CONDITIONS	:	Analog I/o: Two current or voltage inputs,
ANSI 125 - (CC	ONSTRUCTION	I: BF)	:	one speed output
175 psig at 150°F	F (12 bar at 65°C)	:	Digital I/o: Two inputs, two outputs
140 psig at 250°	_		:	Pulse inputs: Two programmable
, , ,				Relay outputs: Two programmable
			:	Communication port: 1-RS485
MECHANICA See file no. 43.5 indicated below Armstrong seal	50 for standard	mechanical seal details as	guaranty perfo meet a system Armstrong wil system harmo	s a low harmonic drive via built-in pc line reactors. This does not be browned by the costs to wide specification. If supplied with the system electrical details, I run a computer simulation of the system wide harmonics. If nic levels are exceeded Armstrong can also recommend additional gation and the costs for such mitigation.
□ c1 (a) □	Others:		: FLOW DE	ADOUT ACCURACY
		·	FLOW RE	ADOUT ACCURACT

The Design Envelope model selected will provide flow reading on the controls local keypad & digitally for the BMs. The model readout will be factory tested to ensure $\pm 5\%$ accuracy.

2

OPTIONS

SENSORLESS BUNDLE (STANDARD)



Operation of pump without a remote sensor. Includes:

- Sensorless control
- Flow readout
- Constant flow
- Constant pressure

Minimum system pressure to be maintained ft (m)

* If minimum maintained system pressure is not known: Default to 40% of design head

□ PARALLEL SENSORLESS



Operation of multiple pumps without a remote sensor

Minimum system pressure to be maintained ft (m)

* If minimum maintained system pressure is not known: Default to 40% of design head

☐ ENERGY PERFORMANCE BUNDLE



Provides energy savings on oversized systems by adjusting pump parameters to on-site conditions. Includes:

- Auto-flow balancing Automatically determines control curve between design flow at on-site system head, and minimum (zerohead) flow for energy savings
- Maximum flow control Limits flow rate to pre-set maximum for potential energy savings

Maximum flow rate gpm (L/s)

□ PROTECTION BUNDLE



Protects other flow sensitive equipment by setting limits of pump operation. Includes:

• Minimum flow control - Attempts to maintain flow rate to pre-set minimum to protect

equipment in system

 Bypass valve control - Actuates a bypass valve to protect flow sensitive equipment if pre-set minimum flow rate is reached

Minimum flow rate gpm (L/s)

☐ DUAL SEASON SETUP



Pre-sets heating and cooling parameters for pumps in 2-pipe systems

Cooling

Duty point	gpm (L/s) at _	ft (m)					
Minimum system pressure to be maintained ft (m)							
Heating							
Duty point	gpm (L/s) at	ft (m)					
Minimum system pressure to be maintained ft (m)							

OPTIONAL SERVICES

ON-SITE PUMP COMMISSIONING



PUMP MANAGER



Online service for sustained pump performance and enhanced reliability.

Available in 3 or 5 year terms

- * Requires an internet connection to be provided by building
- * Includes an extended warranty for parts and labour (wearable parts excluded)


^{*}Only available if sensorless bundle is enabled

^{*}Available in single pump operation only

^{*}Only available if sensorless bundle is enabled

^{*}Available in single pump operation only

3



Performance curves are for reference only.

Confirm current performance data with Armstrong ACE Online selection software.

DIMENSION DATA

	INDOOR	OUTDOOR
	(UL TYPE 12/ODP)	(UL TYPE 4X/TEFC)
Frame size:	364	364
Size:	6×6×8	6×6×8
HP:	60	60
RPM:	1500	1500
AB:	47.44(1205)	47.44(1205)
B1:	9.75(248)	9.75(248)
B2:	9.75(248)	9.75(248)
C1:	16.90(429)	16.90(429)
C2:	17.63(448)	17.63(448)
D1:	16.81(427)	16.81(427)
D2:	16.81(427)	16.81(427)
E:	16.44(418)	16.44(418)
F:	23.68(601)	23.68(601)
P:	19.03(483)	19.03(483)
SD:	33.94(862)	33.94(862)
T:	7.88(200)	7.88(200)
XY:	42.76(1086)	42.76(1086)
Weight:	1311(594.7)	1377(624.4)

Dimensions - inch (mm) Weight - lbs (kg)

- Tolerance of ±0.125" (±3 mm) should be used
- For exact installation, data please write factory for certified dimensions

TORONTO

23 BERTRAND AVENUE TORONTO, ONTARIO CANADA, M1L 2P3 +1 416 755 2291

BUFFALO

93 EAST AVENUE NORTH TONAWANDA, NEW YORK U.S.A., 14120-6594 +1 716 693 8813

BIRMINGHAM

HEYWOOD WHARF, MUCKLOW HILL HALESOWEN, WEST MIDLANDS UNITED KINGDOM, B62 8DJ +44 8444 145 145

MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM, M11 2ET
+44 8444 145 145

BANGALORE

#59, FIRST FLOOR, 3RD MAIN MARGOSA ROAD, MALLESWARAM BANGALORE, INDIA, 560 003 +91 80 4906 3555

SHANGHAI

unit 903, 888 north sichuan rd. Hongkou district, shanghai China, 200085 +86 21 5237 0909

SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES SAO PAULO, BRAZIL +55 11 4785 1330

LYON

93 RUE DE LA VILLETTE LYON, 69003 FRANCE +33 4 26 83 78 74

DUBAI

JAFZA VIEW 19, OFFICE 402 P.O.BOX 18226 JAFZA, DUBAI - UNITED ARAB EMIRATES +971 4 887 6775

MANNHEIM

DYNAMOSTRASSE 13 68165 MANNHEIM GERMANY +49 621 3999 9858

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934