

DESIGN ENVELOPE 4312 TWIN | 0306-007.5 | SUBMITTAL

File No: 100.4722

Date: JANUARY 14, 2016

Supersedes: 100.4722

Date: AUGUST 14, 2015


Job:		Representative:	
		Order No:	Date:
Engineer: Su Contractor: Ap		Submitted by:	Date:
		Approved by:	Date:
PUMP DESIGN DATA		CONTROLS DATA	
No. of pumps:	Гад:	: Sensorless Control:	Standard
Capacity:USgpm (L/s) H	Head:ft (m) Minimum system pressure	ft (m)*
Temperature:°F (°C)	Specific gravity:	5 (1/) 1 ()	☐ Modbus RTU ☐ BACnet [™] MS/TP☐ Johnson® N2 ☐ Siemens® FLN
Suction: 3" (75mm) [Protocol (optional):	□ LonWorks®
OSHPD Seismic Certification OSP-0422-10 UL STD 778 & CSA STD C22.2 NO.108 certified		Enclosure:	☐ Indoor – UL TYPE 12 ☐ Outdoor – UL TYPE 4X with
MOTOR DESIGN DATA		Fused disconnect switch:	Weather Shield ☐ Outdoor - UL TYPE 4X less Weather Shield
HP: RPM: Frame size	e: Enclosure:		
Volts: Hertz: 60	Hz Phase: 3	pre-wired bridge:	
Efficiency: NEMA premium 12.12		ЕМІ/RFI control:	Integrated filter designed to meet EN61800-3
MAXIMUM PUMP OPERAT	ING CONDITIONS	Harmonic suppression:	Dual pc-link reactors (Equivalent: 5% Ac line reactor) Supporting IEEE 519-1992 requirements**
ANSI 125		Cooling:	Fan-cooled through back channel
175 psig at 150°F (12 bars at 65°C) 140 psig at 250°F (10 bars at 121°C)		Ambient temperature:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)
 Tolerance of ±0.125" (±3 mm) should be used For exact installation, data please write factory for certified dimensions 		Analog ı/o:	Two current or voltage inputs, one current output
		Digital ı/o:	Six programmable inputs (two can be configured as outputs)
		Pulse inputs:	Two programmable
		Relay outputs:	Two programmable
MECHANICAL SEAL DESIGN DATA		Communication port:	1-RS485, 1-USB
See file no. 43.50 for standard mechanical seal details as indicated below		•	sure is not known: Default to 40% of design head drive via built-in ɒc line reactors. This does not
Armstrong seal reference number			m wide harmonic specification or the costs to meet

☐ c1 (a)

☐ Others: _

If minimum maintained system pressure is not known: Default to 40% of design head
*The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not
guaranty performance to any system wide harmonic specification or the costs to meet
a system wide specification. If supplied with the system electrical details, Armstrong
will run a computer simulation of the system wide harmonics. If system harmonic
levels are exceeded Armstrong can also recommend additional harmonic mitigation
and the costs for such mitigation.

2




Performance curves are for reference only.

 $Confirm\ current\ performance\ data\ with\ Armstrong\ ACE\ Online\ selection\ software.$

DIMENSION DATA

	INDOOR	OUTDOOR
	(UL TYPE 12/ODP)	(UL TYPE 4X/TEFC)
Frame size:	184TC	213TC
Size:	3×3×6	3×3×6
HP:	7.5	7.5
RPM:	3000	3000
AB:	31.25(794)	37.79(960)
B1:	8.86(225)	8.86(225)
B2:	8.86(225)	8.86(225)
C1:	14.27(362)	14.27(362)
C2:	14.26(362)	14.26(362)
D1:	7.09(180)	7.09(180)
D2:	8.66(220)	8.66(220)
E:	6.84(174)	8.25(210)
F:	15.91(404)	20.25(514)
P:	10.38(264)	11.25(286)
SD:	14.96(380)	14.96(380)
T:	5.91(150)	5.91(150)
XY:	26.56(674)	29.18(741)
Weight:	427(193.7)	541(245.4)

Dimensions - inch (mm) Weight - lbs (kg)



TORONTO

+1 416 755 2291

BUFFALO

+1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER


+44 (0) 8444 145 145


BANGALORE


+91 (0) 80 4906 3555

SHANGHAI ESTABLISHED 1934 +86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY







ARMSTRONGFLUIDTECHNOLOGY.COM