

DESIGN ENVELOPE 4312 TWIN

SINGLE PHASE | 0406-003.0 | SUBMITTAL

Job: ______ Representative: _____

File No: 100.4846

Date: OCTOBER 27, 2014

Supersedes: NEW


Date: NEW

	Order No:	Date:
Engineer:	Submitted by:	Date:
Contractor:	Approved by:	Date:
PUMP DESIGN DATA	CONTROLS DATA	
No. of pumps: Tag:	: : Power sup	ply: Volts : 200-240VAC
Capacity:USgpm (L/s) Head:	ft (m)	Freq: 50/60Hz Phase: 1
Liquid: Viscosity:	Sancarlace cont	rol: Standard
Temperature:°F (°C) Specific gravity:	Minimum system pressu	
Suction: 4" (100mm) Discharge: 4" (100r	: to be maintain	ed:ft (m)*
Saction: 4 (100mm) Bischarge: 4 (100m	Protocol (standal	rd): ☐ Modbus RTU ☐ BACnet™ MS/TP☐ Johnson® N2 ☐ Siemens® FLN
	: Protocol (option	al): \[\text{LonWorks}^\end{al} \]
MOTOR DESIGN DATA	•	ure: ☐ Indoor - UL TYPE 12
нр: 3	:	☐ Outdoor - UL TYPE 4X with
		weather shield
Enclosure: Volts: 208 Freq: 60 Hz	:	☐ Outdoor - UL TYPE 4X less weather shield
Phase: 3 Efficiency: NEMA premium	: Disconnect swit	weather shield t ch: □ Non-fused
	Duty/stand	lby
	pre-wired brid	
MAXIMUM PUMP OPERATING CONDITION	S EMI/RFI cont	rol: 1-phase IVS102 units do not meet the
ANSI 125		EN61800-3 directive
175 psig at 150°F (12 bars at 65°C)	Harmonic suppressi	on: Dual Dc-link reactors (Equivalent: 5%
140 psig at 250°F (10 bars at 121°C)		AC line reactor) Supporting IEEE 519-1992 requirements**
	Cooli	ing: Fan-cooled through back channel
 Tolerance of ±0.125" (±3 mm) should be used For exact installation, data please write factory for certified dimensions 		ure: -10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)
continued difficults	•	ı/o: Two current or voltage inputs,
MECHANICAL SEAL DESIGN DATA	:	one current output I/O: Six programmable inputs (two can be configured as outputs)
Con file no 40 50 for standard machanisal coal data	Pulse inni	uts: Two programmable
See file no. 43.50 for standard mechanical seal detai indicated below		uts: Two programmable
		ort: 1-RS485, 1-USB
Armstrong seal reference number	•	essure is not known: Default to 40% of design head
☐ A1 (c) ☐ Others:	**The IVS 102 drive is a low harmonic guaranty performance to any syste	drive via built-in pc line reactors. This does not em wide harmonic specification or the costs to meet a lied with the system electrical details, Armstrong will

for such mitigation.

run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs

2



Performance curves are for reference only.

 ${\it Confirm \ current \ performance \ data \ with \ Armstrong \ {\it ACE \ Online \ selection \ software.}}$

INDOOR SD D2

TORONTO

+416 755 2291

BUFFALO

+716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER


+44 (0) 8444 145 145

BANGALORE

+91 (0) 80 4906 3555

SHANGHAI

+86 21 3756 6696



DIMENSION DATA

	INDOOR	OUTDOOR
	(UL TYPE 12/ODP)	(UL TYPE 4X/TEFC)
Frame size:	182TC	182TC
Size:	4×4×6	4×4×6
HP:	3	3
RPM:	1750	1750
AB:	29.50(749)	35.53(903)
B1:	9.65(245)	9.65(245)
B2:	9.65(245)	9.65(245)
C1:	15.76(400)	15.76(400)
C2:	16.12(409)	16.12(409)
D1:	11.42(290)	11.42(290)
D2:	11.42(290)	11.42(290)
E:	6.84(174)	7.50(191)
F:	15.94(405)	19.50(495)
P:	10.38(264)	9.56(243)
SD:	19.29(490)	19.29(490)
T:	7.01(178)	7.01(178)
XY:	26.81(681)	26.69(678)
Weight:	520(235.9)	600(272.2)

Dimensions - inch (mm) Weight - lbs (kg)

