



DIMENSIONS SHOWN AS: inches (mm)

EXCHANGER SIZE *-BAFFLE SPACING	DIMENSIONS											
	A		B		C		D		N1		N2	
	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
WX-63-4*-1	41 3/4	1060	28	711	19	483	38	965	3	76	3	76
WX-64-4*-1	53 3/4	1365	40	1016	31	787	50	1270	3	76	3	76
WX-65-4*-1	65 3/4	1670	52	1321	43	1092	62	1575	3	76	3	76
WX-66-4*-1	77 3/4	1975	64	1626	55	1397	74	1880	3	76	3	76
WX-67-4*-1	89 3/4	2280	76	1930	67	1702	86	2184	3	76	3	76
WX-68-4*-1	101 3/4	2584	88	2235	79	2007	98	2489	3	76	3	76
WX-69-4*-1	113 3/4	2889	100	2540	91	2311	110	2794	3	76	3	76
WX-610-4*-1	125 3/4	3194	112	2845	103	2616	122	3099	3	76	3	76
WX-611-4*-1	137 3/4	3499	124	3150	115	2921	134	3404	3	76	3	76
WX-612-4*-1	149 3/4	3804	136	3454	127	3226	146	3708	3	76	3	76

NOZZLE SCHEDULE

SERVICE	MARK	SHELL SIDE	MARK	TUBE SIDE
INLET	N1	AS PER TABLE	N5	1 1/2 (38) NPT
OUTLET	N2	AS PER TABLE	N6	1 1/2 (38) NPT
DRAIN	N3	1/2 (13) NPT	N7	1/2 (13) NPT
VENT	N4	3/4 (19) NPT		

- NOTES: 1. SUPPORTS SUPPLIED ONLY IF SPECIFIED ON ORDER.
 2. NOZZLE SIZES SHOWN ARE RECOMMENDED FOR MAXIMUM EXCHANGER LIFE.
 3. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.
 4. DRAWING IS NOT TO SCALE.
 5. ALL DIMN'S ±1/8 (3) UNLESS OTHERWISE SHOWN.

DESIGN CONDITIONS

	SHELL		TUBES	
	PSIG	KPa	PSIG	KPa
DESIGN PRESSURE	150	1034	150	1034
DESIGN TEMPERATURE	375 °F	191 °C	375 °F	191 °C
MIN. DESIGN METAL TEMP.	35 °F	1.7 °C	35 °F	1.7 °C
HYDRO. TEST PRESSURE	225	1551	300	2068
CONTENTS	WATER		WATER	

CUSTOMER:

LOCATION:

ENGINEER:

ORDER No.:

PROJECT/JOB:

LOCATION:

TAG:

(QUOTE #)

TITLE	G.A. 150 LB. WX SERIES HEAT EXCHANGERS	A R M S T R O N G				NUMBER	WX-6-4P-1(3)	REV.	
DATE:	12 / 01 / 94	BY:	D.C.R.	TEL: (416) 755-2291	TEL: (514) 421-2424	TEL: (716) 693-8813	TEL: (44) 120-657-9491		