



DIMENSIONS SHOWN AS: inches (mm)

EXCHANGER SIZE *BAFFLE SPACING	DIMENSIONS											
	A		B		C		D		(N1)		(N2)	
	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
WX-63-4*-4	48 3/8	1229	28	711	19	483	38	965	3	76	3	76
WX-64-4*-4	60 3/8	1534	40	1016	31	787	50	1270	3	76	3	76
WX-65-4*-4	72 3/8	1838	52	1321	43	1092	62	1575	3	76	3	76
WX-66-4*-4	84 3/8	2143	64	1626	55	1397	74	1880	3	76	3	76
WX-67-4*-4	96 3/8	2448	76	1930	67	1702	86	2184	3	76	3	76
WX-68-4*-4	108 3/8	2753	88	2235	79	2007	98	2489	3	76	3	76
WX-69-4*-4	120 3/8	3058	100	2540	91	2311	110	2794	3	76	3	76
WX-610-4*-4	132 3/8	3362	112	2845	103	2616	122	3099	3	76	3	76
WX-611-4*-4	144 3/8	3667	124	3150	115	2921	134	3404	3	76	3	76
WX-612-4*-4	156 3/8	3972	136	3454	127	3226	146	3708	3	76	3	76

NOZZLE SCHEDULE

SERVICE	MARK	SHELL SIDE	MARK	TUBE SIDE
INLET	(N1)	AS PER TABLE	(N5)	1 1/2 (38) FLG
OUTLET	(N2)	AS PER TABLE	(N6)	1 1/2 (38) FLG
DRAIN	(N3)	1/2 (13) NPT	(N7)	1/2 (13) NPT
VENT	(N4)	3/4 (19) NPT		

- NOTES:
1. SUPPORTS SUPPLIED ONLY IF SPECIFIED ON ORDER.
 2. NOZZLE SIZES SHOWN ARE RECOMMENDED FOR MAXIMUM EXCHANGER LIFE.
 3. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.
 4. DRAWING IS NOT TO SCALE.
 5. ALL DIM'S $\pm 1/8(3)$ UNLESS OTHERWISE SHOWN.

DESIGN CONDITIONS

	SHELL		TUBES	
	PSIG	KPa	PSIG	KPa
DESIGN PRESSURE	150	1034	150	1034
DESIGN TEMPERATURE	375 °F	191 °C	375 °F	191 °C
MIN. DESIGN METAL TEMP.	35 °F	1.7 °C	35 °F	1.7 °C
HYDRO. TEST PRESSURE	225	1551	225	1551
CONTENTS	WATER		WATER	

CUSTOMER:

LOCATION:

ENGINEER:

ORDER No.:

PROJECT/JOB:

LOCATION:

TAG:

(QUOTE #)

TITLE	G.A. 150 LB. WX SERIES HEAT EXCHANGERS	A R M S T R O N G				NUMBER	WX-6-4P-4(3)	REV.			
DATE:	12 / 01 / 94	BY:	D.C.R.	TORONTO - CANADA	TEL : (416) 755-2291	MONTREAL - CANADA	TEL : (514) 421-2424	BUFFALO - N. Y.	TEL: (716) 693-8813	COLCHESTER - U.K.	TEL: (44) 120-657-9491