

# DESIGN ENVELOPE 4382 DUALARM | 0606-003.0 | SUBMITTAL

Date: OCTOBER 30, 2015 Supersedes: 100.4618 Date: AUGUST 14, 2015

Job:			Repre	sentative:			
			Order	No:	Date:		
Engineer: Subm			Subm	itted by:	Date:		
Contractor: Appro			Appro	oved by:	Date:		
PUMP DESIGN DAT	ГА			CONTROLS DATA			
No. of pumps:		Tag:		Sensorless Control:	Standard		
Capacity:U				Minimum system pressure to be maintained:	ft (m)*		
Liquid: Temperature:				Protocol (standard):	<ul> <li>☐ Modbus rtu</li> <li>☐ BACnet<sup>™</sup> MS/TP</li> <li>☐ Johnson<sup>®</sup> N2</li> <li>☐ Siemens<sup>®</sup> FLN</li> </ul>		
Suction: 6" (150mm) Discharge: 6" (150			' (150mm)	Protocol (optional): ☐ LonWorks®			
OSHPD Seismic Certification OSP-0422-10 UL STD 778 & CSA STD C22.2 NO.108 certified				Enclosure:	: ☐ Indoor - UL TYPE 12 ☐ Outdoor - UL TYPE 4X with Weather Shield ☐ Outdoor - UL TYPE 4X less		
MOTOR DESIGN DA	ATA			Fused disconnect switch:	Weather Shield		
HP: RPM: F	rame size: _	Enclos	ure:	Duty/standby	<del>_</del>		
				pre-wired bridge:			
Volts: Hertz: 60 Hz Phase: 3  Efficiency: NEMA premium 12.12				EMI/RFI control:	: Integrated filter designed to meet EN61800-3		
MAXIMUM PUMP OPERATING CONDITIONS				Harmonic suppression:	: Dual DC-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**		
ANSI 125	s at 65°C)			Cooling:	ng: Fan-cooled through back channel		
175 psig at 150°F (12 bars at 65°C) 140 psig at 250°F (10 bars at 121°C)				Ambient temperature:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)		
ANSI 250				Analog I/o: Two current or voltage inputs, one current output			
250 psig at 150°F (17 bars at 65°C) 250 psig at 250°F (17 bars at 121°C)				Digital ı/o:	<b>Digital I/o:</b> Six programmable inputs (two can be configured as outputs)		
- Talamana of Loron"	و وا در در در در در در			Pulse inputs:	Two programmable		
<ul> <li>Tolerance of ±0.125" (±3 mm) should be used</li> <li>For exact installation, data please write factory for certified dimensions</li> </ul>				•	Two programmable		
				Communication port:	1-RS485, 1-USB		
				•	ure is not known: Default to 40% of design head drive via built-in pc line reactors. This does not		
MECHANICAL SEA	L DATA			•	n wide harmonic specification or the costs to meet		
eal Type: 2A Stationary Seat: Silicon carbide			arbide	a system wide specification. If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic			
Secondary Seal: EPDM Rotating Hardware: Stainless steel			nless steel				


FLUID TYPE	ALL GLYCOLS > 30% WT CONC		ALL OTHER NON-POTABLE FLUIDS		POTABLE (DRINKING) WATER	
Temperature	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C
Rotating Face	Silicon carbide		Resin bonded carbon	Antimony loaded carbon	Resin bonded carbon	
Seat Elastomer	EPDM (L-cup)	EPDM (0-ring)	EPDM (L-cup)	EPDM (0-ring)	EPDM (L-cup)	EPDM (o-ring)
Material Code	SCsc L EPSS 2A	SCsc o epss 2A	C-SC L EPSS 2A	ACsc o epss 2A	C-SC L EPSS 2A	C-SC O EPSS 2A

and the costs for such mitigation.

Spring: Stainless steel

levels are exceeded Armstrong can also recommend additional harmonic mitigation

2



Performance curves are for reference only.

 $Confirm\ current\ performance\ data\ with\ Armstrong\ {\tt ACE}\ Online\ selection\ software.$ 

ESTABLISHED 1934

#### **DIMENSION DATA**

	INDOOR	OUTDOOR		
	(UL TYPE 12/ODP)	(UL TYPE 4X/TEFC)		
Frame size:	182	182		
Size:	6×6×6	6×6×6		
HP:	3	3		
RPM:	1800	1800		
AB:	13.65(347)	19.50(495)		
B1:	7.39(188)	7.39(188)		
B2:	7.39(188)	7.39(188)		
C1:	13.63(346)	13.63(346)		
C2:	14.31(364)	14.31(364)		
D1:	16.81(427)	16.81(427)		
D2:	16.81(427)	16.81(427)		
E:	7.50(191)	7.50(191)		
P:	10.38(264)	9.50(241)		
F:	24.74(628)	30.70(780) 33.50(851)		
SD:	33.50(851)			
T:	7.75(197)	7.75(197)		
XY:	19.25(489)	20.00(508)		
Weight:	538(244.0)	616(279.4)		

Dimensions - inch (mm) Weight - lbs (kg)

# TORONTO

+1 416 755 2291

#### BUFFALO

+1 716 693 8813

## BIRMINGHAM

+44 (0) 8444 145 145

#### MANCHESTER


+44 (0) 8444 145 145

### BANGALORE

+91 (0) 80 4906 3555

# SHANGHAI

+86 21 3756 6696



ARMSTRONG FLUID TECHNOLOGY ARMSTRONGFLUIDTECHNOLOGY.COM