

DESIGN ENVELOPE 4382 DUALARM | 0608-002.0 | SUBMITTAL

File No: 100.4642

Date: OCTOBER 30, 2015

Supersedes: NEW

Date: NEW

Job:	Repre	sentative:		
	Order	No:	Date:	
Engineer:		itted by:	Date:	
Contractor: A		oved by:	Date:	
PUMP DESIGN DATA		CONTROLS DATA		
No. of pumps: Tag:		Sensorless Control:	Standard	
Capacity:USgpm (L/s) Head:		Minimum system pressure to be maintained:	ft (m)*	
Liquid: Viscosity: Viscosity:		Protocol (standard):	☐ Modbus rtu ☐ BACnet™ MS/TP☐ Johnson® N2 ☐ Siemens® FLN	
Suction: 6" (150mm) Discharge: 6" (: □ LonWorks®	
OSHPD Seismic Certification OSP-0422-10 UL STD 778 & CSA STD C22.2 NO.108 certified MOTOR DESIGN DATA		Enclosure:	: □ Indoor – UL TYPE 12 □ Outdoor – UL TYPE 4x with Weather Shield □ Outdoor – UL TYPE 4x less Weather Shield	
		Fused disconnect switch:		
HP: RPM: Frame size: Enclosur	e:	Duty/standby pre-wired bridge:		
Volts: Hertz: 60 Hz Phase: 3		:	Integrated filter designed to meet	
Efficiency: NEMA premium 12.12		EN61800-3		
MAXIMUM PUMP OPERATING CONDITIO	NS	Harmonic suppression:	Dual Dc-link reactors (Equivalent: 5% Ac line reactor) Supporting IEEE 519-1992 requirements**	
ANSI 125		Cooling:	Fan-cooled through back channel	
175 psig at 150°F (12 bars at 65°C) 140 psig at 250°F (10 bars at 121°C)		Ambient temperature:	-10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)	
ANSI 250 250 psig at 150°F (17 bars at 65°C)		Analog ı/o:	Two current or voltage inputs, one current output	
250 psig at 250°F (17 bars at 121°C)		Digital ı/o:	Six programmable inputs (two can be configured as outputs)	
T		Pulse inputs:	Two programmable	
 Tolerance of ±0.125" (±3 mm) should be used For exact installation, data please write factory for certified dimensions 		Relay outputs:	Two programmable	
		Communication port:	1-RS485, 1-USB	
		*If minimum maintained system pressure is not known: Default to 40% of design head		

MECHANICAL SEAL DATA

Stationary Seat: Silicon carbide

Rotating Hardware: Stainless steel

Seal Type: 2A


Secondary Seal: EPDM

Spring: Stainless steel

^{*}If minimum maintained system pressure is not known: Default to 40% of design head
**The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not
guaranty performance to any system wide harmonic specification or the costs to meet
a system wide specification. If supplied with the system electrical details, Armstrong
will run a computer simulation of the system wide harmonics. If system harmonic
levels are exceeded Armstrong can also recommend additional harmonic mitigation
and the costs for such mitigation.

FLUID TYPE	ALL GLYCOLS > 30% WT CONC		ALL OTHER NON-POTABLE FLUIDS		POTABLE (DRINKING) WATER	
Temperature	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C
Rotating Face	Silicon carbide		Resin bonded carbon	Antimony loaded carbon	Resin bonded carbon	
Seat Elastomer	EPDM (L-cup)	EPDM (o-ring)	EPDM (L-cup)	EPDM (0-ring)	EPDM (L-cup)	EPDM (o-ring)
Material Code	SCSC L EPSS 2A	SCsc o epss 2A	C-SC L EPSS 2A	ACsc o epss 2a	C-SC L EPSS 2A	C-SC O EPSS 2A

2



Performance curves are for reference only.

 $Confirm\ current\ performance\ data\ with\ Armstrong\ {\tt ACE}\ Online\ selection\ software.$

DIMENSION DATA

	INDOOR (UL TYPE 12/ODP)	OUTDOOR (UL TYPE 4X/TEFC)
Frame size:	182	182
Size:	6×6×8	6×6×8
HP:	2	2
RPM:	1500	1500
AB:	24.39(619)	24.39(619)
B1:	9.75(248)	9.75(248)
B2:	9.75(248)	9.75(248)
C1:	16.90(429)	16.90(429)
C2:	17.63(448)	17.63(448)
D1:	16.81(427)	16.81(427)
D2:	16.81(427)	16.81(427)
E:	7.50(190)	7.50(190)
F:	16.02(407)	16.02(407)
P:	9.50(241)	9.50(241)
SD:	33.94(862)	33.94(862)
T:	7.88(200)	7.88(200)
XY:	20.17(512)	20.17(512)
Weight:	514(233.1)	540(244.8)

Dimensions - inch (mm) Weight - lbs (kg)

TORONTO

+1 416 755 2291

BUFFALO

+1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER


+44 (0) 8444 145 145

BANGALORE

+91 (0) 80 4906 3555

SHANGHAI

+86 21 3756 6696



ARMSTRONG FLUID TECHNOLOGY
ESTABLISHED 1934 ARMSTRONGFLUIDTECHNOLOGY.COM