



DIMENSIONS SHOWN AS: inches (mm)

EXCHANGER SIZE *BAFFLE SPACING	DIMENSIONS											
	A		B		C		D		(N1)		(N2)	
	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
W-42-2*-4	33 1/4	845	16 1/2	419	9 1/2	241	26	660	2	51	2	51
W-43-2*-4	45 1/4	1149	28 1/2	724	21 1/2	546	38	965	2	51	2	51
W-44-2*-4	57 1/4	1454	40 1/2	1029	33 1/2	851	50	1270	2	51	2	51
W-45-2*-4	69 1/4	1759	52 1/2	1334	45 1/2	1156	62	1575	2	51	2	51
W-46-2*-4	81 1/4	2064	64 1/2	1638	57 1/2	1461	74	1880	2	51	2	51
W-47-2*-4	93 1/4	2369	76 1/2	1943	69 1/2	1765	86	2184	2	51	2	51
W-48-2*-4	105 1/4	2673	88 1/2	2248	81 1/2	2070	98	2489	2	51	2	51
W-49-2*-4	117 1/4	2978	100 1/2	2553	93 1/2	2375	110	2794	2	51	2	51
W-410-2*-4	129 1/4	3283	112 1/2	2858	105 1/2	2680	122	3099	2	51	2	51

NOZZLE SCHEDULE				
SERVICE	MARK	SHELL SIDE	MARK	TUBE SIDE
INLET	(N1)	AS PER TABLE	(N5)	1 1/4 (32) FLG
OUTLET	(N2)	AS PER TABLE	(N6)	1 1/4 (32) FLG
DRAIN	(N3)	1/2 (13) NPT		
VENT	(N4)	3/4 (19) NPT		

NOTES: 1. SUPPORTS SUPPLIED ONLY IF SPECIFIED ON ORDER.
 2. NOZZLE SIZES SHOWN ARE RECOMMENDED FOR MAXIMUM EXCHANGER LIFE.
 3. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.
 4. DRAWING IS NOT TO SCALE.
 5. ALL DIMN'S ±1/8 (3) UNLESS OTHERWISE SHOWN.

DESIGN CONDITIONS				
	SHELL		TUBES	
DESIGN PRESSURE	150 PSIG	1034 KP _a	150 PSIG	1034 KP _a
DESIGN TEMPERATURE	375 °F	191 °C	375 °F	191 °C
MIN. DESIGN METAL TEMP.	35 °F	1.7 °C	35 °F	1.7 °C
HYDRO. TEST PRESSURE	225 PSIG	1551 KP _a	225 PSIG	1551 KP _a
CONTENTS	WATER		WATER	

CUSTOMER:
 LOCATION:
 ENGINEER:
 ORDER No.:
 PROJECT/JOB:
 LOCATION:
 TAG: (QUOTE #)

TITLE	A R M S T R O N G				NUMBER	REV.
G.A. 150 LB. W SERIES HEAT EXCHANGERS	TORONTO - CANADA	MONTREAL - CANADA	BUFFALO - N. Y.	COLCHESTER - U.K.	W-4-2P-4(2)	
DATE: 12/01/94 BY: D.C.R.	TEL: (416) 755-2291	TEL: (514) 421-2424	TEL: (716) 693-8813	TEL: (44) 120-657-9491		