

DESIGN ENVELOPE 4382 DUALARM | 0608-007.5

File No: 100.4648

Date: OCTOBER 30, 2015

Supersedes: 100.4634

Date: AUGUST 14, 2015


Job: R			Repre	Representative:			
			Order	No:	Date:		
Engineer:			Submi	itted by:	Date:		
			Appro	oved by:	Date:		
PUMP DESIGN DA	ATA			CONTROLS DATA			
No. of pumps:		Tag:		Sensorless Control:	Standard		
Capacity:				: Minimum system pressure to be maintained:	ft (m)*		
Liquid:				•	☐ Modbus RTU ☐ BACnet™ MS/TP		
Temperature:	°F (°C)	Specific gravity:		•	☐ Johnson® N2 ☐ Siemens® FLN		
Suction: 6" (150mm) Discharge: 6" (150mm)				Protocol (optional):			
оѕнро Seismic Certi	fication osp-	0422-10		Enclosure:	☐ Indoor – UL TYPE 12 ☐ Outdoor – UL TYPE 4X with		
UL STD 778 & CSA STD C22.2 NO.108 certified				:	Weather Shield		
• •				:	☐ Outdoor - UL TYPE 4X less Weather Shield		
MOTOR DESIGN I	DATA			: Fused disconnect switch:			
HP: RPM:	_ Frame size: _	Enclosure	:	Duty/standby			
Volte	Hartz: 60 H	z Phase: a		pre-wired bridge:			
Volts: Hertz: 60 Hz Phase: 3 Efficiency: NEMA premium 12.12				EMI/RFI control:	: Integrated filter designed to meet EN61800-3		
				Harmonic suppression: Dual DC-link reactors (Equivalent:			
MAXIMUM PUMP OPERATING CONDITIONS				•	AC line reactor) Supporting IEEE 519-1992 requirements**		
ANSI 125				: Cooling:	Fan-cooled through back channel		
175 psig at 150°F (12 ba	_			Ambient temperature: -10°C to +45°C up to 1000 meters about			
140 psig at 250°F (10 b	pars at 121°C)			, Ambient temperatures	sea level (-14°F to +113°F, 3300 ft)		
ANSI 250				Analog ı/o:	Two current or voltage inputs,		
250 psig at 150°F (17 bars at 65°C)				Distributives	one current output		
250 psig at 250°F (17 bars at 121°C)				: Digital i/o:	Six programmable inputs (two can be configured as outputs)		
T					Two programmable		
 Tolerance of ±0.125" (±3 mm) should be used For exact installation, data please write factory for certified dimensions 				Relay outputs:	Two programmable		
				Communication port:	1-RS485, 1-USB		
				•	ure is not known: Default to 40% of design head		
MECHANICAL SEA	AL DATA			•	Irive via built-in DC line reactors. This does not nwide harmonic specification or the costs to meet		
Seal Type: 2A	Stationa	ary Seat: Silicon carb	ide	a system wide specification. If supplied with the system electrical details, Armstrong			
Secondary Seal: EPDM Rotating Hardware: Stainless steel			s steel	will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation			

FLUID TYPE	ALL GLYCOLS > 30% WT CONC		ALL OTHER NON-POTABLE FLUIDS		POTABLE (DRINKING) WATER	
Temperature	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C
Rotating Face	Silicon carbide		Resin bonded carbon	Antimony loaded carbon	Resin bonded carbon	
Seat Elastomer	EPDM (L-cup)	EPDM (O-ring)	EPDM (L-cup)	EPDM (0-ring)	EPDM (L-cup)	EPDM (0-ring)
Material Code	SCSC L EPSS 2A	SCsc o epss 2A	C-SC L EPSS 2A	ACsc o epss 2A	C-SC L EPSS 2A	C-SC O EPSS 2A

and the costs for such mitigation.

Spring: Stainless steel

2



Performance curves are for reference only. Confirm current performance data with Armstrong ACE Online selection software.

DIMENSION DATA

	INDOOR (UL TYPE 12/ODP)	OUTDOOR (UL TYPE 4X/TEFC)		
	(OL TTPE 12/ODF)	(OLTTPE 4X/TEPC)		
Frame size:	213	213		
Size:	6×6×8	6×6×8		
HP:	7.5	7.5		
RPM:	1800	1800		
AB:	16.73(425)	20.25(514)		
B1:	9.75(248)	9.75(248)		
B2:	9.75(248)	9.75(248)		
C1:	16.90(429)	16.90(429)		
C2:	17.59(447)	17.59(447)		
D1:	16.75(425)	16.75(425)		
D2:	16.75(425)	16.75(425)		
E:	8.25(210)	8.25(210)		
P:	12.13(308)	11.25(286)		
F:	29.42(747)	35.21(894)		
SD:	33.88(860)	33.88(860)		
T:	7.875(200)	7.875(200)		
XY:	25.64(651)	26.77(680)		
Weight:	674(305.7)	808(366.5)		

Dimensions - inch (mm) Weight - lbs (kg)

TORONTO

+1 416 755 2291

BUFFALO

+1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER

+44 (0) 8444 145 145


BANGALORE

+91 (0) 80 4906 3555

ESTABLISHED 1934

SHANGHAI

+86 21 3756 6696



ARMSTRONG FLUID TECHNOLOGY ARMSTRONGFLUIDTECHNOLOGY.COM