

ASL Air Eliminator - 1"

SUBMITTAL

JOB: _____	REPRESENTATIVE: _____
ENGINEER: _____	ORDER NO: _____ DATE: _____
CONTRACTOR: _____	SUBMITTED BY: _____ DATE: _____
	APPROVED BY: _____ DATE: _____



MODEL NO. ORDERED: _____ QTY.: _____
TAG NO.: _____

Designed and constructed per ASME, Section VIII, Division 1.

MAXIMUM OPERATING CONDITIONS	
Working Temperature	350°F (°C)
Working Pressure	125 psi (862 kPa)

MATERIALS OF CONSTRUCTION	
Body	Steel
System Connection	Steel

Model	A	B	C	D	E	F	G	H	Shipping Weight
	NPT	in. (mm)	in. (mm)	in. (mm)	in. (mm)	in. (mm)	NPT	NPT	lbs. (kg)
1"-ASL	1.00	4.50 (114)	12.00 (305)	4.00 (102)	4.00 (102)	7.00 (178)	0.75	0.75	15 (7)



Armstrong Pumps Inc.
93 East Avenue
North Tonawanda, New York
U.S.A. 14120-6594
Tel: (716) 693-8813
Fax: (716) 693-8970
www.armstrongpumps.com

S.A. Armstrong Limited
23 Bertrand Avenue
Toronto, Ontario
Canada, M1L 2P3
Tel: (416) 755-2291
Fax: (416) 759-9101



© S.A. Armstrong Limited 2003

Armstrong Pumps Limited
Peartree Road, Stanway
Colchester, Essex
United Kingdom, CO3 0LP
Tel: +44 (0) 1206 579491
Fax: +44 (0) 1206 760532

Armstrong Darling
9001 De L'Innovation, Suite 200
Montreal, Quebec
Canada, H1J 2X9
Tel: (514) 352-2424
Fax: (514) 352-2425

