

# DESIGN ENVELOPE 4382 DUALARM

0808-003.0 | SUBMITTAL

File No: 104.5515

Date: JULY 8, 2019

Supersedes: 104.5515

Date: AUGUST 1, 2018

Job: Repre		epresentative:	esentative:		
	C	Order No:	Date:		
Engineer: Subm  Contractor: Appro		ubmitted by:	Date:		
		approved by:	Date:		
PUMP DESIGN DATA		CONTROLS DATA			
No. of pumps:	Tage	Protocol (standard):	☐ BACnet™ MS/TP		
		:	☐ BACnet™ TCP/IP		
Total system design flow:		:	☐ Modbus rtu		
Head:ft(m)		: Eliciosule.	☐ Indoor – UL TYPE 12		
Flow per pump head:			☐ Outdoor – UL TYPE 4X with		
Parallel flow:	USgpm(L/s	s)	Weather Shield		
Liquid:	Viscosity:	_ :	☐ Outdoor - UL TYPE 4X less Weather Shield		
Temperature: °F (°C)	Specific gravity:	:  Fused disconnect switch:			
Suction: 8" (200mm)	Discharge: 8" (200mm)				
OSHPD Seismic Certification o	SP-0422-10	EMIJ RFI COITUOI.	ri control: Integrated filter designed to meet EN61800-3		
UL STD 778 & CSA STD C22.2 1	-	: Harmonic suppression:	Dual Dc-link reactors (Equivalent: 5%		
Test report is supplied with ea	ch pump	:	Ac line reactor) Supporting		
		:	IEEE 519-1992 requirements**		
MOTOR DESIGN DATA		Cooling:	Fan-cooled through back channel		
нр: RPM: Frame size: _	Enclosure: Volts:	Ambient temperature:	-10°c to +45°c up to 1000 meters above		
Hertz: 60 Hz Phase: 3 Eff	iciency: NEMA premium 12.12		sea level (+14°F to +113°F, 3300 ft)		
		Analog ı/o:	Two current or voltage inputs,		
MAXIMUM PUMP OPER	ATING CONDITIONS	<u>:</u>	one speed output		
ANSI 125 - (CONSTRUCTION		Digital ı/o:	Two inputs, two outputs		
175 psig at 150°F (12 bar at 65°C)		Pulse inputs:	Two programmable		
140 psig at 250°F (10 bar at 121°C		Relay outputs:	Two programmable		
.40 po.g at 250 . (10 ca. at .2. t	,,	Communication port:	1-RS485		
		** The IVS drive is a low harmonic dr	rive via built-in DC line reactors. This does not		
FLOW READOUT ACCU	RACY		tem wide harmonic specification or the costs to  If supplied with the system electrical details,		
		micci a system whice specification	i. ii sappiica witii tiic systeiii cicctiicai detaiis,		

#### MECHANICAL SEAL DATA

The Design Envelope model selected will provide flow reading

on the controls local keypad & digitally for the BMS. The model

readout will be factory tested to ensure ±5% accuracy.

Seal Type: 2A Stationary Seat: Silicon carbide Secondary Seal: EPDM Rotating Hardware: Stainless steel Spring: Stainless steel Spring: Stainless steel

FLUID TYPE	ALL GLYCOLS > 30% WT CONC		ALL OTHER NON-POTABLE FLUIDS		POTABLE (DRINKING) WATER	
Temperature	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C	up to 200°F / 93°C	over 200°F / 93°C
Rotating Face	Silicon carbide		Resin bonded carbon	Antimony loaded carbon	Resin bonded carbon	
Seat Elastomer	EPDM (L-cup)	EPDM (o-ring)	EPDM (L-cup)	EPDM (O-ring)	EPDM (L-cup)	EPDM (o-ring)
Material Code	SCSC L EPSS 2A	SCsc o epss 2A	C-SC L EPSS 2A	ACsc o epss 2A	C-SC L EPSS 2A	C-SC O EPSS 2A

Armstrong will run a computer simulation of the system wide harmonics. If

harmonic mitigation and the costs for such mitigation.

system harmonic levels are exceeded Armstrong can also recommend additional

2

# **OPTIONS**

#### SENSORLESS BUNDLE (STANDARD)



Operation of pump without a remote sensor. Includes:

- Sensorless control
- Flow readout
- Constant flow
- Constant pressure

Minimum system pressure to be maintained ft (m)

\* If minimum maintained system pressure is not known: Default to 40% of design head

#### PARALLEL SENSORLESS (STANDARD)



Operation of multiple pumps without a remote sensor

Minimum system pressure to be maintained ft (m)

\* If minimum maintained system pressure is not known: Default to 40% of design head

#### ☐ ENERGY PERFORMANCE BUNDLE



Provides energy savings on oversized systems by adjusting pump parameters to on-site conditions. Includes:

- Auto-flow balancing Automatically determines control curve between design flow at on-site system head, and minimum (zerohead) flow for energy savings
- Maximum flow control Limits flow rate to pre-set maximum for potential energy savings

Maximum flow rate gpm (L/s)

\*Only available if sensorless bundle is enabled

#### □ PROTECTION BUNDLE



Protects other flow sensitive equipment by setting limits of pump operation. Includes:

- Minimum flow control Attempts to maintain flow rate to pre-set minimum to protect equipment in system
- Bypass valve control Actuates a bypass valve to protect flow sensitive equipment if pre-set minimum flow rate is reached

Minimum flow rate gpm (L/s)

# □ ZONE OPTIMIZATION BUNDLE



Controls pumps to ensure multiple zones are satisfied for heating or cooling

 2 sensor control - Controls pumps in a 2-zone application to ensure both zones are always satisfied for heating or cooling

# □ DUAL SEASON SETUP



Pre-sets heating and cooling parameters for pumps in 2-pipe systems

#### Cooling

Duty point	gpm (L/s) at	ft (m)
Minimum system	m pressure to be maint	ained
	ft (m)	
Heating		
Duty point	gpm (L/s) at	ft (m)
Minimum system	m pressure to be maint	ained
	ft (m)	

#### **OPTIONAL SERVICES**

### **ON-SITE PUMP COMMISSIONING**



Where purchased and applicable, onsite commissioning by an Armstrong representative will include setting up communication with the Pump (not wiring to BAS), adjusting parameters to match on-site conditions, register the pumps for enhanced warranty and connect the pumps to the router as part of the activation of Pump Manager.

#### PUMP MANAGER




As a Performance Management Service, Pump Manager is an online automated fault detection and diagnostic service for sustained performance and enhanced reliability. It includes advanced trending, alerts of variance in performance and automated reports.

Available in yearly increments. Includes an option for a price discount on the Extended Warranty Service.

<sup>\*</sup>Only available if sensorless bundle is enabled

<sup>\*</sup>The Service requires an active internet connection.

3



Performance curves are for reference only.

Confirm current performance data with Armstrong ACE Online selection software.

# INDOOR OUTDOOR SD D2 D1 D1 \_E1 Ε B1 В2 \_ E2\_ В1 В2 WEATHER ØΡ ØΡ SHIELD ΑВ C1 C2

#### **DIMENSION DATA**

	INDOOR	OUTDOOR
	(UL TYPE 12/ODP)	(UL TYPE 4X/TEFC)
Frame size:	213	213
Size:	8×8×8	8×8×8
HP:	3	3
RPM:	1500	1500
AB:	29.22(742)	29.22(742)
B1:	10.00(254)	10.00(254)
B2:	9.00(229)	9.00(229)
C1:	18.50(470)	18.50(470)
C2:	18.60(472)	18.60(472)
D1:	18.50(470)	18.50(470)
D2:	23.00(584)	23.00(584)
E:	8.25(210)	8.25(210)
F:	16.77(426)	16.77(426)
P:	11.25(286)	11.25(286)
SD:	45.50(1156)	45.50(1156)
T:	9.47(240)	9.47(240)
XY:	27.21(691)	27.21(691)
Weight:	1088(493.5)	1142(518.2)

Dimensions - inch (mm) Weight - lbs (kg)

- Tolerance of ±0.125" (±3 mm) should be used
- For exact installation, data please write factory for certified dimensions

#### TORONTO

23 BERTRAND AVENUE TORONTO, ONTARIO CANADA M1L 2P3 +1 416 755 2291

#### BUFFALO

93 EAST AVENUE NORTH TONAWANDA, NEW YORK U.S.A. 14120-6594 +1 716 693 8813

#### BIRMINGHAM

HEYWOOD WHARF, MUCKLOW HILL HALESOWEN, WEST MIDLANDS UNITED KINGDOM B62 8DJ +44 (0) 8444 145 145

#### MANCHESTER

WOLVERTON STREET
MANCHESTER
UNITED KINGDOM
M11 2ET
+44 (0) 8444 145 145

#### BANGALORE

#59, FIRST FLOOR, 3RD MAIN MARGOSA ROAD, MALLESWARAM BANGALORE, INDIA 560 003 +91 (0) 80 4906 3555

#### SHANGHAI

UNIT 903, 888 NORTH SICHUAN RD. HONGKOU DISTRICT, SHANGHAI CHINA 200085 +86 (0) 21 5237 0909

#### SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES SAO PAULO, BRAZIL +55 11 4785 1330

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM

