

## VERTICAL IN-LINE FIRE PUMP 43PF | 8 x 8 x 13 | SUBMITTAL

File No: F43.103L  
Date: JULY 17, 2022  
Supersedes: F43.103L  
Date: AUGUST 10, 2016

Job: \_\_\_\_\_ Representative: \_\_\_\_\_  
 \_\_\_\_\_ Order no.: \_\_\_\_\_ Date: \_\_\_\_\_  
 Engineer: \_\_\_\_\_ Submitted by: \_\_\_\_\_ Date: \_\_\_\_\_  
 Contractor: \_\_\_\_\_ Approved by: \_\_\_\_\_ Date: \_\_\_\_\_

### PUMP DESIGN DATA

Flow: \_\_\_\_\_  
 Head: \_\_\_\_\_

### MOTOR DATA

HP: \_\_\_\_\_ RPM: \_\_\_\_\_  
 Volt: \_\_\_\_\_ ph: \_\_\_\_\_ Hz: \_\_\_\_\_

ENCLOSURE: \_\_\_\_\_  
 \_\_\_\_\_


### FLANGE RATING

- ANSI 125# STD
- ANSI 250# STD

### FIRE PUMP LISTING

- UL
- ULC
- FM

- Dimensions are not to be used for construction purposes unless certified.
- Data subject to change without notice.



SUBMITTAL  
8×8×13

Vertical In-line fire pump  
Series 43PF

2

## PUMP DATA

PUMP	DIMENSIONS inches (mm)					WEIGHT
MODEL	A	B	C	D	E	lbs (kgs)
43PF 8×8×13	8.00 (203)	8.00 (203)	23.00 (584)	19.00 (483)	9.94 (252)	552 (250.4)

## UL LISTED MOTOR DATA

MOTOR	DIMENSIONS inches (mm)			WEIGHT
FRAME	F MAX	AG MAX	H MAX	lbs (kgs)
324TC	14.13 (359)	44.15 (1121)	12.69 (322)	424 (192.3)
326TC	14.13 (359)	44.15 (1121)	12.69 (322)	424 (192.3)
364TC	17.63 (448)	41.41 (1052)	16.19 (411)	651 (295.3)
365TC	17.63 (448)	41.41 (1052)	16.19 (411)	651 (295.3)

### TORONTO

+1 416 755 2291

### BUFFALO

+1 716 693 8813

### DROITWICH SPA

+44 8444 145 145

### MANCHESTER

+44 8444 145 145

### BANGALORE

+91 80 4906 3555

### SHANGHAI

+86 21 5237 0909

### BEIJING

+86 21 5237 0909

### SÃO PAULO

+55 11 4785 1330

### LYON

+33 4 26 83 78 74

### DUBAI

+971 4 887 6775

### MANNHEIM

+49 621 3999 9858

### JIMBOLIA

+40 256 360 030

ARMSTRONG FLUID TECHNOLOGY®  
ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM